
ITE Grade AC-DC Power Supplies



250 Watt

- 4.5 x 2.5 X 1.5
- Mounting as Per 4 X 2 Footprint/ 3 X5 Footprint
- 250 Watts Convection Cooled & 350 Watts Forced Cooled
- Efficiency up to 94%
- -40 to 70 degree operating temperature
- High power density : 20.74W/inch³
- 12 V Fan O/P / Thermal Shut-Down feature / Dual fusing
- Current Sharing (Optional with ADD-ON CARD)
- 5 V STBY/ PGPF Signal / Remote ON-OFF Feature (Optional)
- 2.56m Hours, Telcordia -SR332-issue 3 MTBF
- No Load Power < 1W
- Available with metal enclosures/accessories



Dimension

FLS: 4.5 x 2.5 x 1.5 Inches Form factor The New FLS250 series is true fanless power up to 250W. this is a highly efficient power supply that can deliver up to 350W with air. The power supply is packed in 4.5' x 2.5' size having the option of industry-standard "2 x 4" or "3 x 5" like a mounting option. Also available in various type of casing option.

250 Watts Model Number Description Voltage Max. Load Max. Load Min. Load Ripple (Convection) (375 LFM) 2% with Screw Terminal FLS250-1X12 12V 16.60A 25.00A 0.0A with JST Connector 2% FLS250-1X12 12V 16.60A 18.00A 0.0A 2% with Screw Terminal FLS250-1X15 15V 13.30A 20.00A 0.0A 2% FLS250-1X15 with JST Connector 13.30A 15V 18.00A 0.0A 1% with Screw Terminal FLS250-1X24 24V 10.41A 14.50A 0.0A 1% FLS250-1X24 with JST Connector 24V 10.41A 14.50A 0.0A 1% FLS250-1X30 with Screw Terminal 30V 8.30A 11.60A 0.0A 1% FLS250-1X30 with JST Connector 30V 11.60A 0.0A 8.30A 1% with Screw Terminal FLS250-1X48 48V 5.20A 7.20A 0.0A 1% with JST Connector FLS250-1X48 48V 0.0A 5.20A 7.20A 1% FLS250-1X58 with Screw Terminal 58V 4.30A 6.0A 0.0A with JST Connector 1% FLS250-1X58 58V 4.30A 6.0A 0.0A For Screw Terminal version replace "X" above with "0", example FLS250-1024 For Header version replace "X" above with "3", example FLS250-1324 Add Suffix "B" for 3 X 5 Mounting option, example FLS250-1024-B For Current Sharing (ADD-ON CARD) Option contact sales person. For 5V STBY / Remote ON-OFF / PGPF used model number FLS250-2XXX (Contact Sales for more details)

FLS250-CK Metal Cover Kit Accessory Available.

ITE Grade AC-DC Power Supplies



Pin Connection			
J1 (Input)	PIN 1	ACLINE	
	PIN 2	NOT FITTED	
	PIN 3	AC NEUTRAL	
J2 Option 1 & 2	PIN 1,2,3	V1 +VE	
(Output)	PIN 4,5,6	V1 -VE	
J4 (Earth)		Quick Disconnect	
(91)	PIN 1	+VS	
Signal Connector	PIN 2	-VS	
	PIN 3	FAN -	
	PIN 4	FAN +	
J(310)	PIN 1	+5V	
(Multifunction Connector)***	PIN 2	GND	
	PIN 3	GND	
	PIN 4	REMOTE ON/OFF	
	PIN5	PGPF	

Notes -

1. "***" mark content available only in FLS250-2XXX series

2. Ripple is peak to peak with 20 MHz bandwidth and 10 μ F (Tantalum capacitor) in parallel with a 0.1 μ F capacitor at rated line voltage and load ranges.

3. Specifications are for nominal input voltage, 25°C unless otherwise stated.

4. 250W with natural convection cooling at 100 to 264VAC.

5. 350W with Forced cooling at 100 to 264VAC.

6. Combine Output Power of Main Output, Fan supply and Standby shall not exceed max power rating.

7. Output ripple can be more than 1 % of the output voltage.

8. When used in Cover Kit, de-rate output power to 70% under all operating conditions.

9. "***" Standby output voltage 5 V/ 0.5A(convection) with tolerance including set point accuracy, line and load regulation is +/-10 %. Ripple and noise is less than 5 %.

Input					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage	85		264	VAC	De-rate linearly from 100% at 100VAC to 80% at 85VAC
	120		370	VDC	
Input Frequency	47		63	Hz	
Input Current			6.3	А	
Inrush Current	115 VAC - 25A	230VAC - 45A	264 VAC -75A	А	
No Load Input Power			1	W	
Power Factor	exceeds 0.9	95 at Full Load			


ITE Grade AC-DC Power Supplies



Output					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Power		250	350	W	
Hold-up Time		8mS			At 230 VAC
Line Regulation			+/-0.5%		
Load Regulation			+/-0.5%		
Output Voltage Adjustability			+/-3%		
Rise Time		55		ms	
Set Point Tolerance		+/-1%			
Over Current Protection		> 110%			
Over Voltage Protection		110 to 140%			
Transient Response		25% step load	d change, at 0.	1A/uS slew ra	te, 50% duty cycle, 50Hz=4% , recovery time < 5 ms

General					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency	92%		94%		At 230 VAC
Mean Time Between Failure	2.56m Hours				Telcordia -SR332-issue 3
Isolation: Input to Output		4000		VDC	ITAV
Input to Ground		2500		v DC	
Leakage Current		300 uA Typic	al		





ITE Grade AC-DC Power Supplies




Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-40		70	°C	-40 to 0 startup is guaranteed with spec deviation.
					70°C (Derated)
Storage Temperature	-40		85	°C	
Relative Humidity	5		95	%	
Operating Altitude			16,000	ft	RH, non-condensing
Short Circuit Protection		Hiccup mode			
Switching Frequency		PFC – 70 to 130 KHz ,PWM – 50-80 KHz			
Cooling					350W with 375 LFM forced air cooling at 100 to 264VAC
					250W with natural convection cooling at 100 to 264VAC


Signals & Controls	
Characteristic	Notes & Conditions
***Power Good	Is a TTL signal which goes high after main output reaches 90% of its set value.
	The delay is 0.1 s to 0.5 s
***Power Fail	The same signal goes low at least 1ms before main output falls to 90% of set value
	at AC Power off
***Remote on/off	Shorting Pin 3 to Pin 4 enables main output while keeping the Pins open disables
	main output.


Signals & Controls Drawing



ITE Grade AC-DC Power Supplies







ITE Grade AC-DC Power Supplies



Mechanical Specifications

AC Input Connector (J1)	Molex: 26-60-4030
	Mating: 09-50-3031; Pins: 08-50-0106
DC Output Connector (J2) Option 1	Molex: 39357 Series or equivalent
(Screw Terminal)	
DC Output Connector (J2) Option 2	JST p/n: B6P-VH(LF)(SN)
(JST Connector)	Mating: JST p/n: VHR-6M; Pins: SVH-41T-P1.1
Signal Connector (J9)	Molex Part No: 10-89-7041 or equivalent
	Mating part no: 1053082204 ; Pins: 1053001100
J(310)	HEADER 5POS 2.54MM) P/N : P9102-40-12-1
(Multifunction Connector)***	Mating part no : CONN RCPT HSNG 5POS CST-100 II P/N :1375820-5
	Pins : CONN SOCKET 22-26AWG CRIMP TIN P/N : 1375819-1
Dimensions	4.5 x 2.5 x 1.58 inches
	(114.30 x 63.5 x 40 mm)
Weight	400 gm approx

EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN 55032	Level B	CISPR22-B, FCC PART15-B
Radiated	EN 55032	Level A	Level B with external core
			(King core K5B RC 25x12x15-M or Equivalent in
			input cable)

EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Input Current Harmonics	EN 61000-3-2		Class A	
Voltage Fluctuation and Flicker	EN 61000-3-3			compliance
ESD Immunity	EN 61000-4-2	Level 3	A	
Radiated Field Immunity	EN 61000-4-3	Level 3	A	
Electrical Fast Transient Immunity	EN61000-4-4	Level 3	A	
Surge Immunity	EN 61000-4-5	Level 3	A	
Conducted Immunity	EN 61000-4-6	Level 3	A	
Magnetic Field Immunity	EN 61000-4-8	Level 3	A	
Voltage dips, interruptions	EN 61000-4-11		A & B	


Safety Approvals

Safety Agency	Safety Standard	Notes & Conditions
СВ	IEC62368-1:2018	
Nemko	EN62368-1:2020;A11	ITAV
UL	UL62368-1 ED 3.0	
CSA	CAN/CSA C22.2 No. 62368-1:19	
CE Mark	Complies with LVD Directive	


ITE Grade AC-DC Power Supplies



Derating Curve





Derating Curve



ITE Grade AC-DC Power Supplies







Derating Curve

Mechanical Drawing

ITE Grade AC-DC Power Supplies



Screw terminal (1XXX/ 2XXX) 4.50[114.3] 0,37[9,53] <u>0.37[9.53]</u> 3.75[95.25] APPROX 1.57[40.00] 0 000 Ο 00000 \bigcirc .75[44.45] 2.50[63,5] 0 VE J 1^L VE +VE \square +VF +VE \square Ó \bigcirc MOUNTING HOLES EARTH DIA 0.13[3.50] 4-PLS 0.37**[**9.53] 0 \bigcirc \bigcirc 0.37[9.53] 0.37[9.53 \bigcirc \bigcirc \bigcirc ß MECHANICAL DUTLINE DIMENSIONS ALL DIMENSIONS ARE IN INCHESEMM] <u>0,37[9,53]</u> GEN TOLERANCE :+/-0.04 [+/-1.0MM]

ITE Grade AC-DC Power Supplies




Mechanical Drawing

Header terminal (1XXX/ 2XXX)


NDTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13,



ITE Grade AC-DC Power Supplies






ITE Grade AC-DC Power Supplies




Mechanical Drawing




NDTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13.



ITE Grade AC-DC Power Supplies





ITE Grade AC-DC Power Supplies




Mechanical Drawing

FLS250 3 X 5 with L -Bracket

NOTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13.



ITE Grade AC-DC Power Supplies




Mechanical Drawing

FLS250 2.5 X 4.5 with U Channel


NOTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13.



ITE Grade AC-DC Power Supplies





ITE Grade AC-DC Power Supplies




Mechanical Drawing

FLS250 2.5 X 4.5 with Cover kit

NOTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13.



ITE Grade AC-DC Power Supplies




Mechanical Drawing

FLS250 3 X 5 with Cover Kit

NOTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13.



ITE Grade AC-DC Power Supplies





Mechanical Drawing


FLS250 2.5 X 4.5 with Cover kit - Fan

NOTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13.







MECHANICAL OUTLINE DIMENSIONS ALL DIMENSIONS ARE IN MM GEN.TOLERANCE:+/-0.5 MM

ITE Grade AC-DC Power Supplies



Mechanical Drawing

FLS250 3 X 5 with Cover kit - Fan

NOTE:-

PLEASE REFER "FLS250 2.5X4.5 WITH 'L' CHANNEL" SPEC FOR CONNECTOR DETAILS ON PAGE NO.13.

