

Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of NCP18XH103D03RB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=NCP18XH103D03RB

NCP18XH103D03RB












Appearance & Shape







Features

- 1. Excellent solderability and high stability in environment
- 2. Excellent long time aging stability
- 3. High accuracy in resistance and B-constant
- 4. Flow / Reflow soldering possible
- 5. Same B-Constant in the same resistance in the three sizes (0805 size / 0603 size / 0402 size)

Easy to use smaller size in the circuits

- 6. Lead is not contained in the product.
- 7. UL/cULcertified product.(UL1434, File No. E137188)



Applications

Limited Usage Consumer Grade



Packaging Information

Packaging	Specifications	Standard Packing Quantity
RB	180mm Paper Tape	4000

1 of 3

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of NCP18XH103D03RB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=NCP18XH103D03RB

NCP18XH103D03RB



Specifications

Resistance (25°C)	10kΩ
Resistance Value Tolerance (at 25°C)	±0.5%
B-Constant (25/50°C)	3380K
B-Constant (25/50°C) Tolerance	±0.7%
B-Constant(25/80°C) (Reference Value)	3428K
B-Constant(25/85°C) (Reference Value)	3434K
B-Constant(25/100°C) (Reference Value)	3455K
Max. Voltage	5V
Maximum Operating Current (25°C)	0.1mA
Typical Dissipation Constant (25°C)	1mW/°C
Operating Temperature Range	-40°C to 125°C
Size Code (in mm)	1.6x0.8mm
Size Code (in inch)	0.6x0.3inch
Shape	SMD
Mass	0.0047g
MSL	1

2 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




Note: This datasheet may be out of date. Please download the latest datasheet of NCP18XH103D03RB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=NCP18XH103D03RB


NCP18XH103D03RB



Product Data







Maximum Operating Voltage Reduction Characteristics

3 of 3

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

