

Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of PRF15BB103RB6RC from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=PRF15BB103RB6RC

PRF15BB103RB6RC












Appearance & Shape





	Dimensions (mm)					
Part Number	L	W	T	e	g	
PRF03_RL	0.6±0.05	0.3±0.05	0.3±0.05	0.1 to 0.2		
PRF15_RC	1.0±0.05	0.5±0.05	0.5±0.05	0.1 to 0.4	0.3 min.	
PRF18_RB	1.6±0.15	0.8±0.15	0.8±0.15	0.1 to 0.6	-	
PRF21_RA	2.0±0.2	1.25±0.2	0.9±0.2	0.2 min.	0.5 min.	



Features

- 1. SMD type is helpful for miniaturizing circuits because of its small size and light weight.
- 2. Excellent thermal response due to small size
- 3. Solid-state construction provides excellent resistance to mechanical vibration and impact resistance.
- 4. Contactless operation provides noiseless operation.
- 5. UL/cULcertified product. (UL1434, File No. E137188)



Applications

Limited Usage	Consumer Grade
---------------	----------------



Packaging Information

Packaging	Specifications	Standard Packing Quantity
RC	180mm Paper Tape	10000

1 of 3

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





PRF15BB103RB6RC

Note: This datasheet may be out of date.

Please download the latest datasheet of PRF15BB103RB6RC from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=PRF15BB103RB6RC



Specifications

Max. Voltage	32V
Sensing Temperature	130℃
Sensing Temperature Tolerance	±3°C
Measure Condition of Sensing Temperature	at 4.7M ohm
Resistance (25°C)	10kΩ
Resistance Value Tolerance (at 25°C)	±50%
Operating Temperature Range	-20°C to 140°C
Size Code (in mm)	1.0x0.5mm
Size Code (in inch)	0.4x0.2inch
Shape	SMD
Mass	0.001g
MSL	1

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Product Search Data Sheet


Note: This datasheet may be out of date. Please download the latest datasheet of PRF15BB103RB6RC from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=PRF15BB103RB6RC


PRF15BB103RB6RC



Product Data



Resistance-Temperature Characteristics



Resistance-Temperature Charac. Range

3 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

