USB 3.0 AM to AM Cable

pro-signal






Specifications


USB Standard : USB 3.0 Contact Resistance : 3Ω Max.

Insulation Resistance : DC 300V/10ms, $10M\Omega$ Min.

Jacket Colour : Black

Diagram





No	Description		Unit
1	[28AWG×(7/0.127TC)+EAM]×2P+[28AWG×(7/0.127TC)+A]×1P+28AWG(7/0.127TC)×2C+AEB(16/5/0.12AL 65%) OD:5.5mm Black PVC Mark E342987 AWM styll 2725 80°C 30V VW-1; Super High speed USB Revision 3.0		m
2	USB 3.0 A(M) 9P Blue insulation Pin plated gold 5μ″		
3	USB 3.0 A(M) Shell plated nickel after 2		Pcs
4	USB 3.0 A(M) Shell plated nickel before	USB 3.0 A(M) Shell plated nickel before	
5	PVC 45P Black		g
6	USB 3.0 A(M) Clip	2	Pcs

Part Number Table

	Description	L ±T	Part Number
		1000 ±20mm	20mm CAC250039
	USB 3.0 AM to AM Cable, Black	1800 ±30mm	CAC250040
		3000 ±40mm	40mm CAC250041

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

