


# midSMD Series



### **Agency Approvals**

AGENCY	AGENCY FILE NUMBER
c 🔊 us	E74889
SP:	78165
${\bf \Delta}$	72161778 72161795

### Description

The midSMD series provides surface mount overcurrent protection for applications where space is at a premium and resettable protection is desired.

#### Features

- Broadest range of resettable devices available in industry
- Low resistance
- Small 2018 footprint
- Fast time-to-trip
- RoHS complaint, lead-free and halogen-free

#### Applications

• Computer

• Multimedia

Mobile Electronics and Batteries

• Telephone and broadband

HF Rohs 😥 🕅 us 🚱 🛆

- Automotive
- Industrial controls
- Battery

#### **Additional Information**

• Portable electronics

• Game machines



Resources



### **Electrical Characteristics**

Part	l <sub>H</sub>	Ι <sub>τ</sub>	V <sub>MAX</sub>	I <sub>MAX</sub>	P <sub>D MAX</sub>	Max Tin	ne-to-trip	R <sub>MIN</sub>	R <sub>1MAX</sub>
Number	(A)	(A)	(V <sub>DC</sub> )	(A)	(VV)	(A)	(s)	(Ω)	(Ω)
midSMD Series — Size 5050mm/2018mils									
SMD030F-2018	0.30	0.80	60	20	1.50	1.50	1.50	0.500	2.30
decaSMDC050F/60	0.55	1.10	60	10	1.00	8.00	0.10	0.200	1.10
SMD100F-2018	1.10	2.20	15	40	1.40	8.00	0.50	0.100	0.40
SMD150F-2018	1.50	3.00	15	40	1.80	8.00	1.00	0.070	0.18
SMD200F-2018	2.00	4.20	6	40	1.50	8.00	3.00	0.048	0.10

#### Notes:

 $\rm I_{\rm H}$  ~ : Hold current: maximum current device will pass without interruption in 20°C still air.

I<sub>T</sub> : Trip current: minimum current that will switch the device from low resistance to high resistance in 20°C still air.

 $\mathrm{V}_{\scriptscriptstyle MAX}~$  : Maximum continuous voltage device can withstand without damage at rated current.

I<sub>MAX</sub> : Maximum fault current device can withstand without damage at rated voltage.

 $\rm P_{\rm \scriptscriptstyle D}$  ~~ : Power dissipated from device when in the tripped state in 20°C still air.

 $R_{\text{MIN}}$  : Minimum resistance of device as supplied at 20°C unless otherwise specified.

 $\rm R_{1MAX}$  : Maximum resistance measured one hour post-trip or post-reflow at 20°C.

# PolySwitch<sup>®</sup> Resettable PTCs


Surface Mount > midSMD Series



#### **Temperature Rerating**


	Maximum Ambient Temperature										
Part Number	-40°C	-20°C	0°C	20°C	25°C	40°C	50°C	60°C	70°C	80°C	85°C
Hold Current (A)											
midSMD Series — Size 5050mm/2018mils											
SMD030F-2018	0.48	0.42	0.35	0.30	0.28	0.24	0.21	0.17	0.15	0.12	0.10
decaSMDC050F/60	1.00	0.85	0.70	0.55	0.53	0.45	0.40	0.35	0.30	0.25	0.23
SMD100F-2018	1.59	1.43	1.20	1.10	1.03	0.94	0.85	0.72	0.69	0.61	0.57
SMD150F-2018	2.21	1.97	1.70	1.50	1.43	1.26	1.15	1.00	0.91	0.79	0.73
SMD200F-2018	2.81	2.54	2.27	2.00	1.93	1.73	1.59	1.46	1.32	1.19	1.12

### **Temperature Rerating Curve**





### Typical Time-to-Trip Curves at 20°C



Terminal Pad Material	100% Matte Tin with Nickel Underplate
Soldering Characteristics	ANSI/J-STD-002 Category 3
Solder Heat Withstand	per IEC-STD 68-2-20, Test Tb, Section 5, Method 1a
Flammability Resistance         per IEC 695-2-2 Needle Flame Test for 20 seconds	

#### **Environmental Specifications**

Test	Test Method	Conditions	Resistance Change		
Storage Life	PS300, Section 5.3.2	60°C, 1000 hrs 85°C, 1000 hrs	±3% typ ±3% typ		
Humidity Aging	PS300, Section 5.3.1 85°C, 85% R.H., 100 hrs		±1.2% typ		
Thermal Shock	MIL-STD-202, Method 107G	85°C, -40°C (20 Times) 125°C, -55°C (10 Times)	-33% typ -33% typ		
Vibration	MIL-STD-883C	per MIL-STD-883C	No Change		
olvent Resistance PS300, Section 5.2.2		Freon Trichloroethane Hydrocarbons	No Change No Change No Change		

Moisture Resistance Level	Level 2a, J-STD-020
Storage Conditions	40°C max, 70% RH max; devices should remain in original sealed bags prior to use. Devices may not meet specified values if these storage conditions are exceeded.

# PolySwitch<sup>®</sup> Resettable PTCs

Surface Mount > midSMD Series



#### **Dimension Figures**




Figure 1





Figure 2

### Dimensions

	Dimensions in Millimeters (Inches)												
Part Number	A	٩	E	3	(	0	[	)	E	Ξ	I	=	Figure
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	
midSMD Series — Size 5050mm/2018mils													
SMD030F-2018	4.72 (0.186)	5.44 (0.214)	_	1.78 (0.070)	4.22 (0.166)	4.93 (0.194)	0.25 (0.010)	0.36 (0.014)	0.25 (0.010)	0.36 (0.014)	0.30 (0.012)	0.46 (0.018)	2
decaSMDC050F/60	4.70 (0.185)	5.31 (0.209)	0.63 (0.025)	0.89 (0.035)	4.19 (0.165)	4.81 (0.189)	0.25 (0.010)	0.95 (0.040)	0.25 (0.010)	_	_	_	1
SMD100F-2018	4.72 (0.186)	5.44 (0.214)	_	1.52 (0.060)	4.22 (0.166)	4.93 (0.194)	0.25 (0.010)	0.36 (0.014)	0.25 (0.010)	0.36 (0.014)	0.30 (0.012)	0.46 (0.018)	2
SMD150F-2018	4.72 (0.186)	5.44 (0.214)	_	1.52 (0.060)	4.22 (0.166)	4.93 (0.194)	0.25 (0.010)	0.36 (0.014)	0.25 (0.010)	0.36 (0.014)	0.30 (0.012)	0.46 (0.018)	2
SMD200F-2018	4.72 (0.186)	5.44 (0.214)		1.52 (0.060)	4.22 (0.166)	4.93 (0.194)	0.25 (0.010)	0.36 (0.014)	0.25 (0.010)	0.36 (0.014)	0.30 (0.012)	0.46 (0.018)	2

#### **Recommended Pad Layout**




### Packaging and Marking Information

				Recommended Pad Layout Figures [mm (in)]			
Part Number	Tape and Reel Quantity	Standard Package	Part Marking	Dimension A (Nom)	Dimension B (Nom)	Dimension C (Nom)	Agency Recognition
		midSM	/ID Series — Si	ze 5050mm/2018	mils		
SMD030F-2018	4,000	20,000	A03F	4.60 (0.18)	1.50 (0.059)	3.40 (0.134)	UL, CSA, TÜV
decaSMDC050F/60	1,000	5,000	050F 60V	4.32 (0.17)	1.40 (0.055)	3.61 (0.142)	UL, CSA, TÜV
SMD100F-2018	4,000	20,000	A10F	4.60 (0.18)	1.50 (0.059)	3.40 (0.134)	UL, CSA, TÜV
SMD150F-2018	4,000	20,000	A15F	4.60 (0.18)	1.50 (0.059)	3.40 (0.134)	UL, CSA, TÜV
SMD200F-2018	4,000	20,000	A20F	4.60 (0.18)	1.50 (0.059)	3.40 (0.134)	UL, CSA, TÜV

© 2019 Littelfuse, Inc. Specifications are subject to change without notice. Revised: 06/05/19

#### **Solder Reflow Recommendations**

Profile Feature	Pb-Free Assembly
Average ramp up rate (Ts <sub>MAX</sub> to Tp)	3°C/s max
Preheat	
• Temperature min (Ts <sub>MIN</sub> )	150°C
• Temperature max (Ts <sub>MAX</sub> )	200°C
• Time (ts <sub>MIN</sub> to ts <sub>MAX</sub> )	60-120 s
Time maintained above:	
• Temperature (T <sub>L</sub> )	217°C
• Time (t <sub>L</sub> )	60-150 s
Peak/Classification temperature (Tp)	260°C
Time within 5°C of actual peak temperature	
Time (tp)	30 s max
Ramp down rate	3°C/s max
Time 25°C to peak temperature	8 min max



Note: All temperatures refer to topside of the package, measured on the package body surface.


#### **Solder Reflow**

- Recommended reflow method: IR, hot air, nitrogen.
- Recommended maximum paste thickness: 0.25mm (0.010in)
- Devices can be cleaned using standard methods and aqueous solvents.
- Experience has shown the optimum conditions for forming acceptable solder fillets occur when a reasonable amount of solder paste is placed underneath each device's termination. As such, we request that customers comply with our recommended solder pad layouts.
- Customer should validate that the solder paste amount and reflow recommendations meet its application.
- We request that customer board layouts refrain from placing raised features (e.g. vias, nomenclature, traces, etc.) underneath PolySwitch devices. It is possible that raised features could negatively impact solderability performance of our devices.

#### Rework

• Standard industry practices. (Please also avoid direct contact to the device.)

#### Part Ordering Number System



# PolySwitch<sup>®</sup> Resettable PTCs

Surface Mount > midSMD Series





#### **Tape and Reel Specifications**

	midSMD EIA 481-2	midSMD EIA 481-1
Description	SMD030F-2018 SMD100F-2018 SMD150F-2018 SMD200F-2018 SMD200F-2018	decaSMDC050F/60
W	16.0 ± 0.30	12.0 ± 0.30
Po	4.0 ± 0.10	4.0 ± 0.10
<b>P</b> <sub>1</sub>	8.0 ± 0.10	8.0 ± 0.10
P <sub>2</sub>	2.0 ± 0.10	2.0 ± 0.05
A <sub>0</sub>	5.11 ± 0.15	5.0 ± 0.1
B <sub>0</sub>	5.6 ± 0.23	5.4 ± 0.1
B <sub>1</sub> max	6.4	6.15
D <sub>0</sub>	1.5 + 0.10/00	1.55 ± 0.05
F	7.50 ± 0.10	5.50 ± 0.10
E,	1.75 ± 0.10	1.75 ± 0.10
E <sub>2</sub> min	14.25	10.25
T max	0.4	0.35
T₁ max	0.1	0.1
Ko	1.8 ± 0.15	1.7 ± 0.1
A max	330	330
N min	50	50
W1	16.4 + 2.0/00	16.4 + 2.0/00
W <sub>2</sub> max	22.4	22.4



#### **Tape and Reel Diagrams**







#### WARNING

- Users should independently evaluate the suitability of and test each product selected for their own application.
- Operation beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.
- These devices are intended for protection against damage caused by occasional overcurrent or overtemperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
- Contamination of the PPTC material with certain silicone-based oils or some aggressive solvents can adversely impact the performance of the devices.
- Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical
  procedures for electronic components.
- PPTC devices are not recommended for installation in applications where the device is constrained such that its PTC properties are inhibited, for example in rigid
  potting materials or in rigid housings, which lack adequate clearance to accommodate device expansion.
- Operation in circuits with a large inductance can generate a circuit voltage (Ldi/dt) above the rated voltage of the device.

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littlefuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <u>www.littlefuse.com/disclaimer-electronics</u>.