

Product Information

PET cloth tape for high abrasion protection of automotive harnesses

tesa® 51026 is a PET cloth tape with a solvent-free acrylic adhesive. It provides excellent abrasion protection of automotive harnesses and withstands high temperatures and demanding environmental conditions.

Its acrylic adhesive is compatible with new halogen-free cable jacketing materials (PE/PP) and provides enhanced durability at high temperatures.

Main features:

- High abrasion resistance
- High temperature resistance
- Excellent cable compatibility
- Resistant to aging
- Can withstand environmental influences
- Can be used for manual and automatic application
- Flame retardant
- Fogging-free
- Halogen-free
- Tear-resistant
- Constant unwind force
- Flexible and smooth

Main Application

tesa® 51026 has been specially designed for bundling and wire protection against abrasion of automotive harnesses. The main application field is the engine compartment of a car, with demanding temperature-related and environmental conditions.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	PET cloth	• Abrasion resistance (10mm mandrel)	Class D (acc. to LV312)
• Total thickness	260 µm	• Abrasion resistance (5mm mandrel)	Class D (acc. to LV312)
• Type of adhesive	acrylic	• Flame resistance as composite	Class B (acc. to LV312)
• Elongation at break	40 %	• Unwind force (roll width ≤ 9mm)	5 N/roll (30 m/min)
• Tensile strength	275 N/cm	• Unwind force (roll width > 9mm)	11 N/roll (30 m/min)
• Temperature resistance min.	-40 °C	• Noise damping (decibel)	Class A (acc. to LV312)
• Temperature resistance (3000h)	150 °C		

Adhesion to

- steel 5.5 N/cm

tesa® 51026

Product Information



Additional Information

Standard widths: 9, 19, 25, 32 mm

Standard lengths: 25 m

- Most combinations of width and length are possible
- Further dimensions are available upon request
- Standard core diameter: 38 mm
- Applicable for red ring assembly aid

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=51026>