

# tesa® 4329 PV1



## Product Information

Finely creped paper mask tape

The product is thin and flexible and therefore suitable for all general masking applications, as well as oven drying applications up to a temperature of 70 °C.

### Main Application

- Masking
- Lacquering work
- Good flexibility for curves
- Can be used on painted metal, rubber, glass and chrome parts

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### Technical Data

- |                    |                       |                          |         |
|--------------------|-----------------------|--------------------------|---------|
| • Backing material | slightly-creped paper | • Elongation at break    | 10 %    |
| • Total thickness  | 125 µm                | • Tensile strength       | 33 N/cm |
| • Type of adhesive | natural rubber        | • Temperature resistance | 70 °C   |

#### Adhesion to

- steel 2.8 N/cm

#### Properties

- |                    |      |                     |      |
|--------------------|------|---------------------|------|
| • Hand tearability | ●●●● | • Sharp colour edge | ●●●● |
| • Easy to remove   | Yes  | • Conformability    | ●●●● |
| • Paint anchorage  | ●●●● |                     |      |

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

# tesa® 4329 PV1

## Product Information



### Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=04329>