

Characteristics

Parameter	Rating	Units
Blocking Voltage	600	V _P
Load Current, T _A =25°C:		
With 5°C/W Heat Sink	3.5	A _{rms} / A _{DC}
No Heat Sink	1.4	↑rms / ↑DC
On-Resistance (max)	0.75	Ω
Thermal Impedance, Junction-to-Case, θ_{JC}	0.3	°C/W

Features

- 3.5A_{rms} Load Current with 5°C/W Heat Sink
- Low 0.75Ω On-Resistance
- 600V_P Blocking Voltage
- 2500V_{rms} Input/Output Isolation
- Low Thermal Impedance: θ_{JC} = 0.3 °C/W
- Isolated, Low Thermal Impedance Ceramic Pad for Heat Sink Applications
- Low Drive Power Requirements
- No EMI/RFI Generation
- Flammability Rating UL 94 V-0


Applications

- Industrial Controls / Motor Control
- Robotics
- Medical Equipment—Patient/Equipment Isolation
- Instrumentation
- Multiplexers
- Data Acquisition
- Electronic Switching
- I/O Subsystems
- Meters (Watt-Hour, Water, Gas)
- Transportation Equipment

Approvals

UL 508 Recognized Component: File E69938

Pin Configuration





Description

IXYS Integrated Circuits brings OptoMOS® technology, reliability and compact size to a new family of high-power Solid State Relays.

As part of this family, the CPC1979J single-pole normally open (1-Form-A) Solid State Power Relay is rated for up to 3.5A_{rms} continuous load current with a 5°C/W heat sink.


The CPC1979J employs optically coupled MOSFET technology to provide 2500V_{rms} of input to output isolation. The optically coupled outputs, that use patented OptoMOS architecture, are controlled by a highly efficient infrared LED. The combination of low on-resistance and high load current handling capability makes this relay suitable for a variety of high performance switching applications.

The unique ISOPLUS-264 package pioneered by IXYS enables Solid State Relays to achieve the highest load current and power ratings. This package features a unique IXYS process in which the silicon chips are soft soldered onto the Direct Copper Bond (DCB) substrate instead of the traditional copper leadframe. The DCB ceramic, the same substrate used in high power modules, not only provides 2500V_{rms} isolation but also very low junction-to-case thermal impedance (0.3 °C/W).

Ordering Information

Part	Description		
CPC1979J	ISOPLUS-264 Package (25 per tube)		

Switching Characteristics





1 Specifications

1.1 Absolute Maximum Ratings @ 25°C

Parameter	Symbol	Rating	Unit
Blocking Voltage	V_L	600	V_{P}
Reverse Input Voltage	V_R	5	V
Input Control Current, Continuous	I _F	100	mA
Peak (10ms)		1	Α
Input Power Dissipation	P _{IN}	150	mW
Isolation Voltage (Input to Output)	V _{ISO}	2500	V_{rms}
Operating Temperature	T _A	-40 to +85	°C
Storage Temperature	-	-40 to +125	°C

Absolute maximum ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Typical values are characteristic of the device at +25°C, and are the result of engineering evaluations. They are provided for information purposes only, and are not part of the manufacturing testing requirements.

1.2 Electrical Characteristics @ 25°C

Parameter	Conditions	Symbol	Minimum	Typical	Maximum	Units
Output Characteristics						
Load Current ¹						
Peak	$t \leq 10 \text{ms}$				20	A_P
Continuous	No Heat Sink	IL			1.4	
Continuous	T _C =25°C		-	-	14.5	A _{rms} / A _{DC}
Continuous	T _C =99°C	I _{L(99)}			1.7	
On-Resistance ²	I _F =10mA, I _L =1A	R _{ON}	-	0.59	0.75	Ω
Off-State Leakage Current	V _L =600V _P	I _{LEAK}	-	-	1	μА
Switching Speeds						
Turn-On	I _F =20mA, V _I =10V	t_{on}	-	8	25	
Turn-Off	1F=201171, VL=10V	t _{off}	-	0.2	5	ms
Output Capacitance	I _F =0mA, V _L =25V, f=1MHz	C _{out}	-	700	-	pF
Input Characteristics	-		-		*	
Input Control Current to Activate 3	I _L =1A	I _F	-	-	10	mA
Input Control Current to Deactivate	-	I _F	0.6	-	-	mA
Input Voltage Drop	I _F =10mA	V _F	0.9	1.35	1.56	V
Reverse Input Current	V _R =5V	I _R	-	-	10	μА
Input/Output Characteristics						
Capacitance, Input-to-Output	V _{IO} =0V, f=1MHz	C _{IO}	-	1	-	pF

¹ Higher load currents possible with proper heat sinking.

² Measurement taken within 1 second of on-time.

 $^{^3}$ For applications requiring high temperature operation (T_C > 60°C) a minimum LED drive current of 20mA is recommended.



Thermal Characteristics

Parameter	Conditions	Symbol	Rating	Units
Thermal Impedance (Junction to Case)	-	θЈС	0.3	°C/W
Thermal Impedance (Junction to Ambient)	Free Air	$\theta_{\sf JA}$	33	°C/W
Junction Temperature (Operating)	-	TJ	-40 to +100	°C

2.1 Thermal Management

Device high current characterization was performed using Kunze heat sink KU 1-159, phase change thermal interface material KU-ALC 5, and transistor clip KU 4-499/1. This combination provided an approximate junction-to-ambient thermal impedance of 12.5°C/W.

2.2 Heat Sink Calculation

Higher load currents are possible by using lower thermal impedance heat sink combinations.

Heat Sink Rating

$$\theta_{CA} = \frac{(T_J - T_A) I_{L(99)}^2}{I_I^2 - P_{D(99)}} - \theta_{JC}$$

 $T_{J} = Junction Temperature (°C), T_{J} \le 100°C *$

T_A = Ambient Temperature (°C)

 $I_{L(99)}^{\wedge}$ = Load Current with Case Temperature @ 99°C (A_{DC})

 $I_L^{(s)}$ = Desired Operating Load Current (A_{DC}), $I_L \le I_{L(MAX)}$ θ_{JC} = Thermal Impedance, Junction to Case (°C/W) = 0.3°C/W

 θ_{CA}^{-1} = Thermal Impedance of Heat Sink & Thermal Interface Material , Case to Ambient (°C/W)

 $P_{D(99)}^{-}$ = Maximum power dissipation with case temperature held at 99°C = 3.33W

NOTE: The exposed surface of the DCB substrate is not to be soldered.


3 R11 www.ixysic.com


^{*} Elevated junction temperature reduces semiconductor lifetime.





3 Performance Data*


Unless otherwise specified, all performance data was acquired without the use of a heat sink.

































^{*}Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C.

















^{*}Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C.



4 Manufacturing Information

4.1 ESD Sensitivity



This product is ESD Sensitive, and should be handled according to the industry standard JESD-625.

4.2 Soldering Profile

For through-hole devices, the maximum and minimum peak solder temperature limits (T_p) and the device maximum total dwell time through all solder waves is provided in the table below. Dwell time is the interval the device pins are at or above the minimum peak solder temperature. Body temperature of the device must not exceed the limit given in the table below at any time during the soldering process.

Device	Solder Temperature (T _p)		Body Temperature	Dwell Time	Wave Cycles
501100	Minimum	Maximum	Body remperature	Buon rinio	naro o joios
CPC1979J	235°C	260°C	245°C	10 seconds*	1

*Total cumulative duration of all waves.

NOTE: The exposed surface of the DCB substrate must not be soldered.

4.3 Board Wash


IXYS Integrated Circuits recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include but are not limited to: using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to halide flux or solvents.







4.4 Mechanical Dimensions



NOTES:

- 1. Controlling dimension: Inches.
- Metallized external surface of DCB substrate maintains 2500V ms isolation to device internal structure and all external pins.

For additional information please visit our website at: https://www.ixysic.com



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at https://www.littelfuse.com/disclaimer-electronics.

Specification: DS-CPC1979J-R11 ©Copyright 2020, Littelfuse, Inc. All rights reserved. Printed in USA. 11/12/2020