




Terminals & Splices > Splices



Splice Product Type: **Splice**

Wire Size: **1.25 – 2 mm²**

Sealable: **No**

Splice Features: **Standard**

Features

Product Type Features

Splice Product Type	Splice
Sealable	No
Splice Type	Parallel Splice
Serrated	Yes
Splice Accessory Type	Splice
Splice Wire/Cable Type	Copper
Wire Insulation Support Retention Type	Insulation Support

Body Features

Insulation Sleeve Material	Vinyl
Weight per Piece	.904 g
Plating Material	Tin
Splice Features	Standard
Splice Material	Copper
Primary Product Color	Blue

Contact Features

Contact Plating Material	Tin
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Accepts Wire Insulation Diameter Range	4.32 mm[.17 in]
Overall Product Length	19.3 mm[.76 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	90 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Other

Military Category	No
-------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 34133
SPLICE,PG PARA 16-14




TE Part # 5-1377173-6
SMP 0-0034134-0


Also in the Series | PLASTI-GRIP




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(11)



Ring Terminals & Spade Terminals(208)



Splices(45)

Customers Also Bought



TE Part #7-2176231-0
3522 7K5 1% 3W



TE Part #130568
PG SPADE



TE Part #34136
SPLICE,PG PARA 12-10



TE Part #292317-4
STD USB TYPE B, R/A, T/H





TE Part #926897-1
[UNIV.M-N-L.PIN](#)



TE Part #206150-2
[CPC PLUG,SZ 23-37,SMALL PACK](#)



TE Part #2176400-5
[3540 1R5 1%](#)



TE Part #004487-000
[B-150-11-S](#)

Documents

Product Drawings

[SPLICE,PG PARA 16-14](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_34134_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_34134_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_34134_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English

[UL Report](#)



English