


Surge Protection - SD22

SD22 Series, 950W Discrete Unidirectional TVS Diode

HF ROHS PO GREEN



Pinout and Functional Block Diagram



Description

The Unidirectional SD22 Series is designed for use in electronic equipment for low speed and DC applications. It will protect any sensitive equipment from damage due to electrostatic discharge (ESD) and other transient events. The SD22 series can safely absorb repetitive ESD strikes at ± 30 kV (contact discharge, IEC 61000-4-2) without performance degradation and safely dissipate 27A of 8/20µs induced surge current (IEC 61000-4-5 2nd edition) with very low clamping voltages.

Features

- ESD, IEC 61000-4-2, ±30kV contact, ±30kV air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, IEC 61000-4-5 2nd edition, 27A (t_p=8/20µs)
- Low clamping voltage
- Low leakage current
- Small SOD323 package fits 0805 footprints
- Moisture Sensitivity Level(MSL -1)
- Halogen-free, lead-free and RoHS-compliant

Applications

- Switches / Buttons
- Test Equipment / Instrumentation
- Point-of-Sale Terminals
- Medical Equipment
- Notebooks / Desktops / Servers
- Computer Peripherals
- Automotive applications

Life Support Note: Not Intended for Use in Life Support or Life Saving Applications The products shown herein are not designed for use in life sustaining or life saving

applications unless otherwise expressly indicated. ©2020 Littlefuse, Inc. Specifications are subject to change without notice. Revision: 09/02/20

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
P _{pk}	Peak Pulse Power (t _p =8/20µs)	950	W
T _{op}	Operating Temperature	-40 to 150	°C
T _{STOR}	Storage Temperature	-55 to 150	°C

Notes:

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Electrical Characteristics (T_{OP}=25°C)


Parameter	Symbol	Test Conditions	Min	Тур	Max	Units
Reverse Standoff Voltage	V _{RWM}	I _R =1µA			22.0	V
Breakdown Voltage	V _{BR}	I _R =1mA	23.0			V
Reverse Leakage Current	LEAK	V _R =22V		0.02	0.5	μΑ
Clamp Voltage ¹	V _c	I _{pp} =27A, t _p =8/20μs, Fwd		35.5		V
Dynamic Resistance ²	R _{DYN}	TLP, t _p =100ns, I/O to Ground		0.13		Ω
Peak Pulse Current	l _{pp}	t _p =8/20µs			27	A
ESD Withstand Voltage ¹	V _{esd} –	IEC 61000-4-2 (Contact Discharge)	±30			kV
		IEC 61000-4-2 (Air Discharge)	±30			kV
Diode Capacitance ¹	C _{I/O-GND}	Reverse Bias=0V, f=1MHz		160		pF

Note:

1. Parameter is guaranteed by design and/or component characterization.

2. Transmission Line Pulse (TLP) with 100ns width, 2ns rise time, and average window t1=70ns to t2= 90ns

Power Derating Curve




8/20µs Pulse Waveform






TVS Diode Arrays (SPA®Diodes)


Surge Protection - SD22



Clamp Voltage vs. I_{PP}




Positive Transmission Line Pulsing (TLP) Plot




Non-Repetitive Peak Pulse Power vs. Pulse Time 10 Peak Pulse Power-P_{pk} (kW) 0.1 ++++ 0.01 10 100 1000 Pulse Duration -tp(µs)

Negative Transmission Line Pulsing (TLP) Plot





IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage




Soldering Parameters


Reflow Cor	ndition	Pb – Free assembly	
Pre Heat	- Temperature Min (T _{s(min)})	150°C	
	- Temperature Max (T _{s(max)})	200°C	
	-Time (min to max) (t _s)	60 – 180 secs	
Average rai to peak	mp up rate (Liquidus) Temp (T_L)	3°C/second max	
T _{S(max)} to T _L ·	- Ramp-up Rate	3°C/second max	
	- Temperature (T _L) (Liquidus)	217°C	
Reflow	- Temperature (t _L)	60 – 150 seconds	
Peak Tempe	erature (T _P)	260 ^{+0/-5} °C	
Time within 5°C of actual peak Temperature (t _p)		20 – 40 seconds	
Ramp-down Rate		6°C/second max	
Time 25°C to peak Temperature (T _P)		8 minutes Max.	
Do not exc	eed	260°C	


Ordering Information Part Number Package Min. Order Oty. SD22-01FTG SOD323 3000

Part Numbering System



IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage






Product Characteristics

Lead Plating	Matte Tin
Lead Material	Copper Alloy
Lead Coplanarity	0.0004 inches (0.102mm)
Substrate Material	Silicon
Body Material	Molded Compound
Flammability	UL Recognized compound meeting flammability rating V-0

Part Marking System




©2020 Littelfuse, Inc. Specifications are subject to change without notice. Revision: 09/02/20





TVS Diode Arrays (SPA®Diodes)


Surge Protection - SD22

Package Dimensions -SOD323










Unit: ı	mm
---------	----

	SOD323				
Symbol	Millimeters		Inches		
	Min	Max	Min	Max	
Α	-	1.00	-	0.039	
A1	0.00	0.10	0.000	0.004	
A2	0.80	0.90	0.031	0.035	
b	0.25	0.35	0.010	0.014	
С	0.08	0.15	0.003	0.006	
D	1.20	1.40	0.047	0.055	
E	1.60	1.80	0.063	0.071	
E1	2.50	2.70	0.098	0.106	
L1	0.25	0.40	0.010	0.016	

Embossed Carrier Tape & Reel Specification - SOD323



Symbol	Millimeters
A0	1.36min/1.62max
B0	2.90+/-0.10
w	8.0+0.3/-0.10
D0	1.50+0.10
D1	ø1.00min/ø1.25max
E	1.75+/-0.10
E2	-
F	3.50+/-0.05
P0	4.00+/-0.10
Р	4.00+/-0.10
P1	2.00+/-0.05
К0	1.15min/1.45max
т	0.254+/-0.13

Product Disclaimer: Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. http://www.littelfuse.com/disclaimer-electronics.