

DESCO EUROPE



66408 - Statfree® T2 Plus Dissipative Roll, 1.5 mm x 0.6 m x 12.2 m, Gray

- **Dissipative Dual Layer ESD Worksurface**
Provides a worksurface that does not generate a static charge and will control the discharge rate from all conductors (including ESD susceptible items) that are placed on the surface.
- **NEW Nitrile Rubber Oil Resistant Compound**
Improved material compound limits oil absorption to improve electrical and physical properties through the lifespan of the material. May be used in soldering applications with flux and other chemicals.
- **Dissipative (1×10^6 to $<1 \times 10^9$ ohms Rp) Top Layer**
Slows charge removal; meets the minimum recommended worksurface requirement of IEC 61340-5-1.
- **Conductive ($<1 \times 10^6$ Rp) Bottom Layer**
Reduces the resistance to ground (Rg) from the top of the surface to the groundable point ground and allows the material to be used with ESD workstation monitors.
- **Ultraviolet (UV) Stabilizer Additives**
Stabilizes color retention, ensures ESD performance over time and eliminates surface layer deterioration resulting in cracking when the product is flexed.
- **Laser Engraved With ESD Protective Symbol, Specs, and Manufacturer Information**
Identifies ESD protective product for control & auditing purposes.
- **Lead-free RoHS compliant**
- **Made in the United States of America**