

Cable Tie

Mountable, Black

multicomp PRO

Features


- One piece non-releasable mounting cable ties manufactured in natural or black nylon 6.6
- These cable ties are available in lengths from 4" to our exclusive 48" strap. Cable ties will satisfy bundling requirements from 1/16" to 15" and loop tensile strengths from 18 to 175 pounds
- State-of-the-art robotic and raw material handling equipment assures product and material integrity throughout the manufacturing process. Overall quality is achieved through statistical analysis and quality driven operator objectives. It has attained Mil-Spec I-45208 quality ratings from a number of equipment manufacturers



Specifications

Cable Tie Length	: 370mm
Cable Tie Width	: 4.8mm
Cable Tie Material	: PA 6.6 (Polyamide)
Cable Tie Colour	: Black
Tensile Strength	: 0N/mm ²
Cable Bundle Diameter Min.	: 102mm
Cable Diameter Max.	: 102mm
Fixing Hole Diameter	: 4.6mm
Operating Temperature	: -40°C to +85°C
Tensile Strength	: 22kg

Diagram



NBS Smoke Generation for 6.6 Nylon

Simple Thickness (Inch)	Energy Source	Specific Optical Density	
		At Maximum Smoke Accumulation	At 2 Minutes
1/16	Radiant (2.5 watts/sq.cm)	13	0
1/8	Radiant Plus Flaming Gas Jets	26	1

Results provided by natural bureau of standards (NBS). Results may not be directly correlated with larger fires, such as burning buildings.

multicomp PRO

Cable Tie

Mountable, Black

Materials for Moulded Assembly Hardware

Property	ASTM Method	Test Condition	Unit	Moulded 6.6 Nylon
Tensile Strength	D638	+73°F; 50% RH	kpsi	11.2
Elongation at Break			%	≥ 300
Yield Strength			kpsi	8.5
Shear Strength	D732	Dry as Moulded (DAM)		9.6
Deformation under Load	D621	2,000 psi +122°F; DAM	%	1.4
IZOD Impact	D256	+73°F; 50% RH	ft lb/in	2.1
Tensile Impact Strength	D1822	+73°F; Long Specimen; DAM	ft lb/in ²	240
Melting Point	D789	Fisher - Johns	°F	491
Thermal Linear Expansion	D696	DAM	in/in/°F	4 × 10 ⁻⁵
Thermal Conductivity	-	DAM Conche-Fitch	BTU - in/h.ft ² .°F	1.7
Brittleness Temperature	D746	50% RH	°F	-85
Oxygen Index	D2863	DAM 50% RH	%O ₂	28 31

Test conducted on 1/4" specimens.

Temperature Index for Moulded Nylon

Material	Minimum Thickness (Inch)	Temperature Index		Hot Wire ignition (Seconds)
		Electrical (°C)	Mechanical w/o Impact (°C)	
6.6 Nylon	0.058	125	85	15

Temperature index is the temperature at which the specific property will decrease to one-half its original value after 60,000 hours exposure at that temperature.

Part Number Table

Description	Part Number
Cable Tie, Mountable, Black, 370mm	PP002113

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.