

physical. chemical. biological.



LFS1K0.1305.6W.B.010-6



For various conductivity measurement applications



Benefits & Characteristics




- Wide conductivity and temperature range
- Fast response time
- Optimal accuracy
- Resistance to various chemicals¹⁾

- Excellent long-term stability
- Integrated RTD for temperature measurement and / or compensation
- 4 electrode measurement²⁾
- 1) Aggressive media can influence the long term stability. Chemical resistance of the sensor in the end application must be tested by the customer

2) 2 electrode configuration available upon request

Illustration³⁾



3) For actual size, see dimensions

Technical Data

Conductivity range:	100 μS/cm to 200 mS/cm	
Cell constant ⁴⁾ :	typical 0.86 cm ⁻¹	
Nominal resistance:	1000 Ω at 0 °C	
Measurement frequency range:	100 Hz to 10 kHz	
Maximum excitation voltage (between pin 1 and pin 6):	< 0.7 Vpp (Electrolysis of the analyte has to be avoided)	
Operating temperature range:	-30 °C to +100 °C	
Temperature sensor:	Pt1000	
Temperature coefficient (Pt1000):	3850 ppm/K	
Measuring current (Pt1000) ⁵⁾ :	0.3 mA	
Temperature sensor accuracy (dependent on temperature range):	IEC 60751 F0.3 B (IST AG reference)	
Connection:	Pt/Ni wires, Ø 0.2 mm	
Dimensions (L x W x H / H2 in mm):	12.9 ±0.3 x 5.5 ±0.3 x 0.65 ±0.1 / 1.2 ±0.3	





physical. chemical. biological.











Temperature dependence of resistivity:

-50 °C to 0 °C 0 °C to 150 °C according to IEC 60751:

 $R(T) = R_0 \times (1 + A \times T + B \times T^2 + C \times (T-100) \times T^3)$

 $R(T) = R_0 \times (1 + A \times T + B \times T^2)$

A = $3.9083 \times 10^{-3} \times {}^{\circ}C^{-1}$

 $= -5.775 \times 10^{-7} \times {}^{\circ}C^{-2}$

 $C = -4.183 \times 10^{-12} \times {}^{\circ}C^{-4}$

 R_0 = resistance value in Ω at T = 0 °C

= temperature in accordance with ITS90

Storage temperature: -20 °C to +100 °C


4) Cell constant is strongly affected by external objects coming close to the front surface of the sensor

5) Self heating must be considered

Product Photo:



Pin Assignment



I: applied current V: measured voltage T: temperature sensor

Order Information

Description:	Item number:	Former main reference:
LFS1K0.1305.6W.B.010-6	103850	090.00072



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved