### 15-mm carbon / cermet through-hole potentiometer

The PT-15 and PTC-15 potentiometers offer control where frequent adjustment is required. The shaftless design allows for employment of different engagement mechanisms, such as a customized shaft, a motor control or a human interface adjustment. This potentiometer can also control variable outputs including frequency, change in motor speed or volume.



### **KEY FEATURES**

- Excellent performance (up to 3% linearity)
- Carbon or cermet resistive element
- ▶ Up to 38 mechanical detents for tactile feedback
- ▶ Up to 100.000 life cycles
- ▶IP54 protection
- ▶ Magazine packaging for automatic insertion available
- ▶ Polyester / Alumina substrate
- ▶ Wiper positioned at initial, 50% or fully clockwise
- Loose and assembled shaft and knobs
- ▶ Linear, logarithmic and antilogarithmic tapers
- Self extinguishable plastic (UL 94V-0) available
- ▶ SPDT switch and low torque version available

### **ELECTRICAL SPECIFICATIONS**

	PT-15 PTC-15							
Taper <sup>1</sup>	Lin, Log, Alog							
Range of values <sup>1</sup> Lin Log, Alog	(Decad. 1.0 - 2.0 - 2.2 - 2.5 - 4.7 - 5.0) 100Ω ≤ Rn ≤ 5MΩ 1KΩ ≤ Rn ≤ 5MΩ							
Tolerance <sup>1</sup> $100\Omega \le Rn \le 1M\Omega$ $1M\Omega < Rn \le 5M\Omega$	± 20% ± 30%							
Max. Voltage Lin Log, Alog	250 VDC 125 VDC							
Nominal power Lin Log, Alog	50°C (122°F) 0.25 W 0.12 W	70°C (158°F) 0.50 W 0.25 W						
Residual resistance <sup>1</sup>	≤ 0.5% Rn (5Ω min.)							
Equivalent noise resistance	≤ 3% Rn (3Ω min.)							
Operating temperature	-25°C to +70°C <sup>2</sup> (-13°F to + 158°F) -40°C to +90°C <sup>3</sup> (-40°F to + 194°F)							

1 Others available on request; 2 Up to 85°C depending on application.; 3 +120°C/+248°F upon request

### APPLICATIONS

- ► Appliance program selection
- Thermostat adjustment
- ► Timer and control relays
- Consumer electronics
- ▶ Power tool controls

► Test and measurement equipment

### 15-mm carbon / cermet through-hole potentiometer

MECHANICAL SPECIFICATIONS								
	PT-15	PTC-15						
Mechanical rotation angle <sup>1</sup>	265° ± 5°							
Electrical rotation angle	240° ± 20°							
Torque Rotational Stop	0.5 to 2.5 Ncm (0.7 to 3.4 in-oz) > 10 Ncm (>14 in-oz)							
Life <sup>2</sup> Up to 100k cycles Up to 10k cycles								
1 240° ± 5° available upon request. Endless rotation available: ST-15; 2 Others check availability								


### ENVIRONMENTAL TESTING

	Test method (CEI 393-1)	PT-15 ΔR(%)- Piher typical test results	PTC-15 ΔR(%) - Piher typical test results
Electrical life	1.000h at 50°C; 0.15W 1.000h at 70°C; 0.33W	±5% n/a	n/a ±2%
Mechanical life	1000 cycles at 10 to 15 cpm	±3 % (Rn < 1M )	±2%
Temperature coefficient	-25°C; +70°C -40°C; +90°C	±300 ppm/°C (Rn < 100K) n/a	n/a ±100 ppm/°C (Rn < 100K)
Thermal cycling	16h at 85°C and 2h at -25°C 16h at 90°C and 2h at -40°C	±2.5% n/a	n/a ±2%
Damp heat	500h at 40°C and 95% relative humidity (RH)	±5%	±2%
Vibration	2h each plane at 10Hz - 55Hz	±2%	±2%
Storage	6 month at 23°C ±2°C and 50% RH	±2.5%	±2%


Out of range values may not comply with these results. Standard test conditions: temperature:23°C ±2°C and 45% to 70% RH

#### RECOMMENDED CONNECTIONS

Recommended connection circuit for a position sensor or control application (voltage divider circuit electronic design).





### POWER RATING CURVE



### 15-mm carbon / cermet through-hole potentiometer

### HOW TO ORDER






1. Rotors: "Z" adjustment only available on "H"-mounting versions. Standard color for the "T" rotor: Orange.

2. Mounting method: "V24" terminals material: brass.

3.  $\Omega$ - Value: <u>XX</u>X - First two digits of  $\Omega$ -value 000 = CM = 45° switch SPDT version

XXXX - Number of zeros



4. Tolerance: for custom tolerance please check availability: info@piher.net

5. Life: "U" only available for low-torque versions and to be studied case by case.

6. Non-flammable according to UL 94V-0: housing, rotor and shaft. PTC-15 made of non-flammable material by standard.

7. Shaft/rotor color: Without shaft: only the rotor. With shaft: only the shaft.

8. Torque: Detent option not available with low torque models.

9. Packaging: Magazine packaging available for all H and V12, V02, V21, V15 and V23 mounting.




## 15-mm carbon / cermet through-hole potentiometer

STANDARD CONFIGURATION												
		PT-15		PTC-15								
Life		1.000 cycles										
Cut track		no		n/a								
Detents		none										
Packaging		bulk										
Shaft/thumb wheel		none	none									
Non-flammability		no		yes								
Housing color		black		cream								
Rotor color		white		cream								
Wiper Position		initial										
Torque		0.5 to 2.5 Ncm										
Terminal material		steel		brass								
Linearity		not controlled										
ROTORS Wiper shown at initial L Screw driver -	_		N t or thumbwheel		G t or thumbwheel							
	3.00 r		42.5° Wiper position	35 42.5° Wiper position								
Wiper shown positione N Hexagonal -	1	С	F	R T								
	~	<u><u>34</u> <u>04.4</u> <u>23</u></u>	90 97 97 97 97 97 97 97 98 8 8 9 9 9 9 9 9	900 <sup>4</sup> ,02 <sup>±0.05</sup> 900 <sup>4</sup> ,25 <sup>±0.05</sup> 90 <sup>4</sup> ,05 <sup>±0.05</sup> 90 <sup>4</sup> ,05 <sup>±0.05</sup> 90 <sup>4</sup> ,05 <sup>±0.05</sup> 90 <sup>4</sup> ,05 <sup>±0.05</sup>								
With inserted shaft		With inserted thumb	owheel									
W Adjustable from terminal side	X Adjustable from collector side	Adjustable from	Y n terminal side	Z Adjustable from collector side								
		6 AN R P			TI CONTRACTOR							
					$\cup \cup \cup$							


Download the STEP file here: https://www.piher.net/piher/?p=916

15-mm carbon / cermet through-hole potentiometer




15-mm carbon / cermet through-hole potentiometer

### MOUNTING METHOD




### **CRIMPED TERMINALS (DETAIL)**



STANDA	STANDARD RESISTANCE-VALUES AND TOLERANCES																												
Resistance Ω	100	200	220	250	470	500	1K	2K	2.2K	2.5K	4.7K	5K	10K	20K	22K	25K	47K	50K	100K	200K	220K	250K	470K	500K	1M	2M	2.5M	4.7M	5M
Order Code	101	201	221	251	471	501	102	202	222	252	472	502	103	203	223	253	473	503	104	204	224	254	474	504	105	205	255	475	505
Tolerance	erance 20%										30	)%																	

### SWITCH VERSIONS AVAILABLE WITH OR WITHOUT DETENTS




Contact Piher Sensing Systems for ordering information.

Standard Specification Power rating: 24V / 15mA ON position resistance: ≤ 5Ω Insulation resistance: ≥ 30MΩ

±0.2

S

15-mm carbon / cermet through-hole potentiometer




•Standard mechanical life is 500 cycles. •Long life versions are available upon request and have the following characteristics at T<sup>a</sup>: Potentiometers with 1 to 3 detents up to 10K cycles; Potentiometers with 4 and more detents up to 5K cycles •Please consult Piher Sensing Systems if unique non-overlapping values at each detent position or LOG/ALOG tapers are required. •Different output voltage values can be matched at each detent position [see next section]. •Detent torque can vary from 1.2 to 2.5 times the standard potentiometer torque. For all detents versions of more than 13 detents the detent torque will be 0.5 to 3.5 Ncm •For V02, V21, V12, V22, V18 and V24 mounting detent configuration will be studied case by case. •For more than 13 detents versions please contact Piher Sensing Systems.



## 15-mm carbon / cermet through-hole potentiometer

### **STEPPED OUTPUTS / CONSTANT VALUE ZONES**



#### **IMPROVED REPEATABILITY**

Constant value zones can be combined with strategically located mechanical detents to provide exact alignment between the electrical output (flat areas) and the mechanical detent position. This provides clear mechanical positions that are not only repeatable, but perfectly aligned electrical outputs at each of the (detent) angles. The detents also prevent output values from changing due to vibration or accidental rotor movements. The result is a higher level of precision in controlling lighting, temperature,
motor or other electronic control systems.
Systems.

Contact Piher Sensing Systems for ordering information.

#### POSITIONING



Special delivery positions available on request.

## PACKAGING Bulk




Dimensions (mm): 185x85x80

Without shaft: 400 units per box With thumbweel: 200 units per box With shaft: contact Piher Sensing Systems

### 15-mm carbon / cermet through-hole potentiometer

### SHAFTS AND THUMBWHEELS (TOP VIEW, FOR N, G AND T ROTOR TYPES)



### 15-mm carbon / cermet through-hole potentiometer

#### **AVAILABLE PACKAGING OPTIONS**

Mounting Type	Terminal Style	Mounting Method	Bulk	Magazine (35 units)	Embossed Tape
		H01	x	x	
		H05	x	x	
	Straight	H06	х	х	
Horizontal adjust		H25	х	х	
		H02	х	х	
	Crimped	H10	х	х	
		V02	x	х	х
		V12	х	х	
		V15	x	х	х
	Straight	V17	х		Upon request
		V18	x		
Vertical adjust		V20	x		
		V24	x		
		V21	x	х	x
	Crimped	V22	х		
	Crimped	V23	х	х	x
		V25	х		Upon request

Rotor Type X, W, Y, Z only in bulk packaging

#### **OUR ADVANTAGE**

- Leading-edge innovative position sensing solutions
  - ▷ Contactless (Hall-effect and Inductive Technology)
  - ▷ Contacting (Potentiometers, Printed Electronics)
- Engineering design-in support
- All our products can be customized to fit target application and customer requirement
- Capability to move seamlessly from development to true high-volume production
- A global footprint with global engineering and commercial support
- One-stop shop not limited to position sensors (temperature, pressure, gas,...) through group collaboration
- Flexibility and entrepreneurship of a medium-sized company with the backing of Amphenol Corporation









Please always use the latest updated datasheets and 3D models published on our website.

#### Disclaimer

Uscanner: The product information in this catalog is for reference purposes. Please consult for the most up to date and accurate design information. Piher Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Piher"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein. Piher disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which are high the there conducts.

apply to these products. No license, express apply to these products. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher. The products shown herein are not designed for use in medical, life-sustaining applications unless otherwise expressly indicated. Customers using or selling Piher products not expressly indicated for use in such applications do so entirely at their own risk and agree to tully indemnify Piher for any damages arising or resulting for such use or sale. Please contact authorized Piher personnel to obtain written terms and conditions regarding products designed for such applications. Product names and markings noted herein may be trademarks of their respective owners. Information contained in and/or attached to this catalog may be subject to export control regulations of the European Community. USA, or other countries. Each recipient of this document is responsible to ensure that usage and/or transfer of any information control regulations of the European Community. Note: All products / technologies are EARP9 Classified commodities. Exports from the United States are in accordance with the Export Administration Regulations. Diversion contrary to US law is prohibited.

tior



#### CONTACT

**Piher Sensing Systems** Polígono Industrial Municipal Vial T2, Nº22 31500 Tudela Spain

#### sales@piher.net

770	Europe:	+34 948 820 450
5	Americas:	+1 636 251 0855
7707	Asia Pacific:	+65 9641 8886
	India:	+91 9538 686 586

Page 10 of 10 **Amphenol Sensors**