EXL1V0606 High current molded inductor



Product features

- High current carrying capacity
- Low DCR, high efficiency
- · Magnetically shielded, low EMI
- · Soft saturation
- Inductance range from 1 μH to 10 μH
- Current range from 7.0 A to 19 A
- 7.4 mm x 7.1 mm footprint surface mount package in a 6.0 mm height
- Alloy powder core material
- Moisture Sensitivity Level (MSL) 1

Applications

- Voltage Regulator Module (VRM)
- Multi-phase regulators
- Point-of-load (POL) converters
- Desktop and server VRMs and EVRDs
- Base station equipment
- Battery power systems
- · Graphics cards
- Data networking and storage system

Environmental compliance and general specifications

- Storage temperature range (Component): -40 °C to +125 °C
- Operating temperature range: -40 °C to +125 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant





Product specifications

Part number⁵	OCL ¹ (μH) ± 20%	FLL² (µH) minimum	I _{rms} ³ (A) typic +20 °C rise	al +40 °C rise	I_ ⁴ (A)	DCR (mΩ) typical @ +25 °C	DCR (mΩ) maximum @ +25 °C	SRF (MHz) typical
EXL1V0606-1R0-R	1.0	0.56	15	19	16	3.9	4.29	37
EXL1V0606-1R5-R	1.5	0.84	13	16	14	5.1	5.61	31
EXL1V0606-2R2-R	2.2	1.23	11	14	12	7.0	7.80	26
EXL1V0606-3R3-R	3.3	1.84	9.0	12	10.5	11	12.1	24
EXL1V0606-4R7-R	4.7	2.63	8.0	11	9.5	13.1	14.4	22
EXL1V0606-5R6-R	5.6	3.13	7.5	10	9.0	14.3	15.8	17
EXL1V0606-6R8-R	6.8	3.8	7.0	9.0	8.7	18.9	20.8	15
EXL1V0606-8R2-R	8.2	4.59	6.0	8.0	8.0	22.5	24.8	14
EXL1V0606-100-R	10	5.6	5.0	7.0	6.8	26.6	29.3	12

1. Open circuit inductance (OCL) Test parameters: 100 kHz, 0.1 $V_{_{TMS'}}$ 0.0 Adc, +25 $^{\circ}\mathrm{C}$


2. Full load inductance (FLL) Test parameters: 100 kHz, 0.1 V_{ms} I_{sat}, +25 °C

3. Imms: Heat rated current (Imms) will cause the part temperature rise approximately ΔT of 40 °C. Circuit design,

component, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application. The part temperature (ambient + temp rise) should not exceed

+125 $^{\circ}\text{C}$ under worst case operating conditions.

Mechanical parameters, schematic, pad layout (mm)



Part marking: 0606, xxx= Inductance value in µH (R= Decimal point, if no R is present then last digit equals number of zeros), yyyy= Lot code All soldering surfaces to be coplanar within 0.1 millimeters

Tolerances are ± 0.3 millimeters unless stated otherwise

Dimensions of recommended PCB layout are reference only.

Pad layout tolerances are \pm 0.1 millimeters unless stated otherwise

Four terminal kelvin-clip recommended for DCR testing as shown in Figure 1.

Traces or vias underneath the inductor is not recommended.

4. I_{sat}: Peak current for approximately 30% rolloff @ +25 °C

5. Part number definition: EXL1V0606-xxx-R

EXL1V0606 = Product code and size xxx= inductance value in uH. R= decimal point.

If no R is present then third digit equals the number of zeros

-R suffix = RoHS compliant


6. Rated operating voltage: 15 V typical

 EXL1V0606-xxx-R
 7.2 ± 0.2
 6.9 ± 0.2
 5.8 ± 0.2
 5.3 ± 0.3
 1.4 ± 0.2
 2.6 ± 0.25

Packaging information (mm)

Drawing not to scale

Supplied in tape and reel packaging, 750 parts per 13" diameter reel (EIA-481 compliant)




W ± 0.30	16
F ± 0.1	7.5
E1 ± 0.1	1.75
P0 ± 0.1	4.0
P1 ± 0.1	12
P2 ± 0.1	2.0
D0 + 0.1/-0	1.5
D1 + 0.1/-0	1.5
A0 ± 0.1	7.6
B0 ± 0.1	7.3
K0 ± 0.1	6.3
T ± 0.05	0.5
P0 X 10 ± 0.2	40


Qualification testing


No. Test item		Reference standards	Test condition	Acceptable value/range	
1	Life	MIL-STD-202 Method 108	+125 °C + I_{rms} for 1000 hours	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%	
2	Load humidity	MIL-STD-202 Method 103	+85 °C/85% RH +I _{rms} for 1000 hours	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%	
3	Moisture resistance	MIL-STD-202 Method 106	7a & 7b included	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%	
4	Thermal shock	MIL-STD-202 Method 107	$\begin{array}{llllllllllllllllllllllllllllllllllll$		
5	Vibration	MIL-STD-202 Method 204	10 g, 12 hours (10 Hz ~ 2 kHz ~ 10 Hz for 20 minutes, 12 cycles each of 3 orientations)	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%	
6	Shock	MIL-STD-202 Method 213	Half-sine 50 g's, 11 ms	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%	
7	Bending	IEC 68-2-21	1.2 mm for 10 s a. Appearan b. ΔL/L<±10' d. ΔR/R<±15		
8	Solderability	J-STD-002D Method B	Preheat: $+150$ °C, 60 sec. $\geq 95\%$ of the t 245 ± 5 , Dip time: 4 ± 1 sec.covered with sDepth: completely cover the terminationcovered with s		
9	Resistance to soldering heat	MIL-STD-202 Method 210	+260 \pm 5 °C; 10 \pm 1 s a. Appearance b. $\Delta L/L{<}{\pm}10\%$ d. $\Delta R/R{<}{\pm}15\%$		
10	Terminal strength	AEC-0200-006	1 kg for 60 + 1 s	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%	


Inductance and temperature rise vs. current




EXL1V0606 High current molded inductor












Inductance and impedance vs. frequency curve, continued







Solder reflow profile




Table 1 - Standard SnPb solder (T_c)

Package thickness	Volume mm3 <350	Volume mm3 ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_c)

\	Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
	<1.6 mm	260 °C	260 °C	260 °C
	1.6 – 2.5 mm	260 °C	250 °C	245 °C
	>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Powerina Business Worldwide

Standard SnPb solder	Lead (Pb) free solder	
100 °C		
150 °C	200 °C	
60-120 seconds	60-120 seconds	
3 °C/ second max.	3 °C/ second max.	
183 °C 60-150 seconds	217 °C 60-150 seconds	
Table 1	Table 2	
20 seconds*	30 seconds*	
6 °C/ second max.	6 °C/ second max.	
6 minutes max.	8 minutes max.	
	100 °C 150 °C 60-120 seconds 3 °C/ second max. 183 °C 60-150 seconds Table 1 20 seconds* 6 °C/ second max.	

 * Tolerance for peak profile temperature (T_D) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com/electronics

© 2020 Eaton All Rights Reserved Printed in USA Publication No. 11192 BU-MC20169 November 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information

