Schottky Barrier Rectifiers Multicomp PRO

RoHS **Compliant**



Features

- Metal-Semiconductor junction with guard ring
- **Epitaxial construction**
- Low forward voltage drop, low switching losses
- High surge capability
- For use in low voltage, high frequency inverters free wheeling, and polarity protection applications
- The plastic material carries U/L recognition 94V-0

Mechanical Data

- Case:JEDEC DO--27, molded plastic
- Terminals: Axial lead, solderable per MIL-STD-202, method 208
- Polarity: Color band denotes cathode
- Weight: 0.041 ounces, 1.15 grams
- Mounting position: Any

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, halfwave, 60Hz, resistive or inductive load. For capacitive load, derate by 20%.

		1N5820	1N5821	1N5822	UNITS	
Maximum recurrent peak reverse voltage	VRRM	20	30	40		
Maximum RMS voltage	VRMS	14	21	28	V	
Maximum DC blocking voltage	VDC	20	30	40		
Maximum average forward rectified current 9.5mm lead length, @TA=75°C	lf(AV)	3			- А	
Peak forward surge current 8.3ms single half -sine-wave superimposed on rated load	İFSM	80				
Maximum instantaneous forward voltage @ 3A (Note 1) @ 9.4A	VF	0.475 0.85	0.5 0.9	0.525 0.95	٧	
Maximum reverse current @TA=25°C at rated DC blocking voltage @TA=100°C	lR	2 20		mA		
Typical junction capacitance (Note2)	Сл	210	165		pF	
Typical thermal resistance (Note3)	Reja	20			°C	
Operating junction temperature range	TJ	- 55 to + 125				
Storage temperature range	Тѕтс	- 55 to + 150				


- NOTE: 1. Pulse test: 300 µs pulse width,1% duty cycle.
 - 2. Measured at 1MHZ and applied reverse voltage of 4V DC.
 - 3. Thermal resistance junction to ambient



Schottky Barrier Rectifiers multicomp PRO




DO - 27




Dimensions: Millimetres

FIG.1 - FORWARD DERATING CURVE




LEAD TEMPERATURE, °C

FIG.2 - PEAK FORWARD SURGE CURRENT




NUMBER OF CYCLES AT 60Hz

FIG.3 - TYPICAL INSTANTANEOUS FORWARD **CHARACTERISTICS**



INSTANTANEOUS FORWARD VOLTAGE, VOLTS

FIG.4 - TYPICAL JUNCTION CAPACITANCE



REVERSE VOLTAGE, VOLTS

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Page <2> 27/06/22 V1.0