Thin Film High Power AlN Chip

TFHP Series

PROVISIONAL

Features:

- Power rating 6W in 2512 size
- Power rating 2W in 1206 size
- Aluminium nitride substrate
- Large termination soldering area
- Precision to 0.1%, 25ppm/°C





RoHS

All parts are Pb-free and comply with EU Directive 2011/65/EU amended by (EU) 2015/863

Electrical Data

	1206	2512		
W	2	6		
V	10	100		
Ω	50R to 30K1			
%	0.1, 0.25, 0.5, 1			
ppm/°C	25,	50		
	E24 8	& E96		
°C	-55 tc	+155		
	W V Ω % ppm/°C	1206 W 2 V 10 Ω 50R to % 0.1, 0.2 ppm/°C 25, °C -55 to		

Note: 1. Dependent on mounting conditions.

Physical Data

Dimensions in mm and weight in mg						C C	
	L	w	Т	А	С	Wt. nom.	
1206	3.05 ±0.2	1.55 ± 0.2	0 / 2 + 0 15	1.2 ± 0.2	0.5 ± 0.15	11.0	A
2512	6.3 ± 0.2	3.1 ± 0.2	0.45 ± 0.15	1.6 ± 0.25	0.7 ± 0.25	42.3	L FA-W
Recommended mounting pad dimensions in mm							c
	A B C				2		
1206	1206 0.6		1.9		1.8		ва
2512	2512 2.77 2.31		3.2		┝═┾╍┈┥		

Construction

A thin-film material is selectively deposited on an aluminium nitride substrate together with metallic contacts at each end of the resistor. The unadjusted resistors are heat treated to give the required TCR and stability, then a precisely controlled laser trim process adjusts the resistance value. Epoxy protection is applied, and wrap-around terminations are added and tin (Sn) plated. Each resistor is measured immediately before packing into tape.

Marking

TFHP resistors are marked white on black with 3 or 4 characters indicating ohmic value.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TFHP Series PROVISIONAL



Performance Data

Test Method		_	Maximum	
Load Life	1000 hours, cyclic load P_r at $T_A = 70^{\circ}C$	±ΔR%	1	
Short Term Overload	Lesser of 6.25 x P _r or 2 x LEV for 2 s	±ΔR%	0.5	
Damp Heat with Load	1000 hours, cyclic load P _r at 40°C, 90-95%RH	±ΔR%	0.4	
Low Temperature Operation	1 hour at -55°C, 45 minutes P _r	±ΔR%	0.2	
High Temperature Exposure	1000 hours at +155°C	±ΔR%	0.2	
Thermal Shock	100 cycles, -55 to +155°C	±ΔR%	0.2	
Resistance to Solder Heat	260 ± 5°C, 10 ± 1s	±ΔR%	0.2	
Solderability	245 ± 5°C, 3s	-	≥95% coverage	
Insulation Resistance	100V _{dc} , 60s		≥10G	

Thermal Performance Data



Packaging

TFHP resistors are packed in tape which is paper for 1206 and plastic for 2512, on 178mm reels. For full details of tape and reel dimensions see https://www.ttelectronics.com/ttelectronics/media/productfiles/applicationnotes/ps001-packing-of-general-purpose-chip-resistors.pdf

Ordering Procedure

Example: TFHP2512D-1K54FT4 (2512, 25ppm/°C, 1.54 kilohms ±1%, Pb-free)

T F H P 2 5 1 2 D - 1 K 5 4 F T 4							
1		2	3	4		56	
1	2	3	4	5	6		
Туре	Size	TCR	Value	Tolerance	Packing		
TFHP	1206	D = ±25ppm/°C	E24 or E96	B = ±0.1%	T5	1206 5000/r	eel
	2512	C = ±50ppm/°C	3/4 characters	C = ±0.25%	Т4	2512 4000/r	eel
			R = ohms	D = ±0.5%			
			K = kilohms	F = ±1%			

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.