D-101-00 - ACTIVE

Raychem

TE Internal #: 620002-000 SolderSleeve Shield Terminators, Cable Terminator / Shield Terminator / Wire Terminator, .18in [4.57mm] Expanded Inside View on TE.com >



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: Cable Terminator, Shield Terminator, Wire Terminator

Operating Temperature (Max): 150 °C

Expanded Inside Diameter (Min): 4.57 mm [.18 in]

Recovered Inside Diameter (Max): 2.54 mm [.1 in]

Pre-Installed Lead: No

Features

Product Type Features

SolderSleeve Shield Terminator Product Type

Cable Terminator, Shield Terminator, Wire Terminator

Configuration Features

Pre-Installed Lead

No

Dimensions

Expanded Inside Diameter (Min)	4.57 mm[.18 in]
Recovered Inside Diameter (Max)	2.54 mm[.1 in]
Usage Conditions	
Operating Temperature (Max)	150 °C
Wire Temperature (Max)	125 °C
Product Compliance For compliance documentation, visit the product page on TE.com>	
•	Not Compliant
For compliance documentation, visit the product page on TE.com>	Not Compliant Not Compliant
For compliance documentation, visit the product page on TE.com> EU RoHS Directive 2011/65/EU	

D-101-00

SolderSleeve Shield Terminators, Cable Terminator / Shield Terminator / Wire Terminator, .18in [4.57mm] Expanded Inside



SVHC > Threshold:

Pb (37% in Solder)

Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Halogen Content

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CJ2087-000 HL2010E-KIT-120V

Customers Also Bought



D-101-00

SolderSleeve Shield Terminators, Cable Terminator / Shield Terminator / Wire Terminator, .18in [4.57mm] Expanded Inside







Documents

Product Drawings D-101-00

English

Datasheets & Catalog Pages Raychem Electrical Interconnect Products

English

Product Specifications

Product Specification

English