

LED PANEL MOUNT INDICATOR

PROMINENT BEZEL, DC OPERATION, WIRE LEADS

MOUNTING HOLE, Ø 8

PART NO.	COLOR	VOLTAGE V _{OP} [V] DC	CURRENT I _{OP typ.} [mA] DC	LUMINOUS INTENSITY I _{v typ.} [mcd]	DOMINANT WAVELENGTH λ _D [nm]
SATIN CHROME BEZEL					
WL-19W402510152	GREEN	12V	20	60	568
WL-19W402520152	YELLOW	12V	20	80	588
WL-19W402530152	RED	12V	20	80	625
WL-19W402570152	BLUE	12V	20	90	466
WL-19W4025W0152	WHITE	12V	20	450	*
WL-19W403510152	GREEN	24V	14	40	568
WL-19W403520152	YELLOW	24V	14	60	588
WL-19W403530152	RED	24V	14	60	625
WL-19W403570152	BLUE	24V	14	60	446
WL-19W4035W0152	WHITE	24V	14	300	*
WL-19W404510152	GREEN	28V	11	45	568
WL-19W404520152	YELLOW	28V	11	45	588
WL-19W404530152	RED	28V	11	45	625
WL-19W404570152	BLUE	28V	11	50	446
WL-19W4045W0152	WHITE	28V	11	250	*

*Chromaticity coordinates x = 0.31 y = .032


NOTES

- Maximum panel thickness 4mm
- Storage temperature
T_{STG}: -25°C – +80°C
- Ambient temperature
T_A: -20°C – +60°C
- DC operation only
- Voltage tolerance
V_{OP}: ±10%
- Electro-optical ratings at
T_A=25°C
- Degree of protection: IP67 in accordance to DIN EN 60529 when using the supplied gasket
- Mounting hole
8 + 0.2mm
- 152mm PVC insulated wire leads, 24 AWG stranded tinned copper
- Red wire is anode (+)
Black wire is cathode (-)
- Due to production tolerances, slight color variations may be detected within individual consignments
- Supplied with mounting hardware; 1) gasket, 2) spring washer, and 3) M8 nut

CERTIFICATIONS

RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

wamco
LIGHTING

LED PANEL MOUNT INDICATOR

PROMINENT BEZEL, DC OPERATION, WIRE LEADS

MOUNTING HOLE, Ø 8

PART NO.	COLOR	VOLTAGE V _{OP} [V] DC	CURRENT I _{OP typ.} [mA] DC	LUMINOUS INTENSITY I _{v typ.} [mcd]	DOMINANT WAVELENGTH λ _D [nm]
BLACK CHROME BEZEL					
WL-19W412510152	GREEN	12V	20	60	568
WL-19W412520152	YELLOW	12V	20	80	588
WL-19W412530152	RED	12V	20	80	625
WL-19W412570152	BLUE	12V	20	90	466
WL-19W4125W0152	WHITE	12V	20	450	*
WL-19W413510152	GREEN	24V	14	40	568
WL-19W413520152	YELLOW	24V	14	60	588
WL-19W413530152	RED	24V	14	60	625
WL-19W413570152	BLUE	24V	14	60	446
WL-19W4135W0152	WHITE	24V	14	300	*
WL-19W414510152	GREEN	28V	11	45	568
WL-19W414520152	YELLOW	28V	11	45	588
WL-19W414530152	RED	28V	11	45	625
WL-19W414570152	BLUE	28V	11	50	446
WL-19W4145W0152	WHITE	28V	11	250	*

*Chromaticity coordinates x = 0.31 y = .032


NOTES

- Maximum panel thickness 4mm
- Storage temperature
T_{STG}: -25°C – +80°C
- Ambient temperature
T_A: -20°C – +60°C
- DC operation only
- Voltage tolerance
V_{OP}: ±10%
- Electro-optical ratings at
T_A=25°C
- Degree of protection: IP67 in accordance to DIN EN 60529 when using the supplied gasket
- Mounting hole
8 + 0.2mm
- 152mm PVC insulated wire leads, 24 AWG stranded tinned copper
- Red wire is anode (+)
Black wire is cathode (-)
- Due to production tolerances, slight color variations may be detected within individual consignments
- Supplied with mounting hardware; 1) gasket, 2) spring washer, and 3) M8 nut

CERTIFICATIONS

RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

wamco
LIGHTING