### **Features**

- Wide input range 85-305VAC
- 5000m operating altitude

### Regulated Converter

- OVCIII up to 2000m altitude
- 4kVAC isolation rated/60sec.
- EMC compliant without external components
- No load power consumption <200mW</li>

#### Description

RAC20E-K/277, the economy "E-K" series of compact 20 Watt AC/DC modules, is designed to meet general purpose requirements for a wide variety of equipment for the IoT, ITE and industrial markets. These encapsulated power supplies feature 4kVac isolation and over voltage category OVCIII, as well as 100-277VAC nominal input voltages. At OVC II usage, the operating altitude is rated for up to 5000m. For EMC compatibility in floating output configurations, EN55032 limits for class "B" are met without any external components. The outputs are protected against over current and short circuits and input protection by internal fuse is provided. All these features make the product one of the easiest integrated modular power solutions for lowest total cost of ownership in the industry.

#### **Selection Guide**

Part Number	Input Voltage Range [VAC]	nom. Output Voltage [VDC]	Output Current [mA]	Efficiency typ. <sup>(1)</sup> [%]
RAC20E-05SK/277	85-305	5	4000	80
RAC20E-12SK/277	85-305	12	1667	83
RAC20E-24SK/277	85-305	24	833	84

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

#### **Model Numbering**

nom. Output Power \_\_\_\_\_\_

 <u>S</u>	K/277
L	<b>S</b> ingle

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

nternal Input Filter Iominal Input Voltage					
lominal Input Voltage					CM Choke
	50/60Hz		100VAC		277VAC
perating Range <sup>(2, 3)</sup>	47-63Hz		85VAC	277VAC	305VAC
perating hange to a	DC		120VDC		430VDC
	115VAC				400mA
nput Current	230VAC				300mA
	277VAC				250mA
wish Ourrent	cold start	115VAC			20A
nrush Current	at 25°C	230/277VAC			40A
lo load Power Consumption					200mW
rP Standby Mode Conformity	0.5W				0.25W
Maximum output power available for	Input Power= 1.0W				0.6W
tated maximum input power)	2.0W				1.4W

Note3: Refer to "Derating Graph"

continued on next page



#### **RAC20E-K/277**

20 Watt 2" x 1" Single Output






UL/IEC/EN62368-1 certified CAN/CSA C22.2 No. 62368-1 certified IEC/EN62368-1 2nd Edition certified IEC/EN62368-1 3rd Edition certified IEC/EN61558-1/2-16 pending EN55032 compliant EN55035 compliant CB Report

# RAC20E-K/277

**Specifications** (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

### **Series**



Output Load [%]

\_\_\_\_\_ 110VAC \_\_\_\_\_ 230VAC

- - 277VAC

40 30 20


10

0 10 20 30 40 50 60 70 80 90 100

# RAC20E-K/277

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

### **Series**



Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage

# RAC20E-K/277

#### **Series**


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

PROTECTIONS				
Parameter	Cor	ndition	Value	
Isolation Resistance		$V_{ISO} = 500VDC$	1GΩ min.	
Isolation Capacitance	I/P to O/P	100kHz/0.1VDC	100pF max.	
Leakage Current	@2	277VAC	0.25mA max.	
Insulation Grade			reinforced	


ENVIRONMENTAL				
Parameter	Condition			Value
Operating Temperature Range	@ natural convection 0.1m/s	refer to "Derating Graph"		-40°C to +90°C
Maximum Case Temperature				+95°C
Temperature Coefficient				±0.02%/K
Operating Altitude				5000m (0VCII) 2000m (0VCIII)
Operating Humidity	non-col	ndensing		20% - 90% RH max.
Pollution Degree				PD2
Vibration				10-500Hz, 2G 10min./1cycle, period 60min. each along x,y,z axes
MTBF	according to MIL-HDBK-217F, G.B. +25°C +40°C		830 x 10 <sup>3</sup> hours 700 x 10 <sup>3</sup> hours	
		T <sub>AMB</sub> = +40°C	5Vout 12Vout 24Vout	34 x 10 <sup>3</sup> hours 44 x 10 <sup>3</sup> hours 53 x 10 <sup>3</sup> hours
Design Lifetime	230VAC/60Hz and full load	T <sub>AMB</sub> = +25°C	5Vout 12Vout 24Vout	89 x 10 <sup>3</sup> hours 115 x 10 <sup>3</sup> hours 132 x 10 <sup>3</sup> hours

#### **Derating Graph**

(@ Chamber and natural convection 0.1m/s)










# RAC20E-K/277 Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)




SAFETY AND CERTIFICATIONS		
Certificate Type (Safety)	Report / File Number	Standard
Audio/Video, information and communication technology equipment - Safety requirements	E491408-A6018-UL	UL62368-1 3rd Edition CAN/CSA-C22.2 No. 62368-1 3rd Edition
Audio/Video, information and communication technology equipment - Safety requirements (CB)	010015000	IEC62368-1:2014 2nd Edition
Audio/Video, information and communication technology equipment - Safety requirements (LVD)	210615003	EN62368-1:2014 + A11:2017
Audio/Video, information and communication technology equipment - Safety requirements	010015000	IEC62368-1:2018 3rd Editior
Audio/Video, information and communication technology equipment - Safety requirements	210615002	EN IEC 62368-1:2020 + A11:2020
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V (CB Scheme)	nonding	IEC61558-1:2005 2nd Edition + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V	pending	EN61558-1:2005 + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements (CB Scheme)	a se di se	IEC61558-2-16:2009 1st Edition + A1:2013
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements	pending	EN61558-2-16:2009 + A1:2013
RoHS2		RoHS-2011/65/EU + AM-2015/863
EMC Compliance	Condition	Standard / Criterion
ESD Electrostatic discharge immunity test	Air ±2kV, 4kV, 8kV Contact ±4kV	IEC61000-4-2:2008, Criteria A EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	10V/m (8MHz-1GHz) 3V/m (1.4GHz-2GHz) 1V/m (2GHz-2.7GHz)	IEC61000-4-3:2006+A2:2010, Criteria A IEC61000-4-3:2006+A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Port: ±2.0kV	IEC/EN61000-4-4:2012, Criteria A
Surge Immunity	AC Port: ±1.0kV	IEC/EN61000-4-5:2014, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	AC Port: 10Vrms (0.15-80MHz)	IEC61000-4-6:2013, Criteria A EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	30A/m	IEC61000-4-8:2009 / EN61000-4-8:2010, Criteria A

continued on next page

# RAC20E-K/277 Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

EMC Compliance	Condition	Standard / Criterion
	Voltage Dip 100% (0.5P)	IEC/EN61000-4-11:2004, Criteria A
	Voltage Dip 100% (1.0P)	IEC/EN61000-4-11:2004, Criteria A
Voltage Dips and Interruptions	Voltage Dip 30%	IEC/EN61000-4-11:2004, Criteria A
	Voltage Dip 20%	IEC/EN61000-4-11:2004, Criteria A
	Voltage Interruption 100%	IEC/EN61000-4-11:2004, Criteria B
Limits of Harmonic Current Emissions		EN61000-3-2:2014
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013
Low voltage power supplies, d.c. output Part 3: Electromagnetic compatibility (EMC)		EN IEC 61204-3:2018, Class B
Limitations on the amount of electromagnetic interference allowed from digital and electronic devices		FCC 47 CFR Part 15 Subpart B, Class B



# RAC20E-K/277

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

#### **Series**

PACKAGING INFORMATION

Parameter	Туре	Value
Packaging Dimension (LxWxH)	tube	490.0 x 56.0 x 40.0mm
Packaging Quantity		15pcs
Storage Temperature Range		-40°C to +85°C
Storage Humidity	non-condensing	20% to 90% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.