

## TECHNICAL DATA SHEET

Part#: 7246E

**Cutters - Medium Taper Relieved Head - Semi-Flush - Short Handle**  
Designed for maximum tool life, cutting up to .042" diameter soft wire

The 7246E Lazer Line<sup>®</sup> medium tapered/relieved semi-flush cutter has a cutting capacity of .008" - .042" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action. It features an ergonomically molded antimicrobial Anti-Static grip (10<sup>10</sup> ohms/sq surface resistivity) with dual leaf springs.

- |                       |                              |
|-----------------------|------------------------------|
| • Precision Level     | ★★★★★                        |
| • Material            | Carbon                       |
| • Surface Resistivity | 10 <sup>10</sup> ohms/sq     |
| • Shape               | Taper Relieved Head          |
| • Type of Cut         | Semi-Flush                   |
| • Cutting Capacity    | .008" - .042"                |
| • Blade Angle         | 14.25°                       |
| • Blade Length        | .36" (9mm)                   |
| • Body Width          | 0.42" (10.5mm)               |
| • Body Height         | .25"                         |
| • OAL                 | 4.75" (118.75mm)             |
| • Weight (OZ)         | 3                            |
| • UPC                 | 662847009556                 |
| • Schedule B          | 8203.20.60.60                |
| • ECCN                | EAR99                        |
| • UNSPSC Code         | 27111511                     |
| • Country of Origin   | USA                          |
| • Group               | Medium Cutters - 7000 Series |

