1-2232826-3 <

GRACE INERTIA 2.0 TE Internal #: 1-2232826-3 PCB Mount Header, Vertical, Wire-to-Board, 3 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Through Hole - Solder, GRACE INERTIA 2.0

View on TE.com >

Connectors > PCB Connectors > PCB Headers & Receptacles



Connector System: Wire-to-Board

Number of Positions: **3**

Number of Rows: 1

Centerline (Pitch): 2 mm [.079 in]

PCB Mount Orientation: Vertical

Features



Product Type Features

Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
PCB Connector Assembly Type	PCB Mount Header
Configuration Features	
Number of Loaded Positions	3
Number of Positions	3
Number of Rows	1
PCB Mount Orientation	Vertical
Electrical Characteristics	
Operating Voltage	50 VAC
Body Features	
Connector Profile	Standard

C For support call+1 800 522 6752

PCB Mount Header, Vertical, Wire-to-Board, 3 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Through Hole - Solder, GRACE INERTIA 2.0



Connector Code	A
Primary Product Color	Natural
Contact Features	
Mating Square Post Dimension	.5 mm[.02 in]
Contact Mating Area Plating Material Thickness	2 µm[80 µin]
Contact Mating Area Plating Material Finish	Bright
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Type	Pin
Contact Current Rating (Max)	2 A
Termination Features	
Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Method to Printed Circuit Board	Through Hole - Solder
Nechanical Attachment	
Mating Alignment Type	Keyed
Mating Retention	With
PCB Mount Retention Type	Kinked Legs
Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Retention	With
Housing Features	
Housing Material	66 Nylon
Centerline (Pitch)	2 mm[.079 in]
Dimensions	
PCB Thickness (Recommended)	1.6 mm[.063 in]
Jsage Conditions	
Operating Temperature Range	-40 - 105 °C[-40 - 221 °F]
Operation/Application	
Shielded	No
Circuit Application	Signal

C For support call+1 800 522 6752

08/02/2022 11:42AM | Page 2

PCB Mount Header, Vertical, Wire-to-Board, 3 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Through Hole - Solder, GRACE INERTIA 2.0



Glow Wire Rating	Glow Wire
Agency/Standard	VDE
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Type	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

PCB Mount Header, Vertical, Wire-to-Board, 3 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Through Hole - Solder, GRACE INERTIA 2.0





TE Part # 1-2232824-3 SGI2.0 PLUG HOUSING 3P,KEY A,NTL



TE Part # 1-2350224-3 SGI 2.0 Plug Housing, 3 Position, Key A



TE Part # 4-2232826-2 SGI2.0 header assembly TH 2P,key B, BLK



Also in the Series | GRACE INERTIA 2.0





Wire-to-Board Connector Contacts(3)

Customers Also Bought



PCB Mount Header, Vertical, Wire-to-Board, 3 Position, .079 in [2 mm] Centerline, Fully Shrouded, Tin, Through Hole - Solder, GRACE INERTIA 2.0





Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2232826-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2232826-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2232826-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use

Product Specifications

Application Specification

English

Product Environmental Compliance **Product Compliance**

English

Product Compliance

English

Agency Approvals **VDE** Certificate

English