

TECHNICAL DATA SHEET

Part#: 7149E

Cutters - Long Nose Fine .03" x .022" Tip - Relieved Head
Ideal for cutting larger leads (.025") in a confined space

The 7149E Lazer Line[®] relieved fine tip laser flush cutter has a cutting capacity of .001" - .020" soft wire. It is made of carbon tool steel steel with induction hardened cutting blades to RHC 63-65. This overall length is 6". The CNC machining allows the joint surfaces to be perfect to allow for long life. The Anti-Static grips are soft cushioned foam and have a surface resistivity of 10^{10} ohms/sq. The dual leaf springs provide smooth action.

• Precision Level	★★★★★
• Material	Carbon
• Surface Resistivity	10^{10} ohms/sq
• Shape	Relieved Head
• Type of Cut	Lazer Flush
• Cutting Capacity	.001 - .020"
• Blade Angle	16°
• Blade Length	.175" (4.38mm)
• Body Width	0.42" (10.5mm)
• Body Height	
• OAL	5.75" (143.75mm)
• Weight (OZ)	3
• UPC	662847009235
• Schedule B	8203.20.60.60
• ECCN	EAR99
• UNSPSC Code	27111511
• Country of Origin	USA
• Group	Long Nose Fine Tip

