

TECHNICAL DATA SHEET

Part#: 7274E

Cutters - .09" x .08" Transverse End - Short Handle
For horizontal cutting in tight places

The 7274E Lazer Line[®] miniature tapered transverse laser flush cutter with a cutting capacity of .001" - .020" soft wire is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. This overall length is 5.25". The CNC machining allows the joint surfaces to be perfect to allow for long life. It features a ergonomically molded antimicrobial Anti-Static grip (10¹⁰ ohms/sq surface resistivity) with dual leaf springs.

- Precision Level ★★★★★
- Material Carbon
- Surface Resistivity 10¹⁰ ohms/sq
- Shape Transverse End
- Type of Cut Lazer Flush
- Cutting Capacity .001" - .020"
- Blade Angle 90°
- Blade Length .18"
- Body Width 0.42" (10.5mm)
- Body Height .25"
- OAL 4.75" (118.75mm)
- Weight (OZ) 3
- UPC 662847009662
- Schedule B 8203.20.60.60
- ECCN EAR99
- UNSPSC Code 27111511
- Country of Origin USA
- Group Transverse End

