


## AMEOF350-HAMJZ





AMEOF350-HAMJZ series is one of Aimtec's compact size (3"x5"x1") 350W AC/DC converter with active PFC and suitable for medical system equipment. It features universal AC input and at the same time accepts DC input voltage, costeffective, high efficiency, high reliability and double or reinforced isolation. These converters offer excellent EMC and safety performance, which with UL62368-1, ES60601-1 approval and meet IEC/EN62368-1, GB4943, EN60335-1, IEC/EN61558-1, IEC/EN60601-1 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home, medical, etc.

### **Features**



- Universal Input: 85 264VAC/120 370VDC
- Operating Temp: -40 °C to +70 °C
- High isolation voltage: 4000VAC
- Active PFC
- Output short circuit, over-current, over-voltage, over temperature protection
- Low no-load power consumption of 0.5W
- Suitable for Type BF application
- Approval UL62368-1, ES60601-1; Designed to meet IEC/EN62368-1, EN60335-1, EN61558-1, IEC/EN60601-1









## **Training**






Coming Soon!

Product Training Video (click to open)

**Application Notes** 

## **Summary**





## **Applications**









Power Grid

Industrial

Telecom

Medical



# Models & Specifications



Single Output									
Model	Input Voltage (VAC/Hz)	Input Voltage (VDC)	Cooling method	Max Output wattage (W)	Output Voltage (V)	Output Voltage Adjustable Range (V)	Output Current (A)	Maximum capacitive load (μF)	Efficiency @230VAC Typ. (%)
AMEOF350-12SHAMJZ	90-264/47-63	127-373	Free air	180	12	11.4-12.6	15	6000	92
AIVIEUF550-125HAIVIJZ	90-204/47-03	127-373	20.5CFM	300	12	11.4-12.0	25	6000	
AMEOF350-15SHAMJZ	90-264/47-63	127-373	Free air	180	15	14.25-15.75	12	5000	92
AIVIEUF330-133HAIVIJZ	90-204/47-03	127-373	20.5CFM	325	15		21.67		
AMEOF350-24SHAMJZ	90-264/47-63	127 272	Free air	199.9	24	22.8-25.2	8.33	3200	93
		127-373	20.5CFM	350.4			14.6		
ANAFOE2E0 27CHANAI7	90-264/47-63	127-373	Free air	199.8	27	26.65-28.35	7.4	2600	93
AMEOF350-27SHAMJZ	90-204/47-03	127-373	20.5CFM	351	21	20.05-28.35	13		
AMEOF350-36SHAMJZ	90-264/47-63	127-373	Free air	200.16	36	34.2-37.8	5.56	2000	93
AIVIEUF35U-303HAIVIJZ	90-204/47-03	127-373	20.5CFM	350.28	30	34.2-37.8	9.73		
ANAFOE2EO AQCIIANAIZ	90-264/47-63 127-	127 272	Free air	200.1	48	45.6-50.4	4.17	2000	94
AMEOF350-48SHAMJZ		127-373 20.5	20.5CFM	350.4		45.0-50.4	7.3		
AMEOF350-54SHAMJZ #Ø	#Ø 90-264/47-63 12	127-373	Free air	199.8	54	4 51.3-56.7	3.7	2000	94
			20.5CFM	351			6.5		
Add suffix -F for enclosed package. (ex. AMEOF350-12SHAMJZ-F is enclosed package version)									

Input Specifications				
Parameters	Conditions	Typical	Maximum	Units
Input current	115VAC		4	Α
	230VAC		2	Α
Inrush current	115VAC, cold start	50		Α
	230VAC, cold start	75		Α
Leakage	240VAC, normal condition		0.1	mA
	240VAC, single fault condition		0.5	mA
Power factor	115VAC, 100% load	≥0.98		
	230VAC, 100% load	≥0.95		

Output Specifications					
Parameters	Conditions	Typical	Maximum	Units	
Valtage ecourage	12, 15V	±3		%	
Voltage accuracy	24, 27, 36, 48, 54V	±2		%	
Line regulation	Full load	±0.5		%	
Load regulation	0-100% load	±1		%	
	12, 15V, 10-100% load		120	mV p-p	
	24V, 10-100% load		150	mV p-p	
	27, 36V, 10-100% load		200	mV p-p	
Dinnlo 9 Noico*	48, 54V, 10-100% load		250	mV p-p	
Ripple & Noise*	12, 15V, 0-10% load		180	mV p-p	
	24V, 0-10% load		225	mV p-p	
	27, 36V, 0-10% load		300	mV p-p	
	48, 54V, 0-10% load		375	mV p-p	



Hold up time	230VAC, Free air convection	14	ms
Hold up time	230VAC, 20.5CFM	8	ms

<sup>\*</sup> Ripple and Noise are measured at 20MHz bandwidth with a  $10\mu F$  electrolytic capacitor and a  $0.1\mu F$  ceramic capacitor. Please refer to the application note for specific details.

Isolation Specification					
Parameters	Conditions	Typical	Maximum	Units	
Tested I/O voltage	60 sec, leakage ≤ 10mA	≥4000		VAC	
Tested I/PE voltage	60 sec, leakage ≤ 10mA	≥2000		VAC	
Tested O/PE voltage	60 sec, leakage ≤ 10mA	≥1500		VAC	
Resistance I/O*	500VDC	>100		ΜΩ	
Resistance I/PE*	500VDC	>100		ΜΩ	
Resistance O/PE*	500VDC	>100		ΜΩ	
MOP I/O	2xMOPP				
MOP I/PE		1xMOPP			
MOP O/PE		1xMOPP			
* Tosted under 25+5°C ambient temperature with relative humidity <05% and no condensation					

<sup>\*</sup> Tested under 25±5°C ambient temperature with relative humidity <95% and no condensation.

General Specifications					
Parameters	Conditions	Typical	Maximum	Units	
Protection class	Class II without protective earth connection, Class I with protective earth connection				
Over current protection	Auto recovery, hiccup	≥ 110		% of lout	
	12Vout, shut down, manual recovery		15	VDC	
	15Vout, shut down, manual recovery		18.5	VDC	
	24Vout, shut down, manual recovery		30	VDC	
Over voltage protection	27Vout, shut down, manual recovery		33.5	VDC	
	36Vout, shut down, manual recovery		45	VDC	
	48Vout, shut down, manual recovery		59.5	VDC	
	54Vout, shut down, manual recovery		63	VDC	
Short circuit protection	Hiccup, Continuous, Auto recovery time < 3S				
Over temperature protection	Shut down, manual recovery				
Fan power	27V	12V/0.5A, Voltage accuracy +15/-25%			
raii powei	12, 15, 24, 36, 48, 54V	12V/0.5A, Voltage accuracy ±15%			
No-load power consumption			0.5	W	
Operating temperature	See derating graph	-40 to +70		°C	
Storage temperature		-40 to +85		°C	
Power Derating	+50 °C to +70 °C	2.5		%/°C	
rower Derattrig	90VAC to 100VAC	1		%/VAC	
Ambient temperature derating	Operating altitude > 2000m	5		°C/1000m	
Temperature coefficient		±0.03		%/°C	
Cooling	Free air convection, forced air convection 20.5CFM				
Humidity	Non-condensing, storage	>10	95	% RH	
Hamilaity	Non-condensing, operating	>20	90	% RH	
Case material	Enclosed package Metal (1100 Aluminum, SUS304)				
Weight	Open frame	295		g	
vveignt	Enclosed	430		g	
Dimensions (L x W x H)	Open frame	5.00 x 3.00 x 1.	00 inches (127.0 x 7	76.2 x 25.4 mm	
Difficultions (L x W x H)	Enclosed 5.12 x 3.39 x 1.38 inches (130.0 x 86.0 x 35.0 mm)				
MTBF	> 300 000 hrs (MIL	-HDBK -217F, t=+25°0	C)		

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.



### **Safety Specifications**

#### **Parameters**

Standards

Agency approvals cULus UL 62368-1(# With exception of 54Vout model); AMSI/AAMI ES60601-1 V3.1(Ø With exception of 54Vout model)

Design to meet IEC/EN62368-1 EN60335-1 IEC/EN61558-1 IEC/EN60601-1 CAN/CSA-C22 2 No 60601-114 Ed3 EN60601-1

Design to meet IEC/EN62368-1, EN60335-1, IEC/EN61558-1, IEC/EN60601-1, CAN/CSA-C22.2 No.60601-1:14 Ed3, EN60601-1-2 Ed4, GB4943-1


EMC - Conducted and radiated emission*	CISPR32 / EN55032, conducted class B CISPR32 / EN55032, radiated class B with protective earth connection CISPR32 / EN55032, radiated class A without protective earth connection		
EMC - Harmonic current emissions*	IEC 61000-3-2 class A and class D		
EMC - Voltage fluctuations and flicker *	IEC 61000-3-3		
Electrostatic Discharge Immunity *	IEC 61000-4-2 Contact ±8KV, Air ±15KV, Criteria A		
RF, Electromagnetic Field Immunity *	IEC 61000-4-3 10V/m, Criteria A		
Electrical Fast Transient/Burst Immunity *	IEC 61000-4-4 ±4KV, Criteria A		
Surge Immunity *	IEC 61000-4-5 L-L ±2KV L-G ±4KV, Criteria A		
RF, Conducted Disturbance Immunity *	IEC 61000-4-6 10Vr.m.s, Criteria A		


IEC 61000-4-11 0%, 70%, Criteria B


## Derating




Voltage dips, Short Interruptions Immunity \*










<sup>\*</sup> The power supply is considered as a component and will be installed in an end-product. All the EMC tests are performed with the power supply mounted on a 1mm thick 360mm x 360mm metal plate. The EMC compliance of the end-product must be reconfirmed.



### **Dimensions**



## Open frame model




#### Note:

- It is needed to have ≥ 10mm distance between the product and external components for safety.
- 2. Connect mounting point 1, 2 and 4 to protective earth for Class I system.
- 3. Connect mounting point 1, 2 and 4 together for Class II system.

	Pin Output Specifications						
Pin	Function	Connector	Recommended connector				
1	AC Input (N)						
2	NC	ICT DED VIII	ICT VILID ICT CVILL 24 DT D4 4				
3	AC Input (L)	JST B5P-VH	JST VHR, JST SVH-21PT-P1.1				
4	NC	or equivalent	or equivalent				
5	Earth <del>↓</del>						
6	- Fan Output	2.5 XHS-2A	2.5 XHS-2Y				
7	+ Fan Output	or equivalent	or equivalent				
8	-V Output						
9	+V Output		-				



### **Enclosed model**



NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at <a href="https://www.aimtec.com">www.aimtec.com</a>.