

Han 3A M Insert Screw



Part number	09 20 003 2611
Specification	Han 3A M Insert Screw
HARTING eCatalogue	https://b2b.harting.com/09200032611

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Series	Han A [®]

Version

Termination method	Screw termination
Gender	Male
Size	3 A
Number of contacts	3
PE contact	Yes

Technical characteristics

Conductor cross-section	0.75 1.5 mm²
Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Insulation resistance	>10 ¹⁰ Ω
Stripping length	2.5 5.5 mm
Tightening torque	0.25 Nm
Limiting temperature	-40 +125 °C



Technical characteristics

Mating cycles ≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	564b7d75-7bf6-4cfb-acb1-2168eb61b675
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	12.5 g
Country of origin	Romania

Product data sheet 09 20 003 2611 Han 3A M Insert Screw



Commercial data

European customs tariff number 85366990

eCl@ss 27440205 Contact insert for industrial connectors