



Features:

- High Luminance
- High Operating Temperature
- Industry Standard 7.62mm Square Package

Specifications:

Maximum Ratings at Ta=25°C


- Reverse Voltage (<100μA) : 5V
- D.C. Forward Current : 30mA
- Pulse Current (Pulse Width of 0.1ms, 1/10 Duty Cycle) : 100mA
- Operating Temperature Range : -40°C to +100°C
- Storage Temperature Range : -40°C to +100°C
- Soldering Temperature Dip Soldering : 260°C for 5 secs
- Soldering Temperature Hand Soldering : 350°C for 3 secs

Electrical & Optical Characteristics at Ta=25°C


LED Chip			Lens Colour	Dominant Wavelength (nm) at 20mA	Luminous Intensity (mcd) at 20mA		Forward Voltage (V) at 20mA		Viewing Angle 2 Θ 1/2 (deg)	Part Number
Material	Emitted Colour	Brightness			Min.	Typ.	Typ.	Max.		
InGaN / Sapphire	Blue	Mega	Water Clear	465	200	500	3.2	4	65	OVA-1023
InGaN / Sapphire	True Green			520	1,950	3,800				OVA-1024
A1GaInP/Si	Red			625	1,400	2,800	2.1	2.6	50	OVA-1028
A1GaInP/Si	Yellow			589	1,400	3,000	2.1	2.5		OVA-1026

LED Chip			Lens Colour	Co-Ordinates for CIE Chromaticity at 20mA		Luminous Intensity (mcd) at 20mA		Forward Voltage (V) at 20mA		Viewing Angle 2 Θ 1/2 (deg)	Part Number
Material	Emitted Colour	Brightness		X Axis	Y Axis	Min.	Typ.	Typ.	Max.		
InGaN / Sapphire	White	Mega	Water Clear	0.31	0.3	1,400	3,300	3.2	4	65	OVA-1021

Radiation Diagrams



OVA-10 Series



Part Number Table

Description:	Part Number
LED, Suprflux SML Dome, White	OVA-1021
LED, Suprflux SML Dome, Blue	OVA-1023
LED, Suprflux SML Dome, Green	OVA-1024
LED, Suprflux SML Dome, Yellow	OVA-1026
LED, Suprflux SML Dome, Red	OVA-1028

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.