External Plug In Adapter 65W



RoHS Compliant

Features


- C8 Input
- Class 11
- DOE Level VI Efficiency
- Overcurrent Protection
- · Short Circuit Protection
- 1 Year Warranty
- EN62368 Approved


| Model | | MP010274 | MP010275 |
|--------------|-------------------------|--|----------|
| Output | DC Voltage | 12V DC | 24V DC |
| | Rated Current | 5amp | 2.5amp |
| | Current Range | 0-5amp | 0-2.5amp |
| | Rated Power | 60 Watt | 60 Watt |
| | Ripple & Noise | 240m Vp-p max | |
| | Output Regulation | ±5% | |
| | Output Connector | 2.1mm × 5.5mm × 12mm C+ve | |
| Input | Voltage Range | 90 - 264V AC | |
| | Frequency Range | 47 -63Hz | |
| | Input Current | 1.2amp Max | |
| | Inrush Current | 40amp Max | |
| | Standby Power | 0.21amp Max | |
| | Leakage Current | 0.25amp Max | |
| | Input Connector | C8 | |
| Environment | Operating Temp | 0°C to 40°C | |
| | Cooling | Convection | |
| | Temperature Coefficient | 0.05%/°C | |
| | Humidity | 5~95%RH(non-condensing) | |
| | Storage Temp | -20°C to +80%°C | |
| Safety & EMC | Safety Standards | UL/CuL 62368-1, GS/TUV EN62368-1 All Options Plus SAA AN/NZ 62368.1 C8 Version Only | |
| | EMC Emissions | EN55032,EN55035, FCC Part 15 Class B | |

External Plug In Adapter 65W

multicomp_{PRO}

Mechanical Specification





Dimensions: Millimetres

Part Number Table

| Description | Part Number |
|---|-------------|
| External Plug In Adapter, 12VDC, 5A, C8 Desktop, 2.1 C+ve | MP010274 |
| External Plug In Adapter, 24VDC, 2.5A, C8 Desktop, 2.1 C+ve | MP010275 |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

