

Description: 2012 2.4-2.5GHz Chip Antenna

PART NUMBER: ANT2012LL13R2400A

Features:

- Size: 2.00x1.25x1.00 mm
- Omni-directional radiation
- Tape & reel automatic mounting
- Reflow process compatible
- RoHS compliant

Applications:

- 2.4 GHz WiFi device
- Bluetooth gadget
- Zigbee device
- ISM band equipment

Working Frequency Bandwidth Return Loss Polarization

Azimuth Beamwidth

Peak Gain **Impedance**

Operating Temperature

Maximum Power

Termination

Resistance to Soldering Heats

ELECTRICAL SPECIFICATIONS

2.45 GHz 85 MHz(Typ.) 6dBi min. Linear Omni-directional 2.72 dBi (Typ.) 50 Ω

- 40~105 °C

1 W

Ag (Environmentally-Friendly Leadless)

260°C, 10sec.

1. The specification is defined on Pulse evaluation board

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and rederal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:




Description: 2012 2.4-2.5GHz Chip Antenna


PART NUMBER: ANT2012LL13R2400A

MECHANICAL DRAWING

	Dimension
L (mm)	2.00 ±0.20
W (mm)	1.25 ±0.20
T (mm)	1.00 ± 0.20
A (mm)	0.60 ± 0.10
B (mm)	0.40 ±0.10



Terminal name Function Feeding Point S1 S2 **GND** S3 **GND**




BOTTOM VIEW




Description: 2012 2.4-2.5GHz Chip Antenna

PART NUMBER: ANT2012LL13R2400A

REFERENCE DESIGN OF EVALUATION BOARD



Outlook and dimension of evaluation board




Unit: mm

Dimension of footprint


Description: 2012 2.4-2.5GHz Chip Antenna

PART NUMBER: ANT2012LL13R2400A

REFERENCE DESIGN OF EVALUATION BOARD



Details of soldering pad



Frequency= 2.45 GHz Max gain = 2.72dBi, at (120,0) MEG (mean effective gain)= -0.69 dBi Directivity (dB) = 3.88

Efficiency = -1.16dB, 76.56%

Radiation pattern

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION




Description: 2012 2.4-2.5GHz Chip Antenna

PART NUMBER: ANT2012LL13R2400A

ELECTRICAL PERFORMANCES





Maker data

1. 2.40GHz, -6.3276dB

2. 2.45GHz, -22.544dB

3. 2.48GHz, -7.6609dB

Return loss



Description: 2012 2.4-2.5GHz Chip Antenna

PART NUMBER: ANT2012LL13R2400A

REVISION HISTORY		
Revision	Date	Description
Version 1	Nov. 19, 2020	- New issue
Version 2	April. 6, 2021	 Modified MECHANICAL DRAWING: S1 and S2 label