

SPECIFICATION

Part No. : **AP.10E.07.0039B**

Product Name : AP.10E - 1 Stage 15dB 39mm 0.81 with IPEX

MHFI (U.FL compatible)

Feature : World smallest GPS/GALILEO active patch

High performance

Ultra low power consumption

RoHS Compliant






1. Introduction

AP.10E active GPS/GALILEO patch antenna is the smallest GPS high performance antenna currently available in the world. Using extremely sensitive high dielectric constant powder formulation and tight process control the 10*10*4mm patch antenna is accurately tuned to have its frequency band right at 1575.42MHz for GPS systems. With an ultra low power consumption one stage LNA, this small active patch has the performance of an ordinary active patch, but at only a quarter of the size.

This product is suited to small form factor mobile devices such as GPS Smartphones, Personal Location, Medical devices, Telematic devices and Automotive navigation and tracking. Custom gain, connector and cable versions are available. The AP.10E consists of 2 functional blocks – the LNA and also the patch antenna.






2. Specification

ELECTRICAL					
Frequency		1575.42 ± 1.023MHz			
Gain @ Zenith		-10dBic Typ. @ Zenith			
Polarization		RHCP			
Axial Ratio		4.0dB max@Zenith			
Patch Dimension		10*10*4.0mm			
LNA					
Frequency		1575.42 ± 1.023MHz			
Outer Band Attenuation		F0=1575.42MHz			
		F0±30MHz 9dB min.			
		F0±50MHz 20dB min.			
		F0±100MHz 25dB min.			
Output Impedance		50Ω			
Output VSWR					
Pout at 1dB Gain		Typ2dBm			
Compression point		Min6dBm			
LNA Gain, Power Consumption and Noise Figure					
Voltage	L	NA Gain (Typ)	Power Consumption(mA) Typ	Noise Figure Typ	
Min. 1.8V		14dB	3mA	2.5dB	
Typ. 3.0V		15dB	3mA	2.5dB	
Max. 5.5V		15dB	3mA	2.6dB	
MECHANICAL					
Dimensions			10*10*4.0mm		
RF Cable		Coaxial Cable Ø0.81 ± 0.1mm, length 39 ± 2.0mm			
Connector IPEX MHFI (U.FL)					
ANTENNA WITH LNA					
Frequency			1575.42 ± 1.023MHz		
Gain			At 3V: 5 ± 4dBi@90°		
Output Impedance		50Ω			
Polarization		RHCP			
Output VSWR		Max 2.0 -40°C to + 85°C			
Operation Temperature					
Storage Temperature		-40°C to + 85°C 40% to 95%			
Relative Humidity		Min:1.8V Typ. 3.0V Max:5.5V			
Input Voltage		10*10*5.9mm			
Antenna		10102'AWW			




3. LNA Gain and Out Band Rejection @3.0V






4. LNA Noise Figure @3.0V





5. Radiation Pattern


XZ Plane Radiation



YZ Plane Radiation


Pattern | Model No. | Test Model | Freq(MHz) | Max Gain(dB) | Avg. Gain(dB) | Source Polar | Date | 1 | 1624 | YZ | 1624.00 | -12.30 | 352.00 | -29.55 | 216.00 | -16.23 | RHCP | 2010|4/25


XY Plane Radiation





6. Antenna Drawing








7. Plugs Usage Precautions


7.1. Mating / Unmating

- (1) To disconnect connectors, insert the end portion of I-PEX under the connector flanges and pull off vertically, in the direction of the connector mating axis.
- (2) To mate the connectors, the mating axes of both connectors must be aligned and the connectors can be mated. The "click" will confirm fully mated connection. Do not attempt to insert on an extreme angle.




7.2. Pull forces on the cable after connectors are mated

After the connectors are mated, do not apply a load to the cable in excess of the values indicated in the diagram below.






8. Packaging





*One Tray = 60 pieces

*6 Trays per Section = 360 pcs



*Each Carton contains 3 Sections

*1080 pieces per Carton

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.