




### Datasheet

# 40 V, 2 x 5 A low forward voltage power Schottky rectifier



#### **Features**

- Low profile design 1.1mm package typical height
- Wettable flanks for automatic visual inspection
- Very low conduction losses
- High forward surge current capability
- ECOPACK2 compliant

### **Applications**

- DC/DC converter
- Stand by power
- Oring
- Polarity protection

### **Description**

This 2 x 5 A, 40 V Schottky diode is suitable for power supply, especially for lighting power, as well as auxiliary power in server or telecom SMPS.

Packaged in PSMC (TO-277A), this STPS10L40CSF, dual diode device provides a high level of efficiency in a compact and flat package is ideal for oring function in server for instance.



# Product status link STPS10L40CSF

Product summary			
I <sub>F(AV)</sub>	2 x 5 A		
V <sub>RRM</sub>	40 V		
T <sub>j</sub> (max.)	150 °C		
V <sub>F</sub> (typ.)	0.370 V		

# 1 Characteristics

**L**7/

#### Table 1. Absolute ratings (limiting values per diode at 25 °C, unless otherwise specified)

Symbol	Parameter			Value	Unit
V <sub>RRM</sub>	Repetitive peak reverse voltage			40	V
<b>I</b> =	Average forward current, δ = 0.5	$T_{c} = 135 \ ^{\circ}C^{(1)}$	Per diode	5	^
IF(AV)	IF(AV) square wave		Per device	10	A
P <sub>ARM</sub>	Repetitive avalanche power $t_p = 10 \ \mu s$		T <sub>j</sub> = 125 °C	165	W
I <sub>FSM</sub>	Surge non repetitive forward current $t_p = 10 \text{ ms sinusoidal}$			120	Α
T <sub>stg</sub>	Storage temperature range			-65 to +175	°C
Tj	Maximum operating junction temperature <sup>(2)</sup>			+150	°C

1. Value based on R<sub>th(j-c)</sub>(max.).

2.  $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$  condition to avoid thermal runaway for a diode on its own heatsink.

#### Table 2. Thermal resistance parameter

Symbol	Parameter		Typ. value	Unit
R <sub>th(j-c)</sub>	Junction to case, per device	PSMC (TO-277)	1.0	°C/W

For more information, please refer to the following application note:

AN5088: Rectifiers thermal management, handling and mounting recommendations

#### Table 3. Static electrical characteristics (per diode)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I <sub>R</sub> <sup>(1)</sup>		T <sub>j</sub> = 25 °C		-		125	μA
IR <sup>(*)</sup>	Reverse leakage current	T <sub>j</sub> = 125 °C	$V_{\rm R} = V_{\rm RRM}$	-	30	50	mA
	Forward voltage drop	T <sub>j</sub> = 25 °C	I <sub>F</sub> = 5 A	-		0.495	
N (2)		T <sub>j</sub> = 125 °C		-	0.370	0.430	V
VF <sup>(2)</sup>		T <sub>j</sub> = 25 °C		-		0.600	V
		T <sub>j</sub> = 125 °C	I <sub>F</sub> = 10 A	-	0.505	0.590	

1. Pulse test:  $t_p = 5 ms$ ,  $\delta < 2\%$ 

2. Pulse test:  $t_p = 380 \ \mu s, \ \delta < 2\%$ 


To evaluate the conduction losses, use the following equation:

 $P = 0.25 \text{ x } I_{F(AV)} + 0.036 \text{ x } I_{F}^{2}(RMS)$ 

For more information, please refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

### 1.1 Characteristics (curves)








Figure 4. Junction capacitance versus reverse voltage applied (typical values, per diode)





0.4

0.5


0.6

0.7

0.8

tage drop versus forward current values, per diode) Figure 6. Thermal resistan copper surface under tab board FR4






0.0

0.1

0.2

0.3






# 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.


### 2.1 PSMC (TO-277A) package information

- Epoxy meets UL94,V0
- Cooling method : by conduction (C)



### Figure 8. PSMC (TO-277A) package outline

C






	Dimensions						
Ref.		Millimeters			Inches (for reference only)		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	1.00	1.10	1.20	0.039	0.043	0.047	
b	1.05	1.20	1.35	0.041	0.047	0.053	
b2	1.90	2.05	2.20	0.075	0.081	0.087	
b4		0.75			0.029		
С	0.15	0.23	0.40	0.006	0.009	0.016	
D	4.45	4.60	4.75	0.175	0.181	0.187	
D1	4.25	4.40	4.45	0.167	0.173	0.175	
D2	3.40	3.60	3.70	0.134	0.142	0.146	
E	6.35	6.50	6.65	0.250	0.256	0.262	
E1	6.05	6.10	6.15	0.238	0.240	0.242	
E2	4.50	4.60	4.70	0.177	0.181	0.185	
E3		3.94			1.55		
е		2.13			0.084		
e1		3.33			0.131		
G		1.20			0.047		
G1		0.70			0.027		
L	0.90	1.05	1.24	0.035	0.041	0.049	
L4	0.02			0.0008			
L5	0.02			0.0008			

### Table 4. PSMC (TO-277A) package mechanical data

### Figure 9. PSMC (TO-277A) package footprint in mm (in inches)



Note: For package and tape orientation, reel and inner box dimensions and tape outline please check TN1173



# **3** Ordering information

Table 5.	Ordering	information	
----------	----------	-------------	--

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS10L40CSF	10L40C	PSMC (TO-277A)	90 mg	6000	Tape and reel

# **Revision history**

### Table 6. Document revision history

Date	Version	Changes
20-May-2021	1	Initial release.

#### IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics - All rights reserved