

# PCB TERMINAL BLOCKS

## 5.08mm Pitch Standard Profile 90° Rising Clamp Terminal Blocks

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDs &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS


RELAY  
BASES

DIN RAIL  
ENCLOSURES

BATTERIES

SOLAR  
PANELS

TRANS-  
FORMERS

- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 pole solid block end stackable
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.2-4.0mm<sup>2</sup> (30-12AWG) solid cable
- 0.2-2.5mm<sup>2</sup> (30-12AWG) stranded cable
- Guided pin alignment
- Captive screw
-  approved


CTB0158



TYPE NO.	POLES	LENGTH
CTB0158/2	2	10.16mm
CTB0158/3	3	15.24mm
CTB0158/4	4	20.32mm
CTB0158/5	5	25.4mm
CTB0158/6	6	30.48mm
CTB0158/7	7	35.56mm
CTB0158/8	8	40.64mm
CTB0158/9	9	45.72mm
CTB0158/10	10	50.8mm
CTB0158/11	11	55.88mm
CTB0158/12	12	60.96mm

### SPECIFICATION

Rating	24A/250V UL=14A/300V, VDE&IMQ=24A/250V
Dielectric strength	≥2kV
Impulse withstand voltage	4kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Tinned, nickel plated brass
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.5mm



For other dimensions see CTB0108



CAMDENBOSS

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.1

+44 (0)1638 716101  
info@camdenboss.com  
www.camdenboss.com



FM 28614 EMS 613558