

ECS-CTP SMD Ceramic Resonator

MIN

1.84

500

-40

-55

UNITS

MHz

%

ΜΩ

°C

°C

%

Rev.2021

The ECS-CTP Series SMD ceramic resonator includes built in capacitors for reduced component count. The SMD Ceramic resonator is a low cost frequency control solution when absolute frequency accuracy is not important.

Request a Sample

ECS-CTP

MAX

20.00

 ± 0.5

+85

+85

±0.1


TYP





- 6.0 x 3.0 mm package
- Industry Standard footprint
- Extended Temp. Range
- **Built-in Caps**

DIMENSIONS (mm)






Figure 1) Top, Side, and Bottom views

Francisco es Chabilitas	1.84 ~ 8.00 MHz		± 0.3	%
Frequency Stability Over -40 ~ +85°C Equivalent Series Resistance (ESR)	8.01 ~ 12.00 MHz		± 0.2	%
	12.1 ~ 20.00 MHz		±0.3	%
	1.84 ~ 2.99 MHz		100	Ω
	3.0 ~ 3.49 MHz		50	Ω
	3.5 ~ 12.00 MHz		30	Ω
	12.1 ~ 20.0 MHz		60	Ω
Withstanding Voltage	DC, 5 s Max.		100	V
Valtage Deting	DC Voltage		6	V
Voltage Rating	AC Voltage		15	Vp-p

OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS

CONDITIONS

@ +25°C

10V, 1 Min.

Topr

Tstg

@ +25°C ±3°C

Height 1.8 ±0.2 (1.84~3.5 MHz) $1.5 \pm 0.2 (3.51 \sim 12 \text{ MHz})$ 1.6 ±0.2 (12.1 ~ 20 MHz

Insulation Resistance

Storage Temperature

Aging (First Year)

Operating Temperature

PARAMETERS

Frequency Tolerance

Frequency

PAD CONNECTIONS					
1	In/Out				
2	Gnd				
3	Out/In				




Figure 2) Suggested Land Pattern

PART NUMBERING GUIDF: Fxample FCS-CTP-8.00-30-TR


ECS -CTP	FREQUENCY	Built In	PACKAGING	
263-611	THEQUENCY	CAPACITANCE		
	8.00 = 8.000 MHz	Standard	TR =	
	*See Developed	30 = 30 pF	Tape	
	Frequencies Pg. 2	10 = 10 pF	& Reel	
		15 = 15 pF	4K/Reel	
ct ECS for availability of non-developed		22 = 22 pF		
cies/non standard cap values.		33 = 33 pF		
sticles/flott statidard cap values.		39 = 39 pF		



ECS-CTP SMD Ceramic Resonator



POCKET TAPE DIMENSIONS (mm)



Α	В	С	D	F	J	L	М	Reel Dia.	Qty/Reel
6.4	3.4	16.0	7.5	8.0	1.6	0.3	2.1	330 mm	4000

SOLDER PROFILE
Peak solder Temp +260°C Max 10 sec Max.
2 Cycles Max.
MSL 1, Lead Finish Sn/Ag




Figure3) Suggested Reflow Profile

DEVLOPED FREQUENCIES
2.00 MHz
3.58 MHz
3.68 MHz
4.00 MHz
4.19 MHz
8.00 MHz
10.00 MHz
12.00 MHz
16.00 MHz
20.00 MHz



ECS-CTP SMD Ceramic Resonator






Figure4) Test Circuit

IC: 1/6TC4069UBP x 2

C1,C2: 30 (1±20%) pF (1.84 ~ 8.00 MHz) other (10/15/22/33/39/47 pF) 15(1±20%) pF (8.01~12 MHz) Other (10/22/30/33/39/47 pF) 10 (1±20%) pF (12.01 ~ 20 MHz)

Note: ECS does not approve the use of it's products in Automotive, Military, Avionics, Life Sustaining or Life Support systems or any other related medical applications without written approval from ECS Inc.