

## **SP-13**

## **Description:**

Triad's high reliability audio transformers provide the durability and precision required in today's demanding designs. These transformers are available for a wide variety of applications.

## **Electrical Specifications (@25C)**

Power	Matching Impedance		Max. Ma DC	DC Resistance (Ω)		Overall
level	Primary	Secondary	Unbalance in Primary	Primary	Secondary	Turns
(mW)						Ratio
40	25K CT/20K CT	1K CT/800CT	0.5	1,700.0	115.0	5.0:1.0

Operating Temperature: -40C° to 85C°

Storage Temperature: -40C° to 85C°

Humidity: Storage Humidity: 10 to 95% RH, non-condensing


Frequency Response: <u>+</u> 2.0 DB, at 300 Hz to 100K Hz

Pri-Sec Hipot test (Pri-Sec): 1,000 VRMS for 1 sec.

Working voltage: 150VDC

## **Construction:**

Plug-in terminals are precision spaced to provide fixed mounting centers. Epoxy molded case includes a .020" recess for ease of solder inspection. Leads are made of high strength Nickel alloy, gold plated and are .020" in diameter.



**RoHS Compliance:** As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

\*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see http://www.triadmagnetics.com/faq.html

Web: www.TriadMagnetics.com
Phone 951-277-0757
Fax 951-277-2757

460 Harley Knox Blvd. Perris, California 92571

