

POWER TRANSFORMER PC MOUNT: SPLIT PACK

FS28-700

Description:

The FS28-700 is a dual primary and dual secondary, split bobbin design which operates with either a parallel input of 115V or a series input of 230V. The output voltage will be either 28.0V with a center-tap under a 0.7A load with the secondaries wired in series, or 14.0V under a 1.4A load with the secondaries wired in parallel. The split bobbin design eliminates the need for costly electrostatic shielding.

Electrical Specifications (@25C)

1. Maximum Power: 20.0VA

2. Primary: Series: 230V; Parallel: 115V

3. Secondary: Series: 28.0V CT@ 0.7A; Parallel: 14.0V @ 1.4A

4. Voltage Regulation: 25% TYP @ full load to no load

5. Temperature Rise: 25C TYP 6. Hipot tested 100% at 2500 VRMS

Construction:

Three flange bobbin construction with primaries and secondaries wound side by side for low capacitive coupling.

Agency File:

UL: File E53148, UL 5085-2 (506), Class B General Purpose Transformer, cUL: File E53148, UL 5085-2 (506), Class B General Purpose Transformer, Canadian Use (CSA 22.2, No.66.2-06)

This model is also available in Class 2, UL 5085-3 (1585) version as FS28-700-C2




Dimensions: Units in inches.

1.875	2.25	0.300	0.400	1.600	0.041	0.020	0.234
	1.875	l l		, , , , , , , , , , , , , , , , , , ,			

Weight: 0.80 lbs


Schematic:





RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

As of April 7, 2008, UL standards 506 and 1585 will be migrated to UL 5085-2 and 5085-3, respectively.

*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see http://www.triadmagnetics.com/faq.html







Board Layout

Web: www.TriadMagnetics.com Phone 951-277-0757 Fax 951-277-2757

460 Harley Knox Blvd. Perris. California 92571

Publish Date: May 30, 2019