

Temperature sensor, Isolated, 0-150°C, 4-20mA, G1/2



# SRTH600-203-2201 Temperature Sensor

#### **Features**

- · Simple installation
- · Isolation structure
- · 316L Stainless steel housing
- · Reverse polarity and overload protection
- · Fast response
- High accuracy
- · Long-term stability

### **Applications**

- · Pipelines
- · Ventilation systems
- Hydraulic and pneumatic systems
- · Cooling and heating systems

- Water treatment
- HVAC systems
- Automation systems

#### **Description**

1


The L-com SRTH600-203 series of temperature sensors feature a sensitive platinum resistance element, encapsulated in a 316L stainless steel probe. The extended probe isolates the main body from the media and is arc welded for a high strength, vibration resistance and overall durability. High corrosion resistance means compatibility with both gas and liquids. These rugged sensors are well suited for use in factory automation, and other conditions where RFI & EMI may be of concern. The output changes linearly with temperature, and is long term stable to just 0.1% of full scale value. The L-com SRTH600 series is part of the IoT portfolio of products available from L-com, in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for more information on this, and other IoT products from L-com.

#### **General Specifications**

Application: Temperature Sensor

Mounting: G1/2 fitting
Electric Connector: flying leads

Process Connection Gender: Male
Reverse Polarity Protection: Yes
Sensing Element: PT100
Output Signal: 4-20mA
Cable Length: 1 m



Description	Minimum	Typical	Maximum	Unit	
Accuracy (Temperature)		±0.5		%	
Long Term Stability		±0.1		% FS/yr	
Zero Drift		0.02		%FS/C	
Temperature Range	0		150	deg C	
Pressure Resistance		300		bar	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Temperature sensor, Isolated, 0-150°C, 4-20mA, G1/2 SRTH600-203-2201



Temperature sensor, Isolated, 0-150°C, 4-20mA, G1/2



# SRTH600-203-2201 Temperature Sensor

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Unit	
Power Supply Voltage	9	24	30	VDC	

## **Material Specifications**

Description	Material	
Casing	Stainless Steel 316L	
Probe Material	Stainless Steel 316L	
Cable Material	PVC	

## **Environmental Specifications**

Temperature (Operating) -40deg C to 85deg C
Temperature (Storage) -40deg C to 125deg C

Impact 100g, 11ms
Ingress Protection IP65

#### Certifications

ROHS Compliant

**CE** Compliant

The Infinite Electronics portfolio includes coaxial cable assemblies, connectors, adapters and custom products, as well as our wireless product line which includes antennas, RF amplifiers, lightning and surge protectors, and NEMA rated enclosures.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.

**SRTH600-203-2201 CAD Drawing** Temperature sensor, Isolated, 0-150°C, 4-20mA, G1/2

