

698 - 960 MHz / 1710 - 2700 MHz / 3300 - 6000 MHz, 10 / 11 dBi, Log Periodic Antenna, Low PIM, V-pol, Type N Female connector

LCANLP1014



Features

- Frequency coverage for 698 MHz to 6000 MHz
- Very High Gain 11 dBi Low PIM Directional Antenna
- · Each connector covers wide band of frequencies
- · Easy Install universal mounting bracket provided
- Weatherproof ABS UV Resistance PVC radome
- Pigtail 8 inches
- N-Type Female connector

Applications

- Point-to-point, LPWAN, LoRA, LTE-M, NB-IoT, IoT, CBRS, M2M
 DAS (Distributed Antenna Systems) applications
- 5G / 4G LTE B1 to B10, B12 to B20, B23, B22, B24, B25, B28 / Public safety, utilities, CCTV and local radio coverage 3G / GSM / AWS / WLAN/ CBRS operation supported
- 5G Bands supported

- IEEE 802.11a / b /g / n / ac / ad / ah/ ax Wi-Fi applications
- Smart cities expansion for coverage and IOT / IIOT

Description

The L-com LCANLP1014 is a high performance, wideband log periodic antenna designed to operate from 698 to 6000 MHz for point to point communications. The LCANLP1014 from L-com has 11 dBi of gain and can be used for long distance directional communication over a wide range of frequencies. The LCANLP1014 is ideal for boosting 5G, LTE, CMDA, LoRA, IoT, WIFI.

The log periodic LCANLP1014 has 50 vertical beamwidth and 65 horizontal beamwidth. This antenna has Vertical polarization and the included mounting brackets allow for either vertical or horizontal mounting configurations. Log periodic antennas function as boosters where the existing cellular signal is weak and needs to reach further distances. The L-com directional antenna has a 8 inches long pigtail terminated with 1 Type N Female connector.

L-com's 698 to 6000 MHz log periodic LCANLP1014 antenna with 11 dBi max gain for 5G DAS networks operates in bands n1, n2, n3, n5, n7, n8, n12, n13, n14, n18, n20, n25, n26, n28, n29, n30, n34, n38, n39, n40, n41, n46, n47, n48, n53, n65, n66, n67, n67, n70, n71, n77, n78,n79, n80, n81, n82, n83, n84, n85, n86, n89, n90, n91, n92, n93, n94, n95, n96, n97, n98. This 5G directional log periodic antenna with N Female Type connector is in stock and ready to ship the same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

Configuration

Design Band Type Radiation Pattern Polarization Cable Type Cable Length Connector Type Number of Ports

Log Periodic Multi Directional Vertical RG58U 7.87 in [199.9 mm] N Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units	
Frequency Range	698		6,000	MHz	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 698 - 960 MHz / 1710 - 2700 MHz / 3300 - 6000 MHz, 10 / 11 dBi, Log Periodic Antenna, Low PIM, V-pol, Type N Female connector LCANLP1014



698 - 960 MHz / 1710 - 2700 MHz / 3300 - 6000 MHz, 10 / 11 dBi, Log Periodic Antenna, Low PIM, V-pol, Type N Female connector

LCANLP1014

Input VSWR		1.7:1	2:1	
Impedance		50		Ohms
Gain	10		11	dBi
Horizontal Beamwidth	50		65	Degrees
Vertical Beamwidth	45		50	Degrees
Input Power			100	Watts

Specifications by Band

Band 1	Band 2	Band 3	Band 4	Band 5	Units
0.698 to 0.96	1.71 to 2.7	3.3 to 6			GHz
10	11	11			dBi
65	50	50			Degrees
50	45	45			Degrees
2:1	1.7:1	2:1			
100	100	100			Watts
	0.698 to 0.96 10 65 50 2:1	0.698 to 0.96 1.71 to 2.7 10 11 65 50 50 45 2:1 1.7:1	0.698 to 0.96 1.71 to 2.7 3.3 to 6 10 11 11 65 50 50 50 45 45 2:1 1.7:1 2:1	0.698 to 0.96 1.71 to 2.7 3.3 to 6 10 11 11 65 50 50 50 45 45 2:1 1.7:1 2:1	0.698 to 0.96 1.71 to 2.7 3.3 to 6 10 11 11 65 50 50 50 45 45 2:1 1.7:1 2:1

Mechanical Specifications

 Radome Material
 ABS

 Width
 8.27 in [210.06 mm]

 Height
 16.14 in [409.96 mm]

 Weight
 2.2 lbs [997.9 g]

Environmental Specifications

TemperatureOperating Range
Wind Survivability
Wind Loading

-40 to +60 deg C 150 MPH [241.4 KPH] 23.5 lbs at 100 MPH 36.2 lbs at 125 MPH

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

698 - 960 MHz / 1710 - 2700 MHz / 3300 - 6000 MHz, 10 / 11 dBi, Log Periodic Antenna, Low PIM, V-pol, Type N Female connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors,



698 - 960 MHz / 1710 - 2700 MHz / 3300 - 6000 MHz, 10 / 11 dBi, Log Periodic Antenna, Low PIM, V-pol, Type N Female connector

LCANLP1014

adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

