



MODEL A10160-DST

45MHz 34Vp-p Single Channel Signal Amplifier

- 45MHz bandwidth
- High amplitude to 34Vp-p into 50
- High output current drive to 1A
- Fast transition time of <10ns
- · Small footprint, all metal case
- · Custom gain configuration
- Low distortion

Model A10160 is an ultra-small footprint, wideband, DC coupled amplifier d esigned for high frequency, high current, signal amplification. With a high bandwidth of 45MHz, 34Vp-p into 50 ohms and up to 10W output power, the A10160 is the ideal complementary amplifier to any signal source that needs a supporting power boost for demanding applications.

Enhancing Performance

The A10160 was designed as a "Snap-On" accessory for the Tabor WaveXciter series and models WS8351/2, both having a maximum amplitude of 4Vp-p, which can be limiting for some applications, requiring higher voltage and current to drive their UUT. Combined with the A10160 the WX and WS models will now offer even higher abilities to solve demanding application requiring up to 45MHz signals at 34Vp-p into 50 ohms loads, without compromising their signal integrity.

High Current High Power

With a peak output current of 1A and 750mA continuous the A10160 enables a continuous power output of 7.5W, and a peak output power of up to 10W, making it ideal for various pulse applications.

Cost Effective Versatile Solution

While the A10160 was designed with the Tabor units in mind, it can be used as a standalone amplifier for any signal source. The A10160 offers a compatible, compact and cost effective solution for extending any signal source's power performance.



Optional Configurations

The A10160's standard configuration enables a maximum output voltage of 34Vp-p into 50 ohms with a gain of x10. Other custom gain, such as x15 or 20 can be ordered at the time of the purchase, enabling clients' even wider variety of choices to solve their application.

Target Applications

While target applications include piezoelectronics, transducer characterization, MEMS, general electronics and scientific applications, the new A10160 is an ideal solution for virtually any wide bandwidth application that requires high voltage and high current amplification.



MODEL A10160

45MHz 34Vp-p Single Channel Signal Amplifier

Specification

INPUT CHARACTERISTICS

Channels: 1

Type: Single Ended

Connector: Front panel SMA

Impedance: 50Ω Coupling: DC

Damage Level: 6Vp-p (-3V to +3V peaks)

Frequency Range: DC to 45MHz

OUTPUT CHARACTERISTICS

No. of Channels: 1

Type: Single Ended

Coupling: DC coupled

Connector: Rear panel BNC

Gain: x10, fixed (x15 gain optional)

Polarity: Normal Amplitude:

Peak 34Vp-p into 50Ω Continuous 30Vp-p into 50Ω

Max. Output Current:

Peak 1A 750mA Impedance: $2.5\Omega \pm 5\%$

Protection: Short Circuit to Case Ground &

thermal protection

SQUARE WAVE CHARACTERISTICS

Transition Time: <10ns (typ.)

Aberration:

10Vpp <5% 34Vpp <10%

SINE WAVE CHARACTERISTICS

Bandwidth (-3dB):

<10Vpp 45MHz (typ.) <34Vpp 30MHz (typ.)

Harmonics & Non-Harmonic Distortion (typ.)

 10Vpp
 25Vpp

 1MHz
 <-58dBc</td>
 <-54dBc</td>

 10MHz
 <-45dBc</td>
 <-45dBc</td>

 30MHz
 <-42dBc</td>
 <-30dBc</td>

GENERAL

Voltage: ±20VDC

Power Consumption: 20W Signal Ground: Grounded

Dimensions: 45 x 30 x 85 mm (W x H x D)

Weight:

Without Package 115 g (Standalone)

Shipping Weight

1 x A10160 Kit 1.25 Kg 2 x A10160 Kit 1.45 Kg

Temperature:

Operating 0°C to 40°C
Storage -40°C to 70°C **Humidity:** 80% RH, non-condensing **Safety:** CE Marked, IEC61010-1

Calibration: 1 years **Warranty:** 1 year

ORDERING INFORMATION

MODEL DESCRIPTION A10160-10 (1)

45MHz 34Vp-p,

Single Channel Signal

Amplifier

Gain: 10 = x10 gain, fixed

15 = x15 gain, fixed

20 = x20 gain, fixed

(1) Standard Configuration

(2) Specification is given for the standard

configuration only

The contents of this document are provided by Tabor Electronics, 'as is'. Tabor makes no representations nor warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to the specification at any time without notice. Ver 1.0