Wide input voltage non-isolated and regulated single

Features

- Ultra-small, ultra-thin DFN package(9mm × 7mm × 3mm)
- Operating ambient temperature range: -40°C to +105°C
- High efficiency up to 94%
- No-load input current as low as 0.1mA
- Continuous short circuit protection
- Meets EN62368
- Meets AEC-Q100 (under testing)
- No heat sink required
- 1.0A DFN package
- · Short circuit protection
- Low ripple and noise
- MTBF: 8552k hours (Mil-HDBK-217F @ 25°C)
- 3 Years Warranty

Selection Guide								
Part Number	Input Voltage (VDC)*	Output		Full Load Efficiency (%) Typ. Vin Min./ Vin Nominal / Vin Max.	Capacitive Load (μF)			
	Nominal (Range)	Voltage (VDC)	Current (mA) Max.		Wax.			
MP-K7803MT-1000R4	24 (4.75-36)	3.3	1000	89/84/81	680			
MP-K7803MT-1000R4(100)	12 (8-27)	-3.3	-500	85/85/81	330			
MP-K7805MT-1000R4	24 (6.5-36)	5	1000	92/87/84	680			
MP-K7805MT-1000R4(100)	12 (8-27)	-5	-500	85/85/83	330			
MP-K7812MT-1000R4	24 (15-36)	12	1000	94/91/89	680			
MP-K7812MT-1000R4(100)	12 (8-20)	-12	-300	83/85/84	330			
Note: * For input voltage exc	eeding 30 VDC, an input	capacitor of 22u	F/50V is required	d.				

Input Specifications									
Item	Operating Conditions	Unit							
No-load Input Current	Nominal input voltage		0.1		mA				
Reverse Polarity at Input	Avoid / Not protected								
Input Filter		Capacitance filter							
Ctrl*	Module on	Ctrl pin open or pulled high(TTL 1.6V DC to 5V DC)							
Cin	Module off	Ctrl pin pul	led low to GNE	D(-Vo)(0V DC t	o 0.6V DC)				
Nominal input voltage, input current when off		240 uA			uA				
Note: *The positive output	ctrl pin voltage is referenced to input GN	ID; Negative o	utput ctrl pin v	oltage is refer	enced to -Vo.				

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro







Description

The MP-K78_MT-1000R4 series are high efficiency switching regulators. The converters feature high efficiency, low loss and short-circuit protection in a compact DFN package. These products are widely used in applications such as industrial control, instrumentation and electric power.

Output Specifications							
Item	Operating Co	Min.	Тур.	Max.	Unit		
Veltage Assuracy	Full load, input	3.3 VDC output		1.2	±4		
Voltage Accuracy	voltage range	Others		<u> </u>	±3	0/	
Linear Regulation	Full load, input voltage range	9		±0.2		%	
Load Regulation	Nominal input voltage, 10% ·	Nominal input voltage, 10% -100% load					
	20MHz bandwidth, nominal input voltage, full load			75	150		
Ripple & Noise*	20MHz bandwidth, nominal input voltage, full load, external capacitor 22µF			- 20	75	mVp-p	
Temperature Coefficient	Operating temperature -40°C		±0.02		%/°C		
Transient Response Deviation	Nominal input voltage, 25%	3.3 V/5V/6.5V/9VDC output		50	150	mV	
	load step change	12V/15VDC output		100	300		
Transient Recovery Time	Nominal input voltage, 25%		0.1	0.8	ms		
Short-circuit Protection	Continuou				self-re	covery	
Trim	Input voltage range		±10		%Vo		
Note: * The "parallel cable" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information:							

General Specifications					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Operating Temperature	See Fig. 1	-40		+105	°C
Storage Temperature		-55		+125	0
Storage Humidity	Non-condensing	5		95	%RH
Reflow Soldering Temperature		Peak t max. IPC	emperatu tion over 217 /JEDEC、	ıre ≤245° ≤60s °C. Also J-STD-02	°C, dura- refer to 20D.1.
Switching Frequency	Full load, nominal input voltage		1		MHz
MTBF	MIL-HDBK-217F@25°C	8552			K hours
Moisture Sensitivity Level (MSL)	IPC/JEDEC J-STD-020D.1		Le	vel 3	
Pollution Degree			P	D3	

Mechanical Specifications						
Case Material	Black epoxy resin; flame-retardant and heat-resistant(UL94 V-0)					
Dimensions	9mm × 7mm × 3.1mm					
Weight	0.58g (Typ.)					
Cooling Method	Free air convection					

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Non Isolated Board Mount multicomp PRO **DC / DC Converters**

Electromagnetic Compatibility (EMC)								
Emissions	CE	CISPR32/EN55032	CLASS B (see Fig. 3-2 for recommended circuit)					
Emissions	RE	CISPR32/EN55032	CLASS B (see Fig. 3-2 for recommended circuit)					
	ESD*	IEC/EN 61000-4-2	Contact ±6KV	perf. Criteria B				
	RS	IEC/EN 61000-4-3	10V/m	perf. Criteria A				
Immunity	CS	IEC/EN 61000-4-6	3Vr.m.s	perf. Criteria A				
minumy	EFT	IEC/EN 61000-4-4	±1KV (see Fig. 3-1 for recommended circuit)	perf. Criteria B				
	Surge	IEC/EN 61000-4-5	line to line ± 1 KV (see Fig. 3-1 for recommended circuit)	perf. Criteria B				

Typical Characteristic Curves





Fig. 1

Design Reference



Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



C2

Ra1/Ra2

(Trim

resistance))

Refer to Trim

resistance

calculation

Notes:

Negative output Fig. 2 Typical application circuit Table 1

- 1. The required C1 and C2 capacitors must be connected as close as possible to the terminals of the module;
- 2. Refer to Table 1 for C1 and C2 capacitor values. For certain applications, increased values and/or tantalum or low ESR electrolytic capacitors may also be used instead;
- 3. Converter cannot be used for hot swap and with output in parallel.

2. EMC compliance circuit



Part No.	MOV	C1	C2	LDM2	C3	C4
MP-K7803/05/MT-1000R4 MP-K7803/05/MT-1000R4(100) (Positive output)	S20K30	680µF /50V	10µF/50V	68µH		22µF/25V
Others	S20K30	680µF /50V	10µF/50V	68µH	10µF/50V	22µF/25V

Notes: For EMC tests we use Part 1 in Fig.3 for immunity and part 2 for emissions test. Selecting based on needs.

3. Trim Function for Output Voltage Adjustment (open if unused)

1.Positive output application: connect trim resistor to GND/Vo respectively for adjusting up/down. 2.Negative output application: connect trim resistor to GND/Vo- respectively for adjusting up/down





Calculating Trim resistor values:

$$\begin{array}{l} \text{Trim up}: \ \mathbf{R}_{a2} = \frac{aR_2}{R_2 - a} - R_3, \ a = R_2 \, / \, / \, (R_3 + R_{a2}) = \frac{V_{\text{ref}}}{V_{\text{o}}^{-1} \cdot \mathrm{V_{ref}}} R_1 \\ \\ \text{Trim down}: \ \mathbf{R}_{a1} = \frac{aR_1}{R_1 - a} - R_3, \ a = R_1 \, / \, / \, (R_3 + R_{a1}) = \frac{V_{\text{o}}^{-1} \cdot V_{\text{ref}}}{\mathrm{V}_{\text{ref}}} \, R_2 \end{array}$$

Vout(V)	R1(KΩ)	R2(KΩ)	R3(KΩ)	Vref(V)
3.3	150	33	180	0.6
5	100	13.66	82	0.6
6.5	32.4	3.3	20	0.6
9	100	7.14	47	0.6
12	100	5.28	43	0.6
15	180	7.5	51	0.6

Dimensions and Recommended Layout

Vout nom.	±3.3	VDC	±5.0	VDC	±6.5	VDC	±9.0	VDC	±12	VDC	±15	VDC
Vout Trim.	Ra1 (KΩ)	Ra2 (KΩ)										
2.97	815	-	-	-	-	-	-	-	-	-	-	-
3.63	-	117.3	-	-	-	-	-	-	-	-	-	-
4.5	-	-	710	-	-	-	-	-	-	-	-	-
5.5	-	-	-	36.2	-	-	-	-	-	-	-	-
5.85	-	-	-		245.4	-	-	-	-	-	-	-
7.15	-	-	-	-	-	9.5	-	-	-	-	-	-
8.1	-	-	-	-	-	-	783.2	-	-	-	-	-
9.9	-	-	-	-	-	-	-	19.9	-	-	-	-
10.8	-	-	-	-	-	-	-	-	382.2	-	-	-
13.2	-	-	-	-	-	-	-	-	-	5.5	-	-
13.5	-	-	-	-	-	-	-	-	-	-	509.6	-
16.5	-	-	-	-	-	-	-	-	-	-	-	21

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Dimensions and Recommended Layout





Note: Grid 2.54*2.54mm

Pin-Out						
Pin	Positive output	Nagative output				
1	+Vin	+Vin				
2	GND	-Vo				
3	+Vo	GND				
4	Trim	Trim				
5	GND	-Vo				
6	Ctrl	Ctrl				

Unit :mm[inch] Pin diameter tolerances : $\pm 0.10[\pm 0.004]$

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability for loss or damage resulting from any reliance on the Information or use of it (including liability of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

