

5725 MHz - 5850 MHz, 16 dBi, Log Periodic Antenna, High Gain, V-pol, Type N Female connector

LCANLP1011



Features

- Frequency coverage for 5725 MHz to 5850 MHz
- · Very High Gain 16 dBi Directional Antenna
- · Each connector covers wide band of frequencies
- · Easy Install universal mounting bracket provided

Applications

- Point-to-point, NB-IoT, IoT, M2M applications
- 5G / WLAN / Sub-6 GHz operation supported
- 5G Bands supported n46, n47
- DAS (Distributed Antenna Systems)

- · Weatherproof ABS radome
- Pigtail 9 inches
- N-Type Female connector
- IEEE 802.11a / n / ac / ah / ax Wi-Fi applications
- · Public safety, utilities, CCTV and local radio coverage
- Smart cities expansion for coverage and IOT / IIOT

Description

The L-com LCANLP1011 is a high performance, wideband log periodic antenna designed to operate from 5725 to 5850 MHz for point to point communications. The LCANLP1011 from L-com has 16 dbi of gain and can be used for long distance directional communication over a wide range of frequencies. The LCANLP1011 is ideal for boosting 5G, LTE, CMDA, LoRA, IoT, WIFI.

The log periodic LCANLP1011 has 19 vertical beamwidth and 19 horizontal beamwidth. This antenna has Vertical polarization and the included mounting brackets allow for either vertical or horizontal mounting configurations. Log periodic antennas function as boosters where the existing cellular signal is weak and needs to reach further distances. The L-com directional antenna has a 9 inches long pigtail terminated with 1 Type N Female connector.

L-com's 5725 to 5850 MHz log periodic LCANLP1011 antenna with 16 dBi max gain for sub 6 GHz 5G DAS networks operates in bands n46, n47. This 5G directional log periodic antenna with N Female Type connector is in stock and ready to ship the same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

Configuration

Design
Band Type
Radiation Pattern
Polarization
Cable Type
Cable Length
Connector Type
Number of Ports

Log Periodic Single Directional Vertical Coax Cable 9.1 in [231.14 mm] N Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain			16.5	dBi

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 5725 MHz - 5850 MHz, 16 dBi, Log Periodic Antenna, High Gain, V-pol, Type N Female connector LCANLP1011



5725 MHz - 5850 MHz, 16 dBi, Log Periodic Antenna, High Gain, V-pol, Type N Female connector

LCANLP1011

Front to Back Ratio	18		dB
Input Power		100	Watts

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	5.725 to 5.85					GHz
Gain	16					dBi
Horizontal HPBW	19					Degrees
Vertical HPBW	19					Degrees
Front to Back Ratio	18					dB
VSWR Max	1.5:1					
Maximum Input Power	100					Watts

Mechanical Specifications

 Radome Material
 ABS

 Size
 16.53 in [419.86 mm]

 Width
 18.9 in [480.06 mm]

 Width
 18.9 in [480.06 mm]

 Height
 11 in [279.4 mm]

 Weight
 1 lbs [453.59 g]

Environmental Specifications

Temperature

Operating Range -40 to +65 deg C
Wind Survivability 130.5 MPH [210.02 KPH]
Wind Loading 23.5 lbs at 100 MPH
36.2 lbs at 125 MPH

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

5725 MHz - 5850 MHz, 16 dBi, Log Periodic Antenna, High Gain, V-pol, Type N Female connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive,





5725 MHz - 5850 MHz, 16 dBi, Log Periodic Antenna, High Gain, V-pol, Type N Female connector

LCANLP1011



and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

