

Multi-Function Power Meter Eco-POWER METER®

KW9M SERIES



One Meter Works for Both Energy Saving and Power Quality Surveillance



0.2 % High Accuracy, **Multi-Function Power Meter**

featuring demand management and power quality surveillance function in addition to the energy saving




Useful Functions

Function 1


Demand measuring function compliant with IEC61557-12 effective for energy saving * 30-min demand method is also selectable for use in Japan.(Advanced type)

IEC demand (Sliding block interval and Fixed block interval) Users set the time span for demand calculation to an arbitrary value between 1 to 60 minutes (in increments of one minute). The average power demand within the set span is calculated at the end of the span. [The demand values of active, reactive, apparent, active (export), and reactive (export) power are calculated.]



· Sliding block interval method


The next time span starts "n" minutes later. (Value "n" is arbitrarily set by users.)



* Also ready for CT inputs (electric power measurement)

Function 2


Harmonic measurement * Standard type supports THD measurement only. Inverter equipment and fluorescent lighting fixtures are harmonic sources and can have adverse effects on precision equipment, thereby causing it to malfunction. **OK** ental wave Install a harmoni Harm filter for protectio Inverter equipmen



Function 3


Improvement of between phases unbalance (Advanced type)

and the motor torque becomes insufficient, causing a rise in heat or reduction in product life.



Multi-Function Power Meter KW9M SERIES

Eco-POWER METER® is a registered trademark of Panasonic Corporation. (Registered Trademark No. 5501901)



Fixed block interval method

The next time span starts after completion of the current span.

If there is an unbalanced load due to a V-connected transformer or a heater, a voltage imbalance occurs between phases, **OK** Adjust the load at each phase to eliminate b phases unbalance Motor equipment

Features


Multi-Function Power Meter KW9M SERIES

Application Example


Eco-POWER METER® is a registered trademark of Panasonic Corporation. (Registered Trademark No. 5501901)

Feature 1

Large-screen LCD with backlight clearly displays the electric power of each phases and their total on one screen.



Capable of simultaneously measuring up to three circuits in a single phase two-wire system of same power supply The advanced type is also capable of N-phase measurement with the fourth CT.



Feature 5

Various log functions available

٦	Гуре	Standard	Advanced
	Power	-	12 records (for 12-month)
Measurement max value	Current	-	12 records (for 12-month)
for each month	Voltage	-	12 records (for 12-month)
Measurement	Power factor	-	12 records (for 12-month)
min. value for each month	Frequency	_	12 records (for 12-month)
(with time stamp*1)	Unbalanced current	_	12 records (for 12-month)
(marane etamp 1)	Unbalanced voltage	_	12 records (for 12-month)
	e power, apparent power, export reactive power, imp*1)*2	1 record for each, Max. value	12 records (for 12-month), Max. value
	Voltage interruption	_	Up to 10 records
Power quality*1	Over voltage	_	Up to 10 records
(with time stamp for happening date and period)	Under voltage	-	Up to 10 records
	Over current	-	Up to 10 records
	Under current	_	Up to 10 records

Feature 2

Capable of displaying small currents of 1 mA or above This allows for the monitoring of standby power consumption, which helps energy saving

Eco-POWER METER® is a registered trademark of Panasonic Corporation. (Registered Trademark No. 5501901)



* Capable of measuring 0.1 % or higher the rating of the secondary side of CT.

Equipped with input and output terminals (Advanced

(Jbc)	
Two pulse input points	Simultaneously measures data including that other than electric energy (production amount, flow rate, etc.). Capable of time synchronization by inputting a clock setting trigger
Two pulse	The PhotoMOS output allows for connection of NPN input and PNP input devices.

output points Ready for alarm outputs, which are frequently used. Terminal block C (middle) 8F

ferminal block C		number	1	2	3	4	5	6	7	8
8P Ferminal block B	Q O	Functions		COM1	OUT2	COM2	IN1+	IN1-	IN2+	IN2-
8P		1 Uncuons	Outp	out 1	Outp	out 2	Inp	ut 1	Inpu	ut 2
USB port -	╘═╧╱╧┛╝									
Rattery	cover									

Feature 6

Feature 4

Data can be made visualization by connecting the meter to DLL* and logging the data. Alarms can be e-mailed to mobile phones or other equipment.


*DLL is the abbreviation for Data Logger Light.




Feature 7


You can measure power with a direct connection to an already-installed large-capacity general-purpose CT (secondary side 1 A / 5 A type).

* The dedicated CT for Eco-POWER METER[®] cannot be used. Use a CT with a secondary side current of 1 A / 5 A.



The measuring accuracy of the Eco-POWER METER® does not take the CT error into account. Other Eco-POWER METER® series (except KW2M and AKW8115) need to use two CTs for measurement. KW9M is ready for direct input from only one CT, allowing higher accuracy measurements than with other Eco-POWER METER® series.





Free visualization software for supporting energy management Power consumption analysis enhances equipment operation efficiency. (EN)(CH)(ID)(VN)(DE)(ES)(PT)(KR)(JP)LANGUAGE Panasonic **KW Watcher** Ver. 2.10 KW Watcher can be downloaded, free of charge, from our website *You can also check the required operating environments Free software to create graphs from data collected by DLL for energy management

- Cumulative bar charts by equipment and pie charts
- Comparison graphs by time and equipment
- Numeric display function
- Auto graph updating function
- * KW Watcher cannot simultaneously display values of three phases in graphs (Up to two graphs for comparison can be displayed.)

Multi-Function Power Meter KW9M SERIES





Specifications

Multi-Function Power Meter KW9M SERIES

Eco-POWER METER[®] is a registered trademark of Panasonic Corporation. (Registered Trademark No. 5501901)

ORDER GUIDE

Product name	Phase/Wire system	Input measurement voltage	Input measurement current	Applicable current transformer*	Model No.
KW9M Eco-POWER METER® Standard type	Single-phase two-wire (1P2W) Single-phase three-wire (1P3W)	0 to 500 V AC		Secondary side current	AKW91110
KW9M Eco-POWER METER® Advanced type	Three-phase three-wire (3P3W) Three-phase four-wire (3P4W) (common)	(for UL 0 to 300V AC)	1 to 65,535 A	1 A or 5 A	AKW92112

*The dedicated current transformer (CT) can not be used. Please use a CT with a secondary side 1 A / 5 A.

OVERVIEW OF FUNCTIONS

	Туре	Standard	Advanced			
	Active power	Each phase and Total (Import, Export)				
	Reactive power	Each phase and Total (Imp	oort, Export)			
	Apparent power	Each phase and Total				
	Power demand	IEC61557-12 demand	IEC61557-12 demand 30-min demand Peak demand			
	Active electric energy	Each phase and Total (Imp	oort, Export)			
	Reactive electric energy	Each phase and Total (Imp	oort, Export)			
S	Apparent electric energy	Each phase and Total				
Measurement items	Current	Each phase and Average current	Each phase, N-phase (when 3P4W) and Average current			
nt ii	Unbalanced current	_	Total (except N-phase)			
mei	Current THD	Each phase				
ure	Current harmonics	—	Each phase (2nd to 31st harmonics)			
eas	Current demand	Each phase	current demand			
ž	Voltage	Line voltage (Each line and average), I	Phase voltage (Each phase and average)			
	Unbalanced voltage	—	Total			
	Voltage THD	Line and P	hase voltage			
	Voltage harmonics	—	Line and Phase voltage (2nd to 31st harmonics)			
	Power factor	Each phase and Average				
	Frequency	Each phase and Average				
	Pulse count (Integral pulse)	—	2 points			
	Temperature	Ambient t	emperature			
	Calendar	_	Internal clock			
In	put	_	2 points			
0	utput	—	2 points			
' IE	C 61557-12 is an internatio	nal standard on performance r	neasuring and monitoring			

devices (PMD).

■MEASUREMENT ITEMS

Ву Туре

		Туре		Standard	A	dvance	d
Item		Unit	Display data range	Present value (Instantaneous value)	Present value (Instantaneous value)	Maximum	Minimum
Instantaneous	Active	kW					
power	Reactive	kvar	-99999 to 0.000 to				
power	Apparent	kVA	33333				
Integral	Active	kWh	0.00				
power	Reactive	kvarh	0.00 to 9999999.9			_	_
(import)	Apparent	kVAh	10 9999999.9				
Integral power	Active	kWh					
for each time zone (4-zone)	Reactive	kvarh	0.00 to 9999999.9	_		_	_
(import)	Apparent	kVAh	10 9999999.9				
Integral power	Active	kWh	0.000 to	-	-		
(export)	Reactive	kvarh	9999999.9	•	•	-	-
Integral power	Active	kWh					
for each time zone (4-zone) (export)	Reactive	kvarh	0.000 to 9999999.9	-	•	-	-
Current		Α	0.000 to 00000			•	
N-phase v	vhen 3P4W	Α	0.000 to 99999	_		•	
Voltage (Phase and L	ine voltage)	V	0.00 to 99999				
Power factor			-1.000 to 0.000 to 1.000				•
Frequency		Hz	0.00 to 99.99				
Pulse count value			0.000 to 99999999	_		_	—
Power	Total					_	_
conversion value	For each tin	ne zone	0.000 to 99999999	_	•	-	_
Temperature degree		degree C	-100.0 to 100.0			_	_
Calendar			January 1, 2000 00:00:00 to Dec. 31, 2099 23:59:59	_	•	_	_

* "Display data range" is the range to be able to indicate with the main unit display, it is not a range that can be measured.

■MEASUREMENT ITEMS

Power quality							
Item			Present value (Instantaneous value)	Maximum	Minimum		
Each phase	%	0.000 to 999.99					
Each phase	%	0.000 to 999.99					
Each phase	%	0.000 to 400.00		_	_		
Each phase	%	0.000 to 400.00		_	_		
Each phase	%	0.000 to 400.00		_	_		
Phase	%	0.000 to 400.00		-	_		
Line	%	0.000 to 400.00		_	_		
	Each phase Each phase Each phase Each phase Phase	Each phase % Each phase % Each phase % Each phase % Each phase % Phase %	Each phase % 0.000 to 999.99 Each phase % 0.000 to 400.00 Phase % 0.000 to 400.00	Unit Display data range (instantaneous value) Each phase % 0.000 to 999.99 ● Each phase % 0.000 to 999.99 ● Each phase % 0.000 to 999.99 ● Each phase % 0.000 to 400.00 ● Each phase % 0.000 to 400.00 ● Each phase % 0.000 to 400.00 ● Phase % 0.000 to 400.00 ●	Unit Display data range (restanaeous value) Maximum Each phase % 0.000 to 999.99 ● ● Each phase % 0.000 to 999.99 ● ● Each phase % 0.000 to 400.00 ● ● Each phase % 0.000 to 400.00 ● ● Each phase % 0.000 to 400.00 ● ● Phase % 0.000 to 400.00 ● ●		

*1 Only advanced type *2 total harmonic distortion *3 2nd to 31st *4 If the voltage to be measured is not the rated (commercial) frequency, it may take time for THD (total harmonic distortion) to stabilize.

Demand measurement

Ite	em	Unit	Display data range	Present value *3	Maximum	Minimum
	Active	kW				
	Reactive	kvar				
Present	Apparent	kVA	0.000 to 99999			
demand	Active (export)	kW	0.000 10 99999	•	•	-
	Reactive (export)	kvar				
	Current	Α				
Estimated dem	and*1*2	kW	0.000 to 99999		_	_
Ratio of estimate	ed demand*1*2	%	0.000 to 99999		_	_
Integral power converted by pulse*1*2 kWh			0.000 to 999999.99		_	_
The demand va 1 Only advanced		n this fur	standard. action is not guarante	ed.		

*3 Instantaneous value

Weight

450 g approx.

■MAIN UNIT SPECIFICATIONS

Туре		Standard	Advanced				
Supply voltage		85 to 264 V AC					
range	Ţ.	100 to 300 V DC					
Rated fre	equency	50/60 Hz					
Nominal	power	5 VA approx. (240 V AC at 25 °C 77 °F)	6 VA approx. (240 V AC at 25 °C 77 °F)				
consump	tion	3 W approx. (240 V DC at 25 °C 77 °F)	3 W approx. (240 V DC at 25 °C 77 °F)				
Inrush c	urrent	30 A or less (240 V AC/DC at 2	5 °C 77 °F)				
Allowable power-off	momentary time	10 ms or less					
A		Accuracy guarantee: -10 to +5	5 °C 14 to 131 °F				
Ambient tempera		Operation: -25 to +55 °C -14 t Storage: -25 to +70 °C -14 to					
Ambient	humidity	30 to 85 % RH (at 20 °C 68 °F)	non-condensing				
		Between the isolated circuits: 2,000 V/1 min	Between the isolated circuits: 1,500 V/1 min				
Breakdown voltage (initial)		a) enclosure - all terminals b) between insulated circuits power supply terminals - other terminals • RS485 terminals - other terminals • measured current input terminals - other terminals • measured current input terminals - other terminals • observed current input terminals					
Insulation re	sistance (initial)	Between the isolated circuits: 100 MΩ or more					
Vibration	resistance	10 to 150 Hz (7.5 minutes/cycle) single amplitude: 0.075 mm 0.0030 in (1 h on 3 axes) 10 to 55 Hz (1 minute/cycle)					
		single amplitude: 0.375 mm 0.015 in (1 h on 3 axes)					
	esistance	Min. 294 m/s ² (5 times on 3 axes)					
Display I		LCD with backlight					
	pdating time	100 to 1000 ms (set with setting mode)					
Power failur method (wh	re memory en power OFF)	Internal memory (overwrite 101	° or more)				
	Range		From January 1, 2000 00:00:00 to December 31, 2099 23:59:59				
Calendar	Accuracy		±15 seconds/month (at 25 °C 77 °F)				
	Backup		About 1-month (backup with secondary battery) (after passing 48-hour, at 23 °C 73.4 °F)				
Degree of protection		Front: IP51, Back: IP20					
Sea leve	altitude	Under 2,000 m 6,562 ft					
Overvolta	ige category	2					
Pollution	degree	11					
Dimensi	ons W/H/D	96 × 96 × 56 mm 3.78 × 3.78 × 96 × 96 × 68 mm 3.78 × 3.78 ×	2.20 in (without terminal block) 2.68 in (with terminal block)				
M/aiabt		4E0 a annexy	100 a approve (with according (hottom))				

480 g approx. (with secondary battery)

Specifications

MEASUREMENT SPECIFICATIONS

Туре		9	Standard Advanced					
Mea	Measured data		a	AC sine				
Phas	se/V	Vire sy	stem	Single-phase two-wire (1P2W) (max. 3-circuit), Single-phase three-wire (1P3W), Three-phase three-wire (3P3W) and Three-phase four-wire (3P4W) (Common)				
Applic	cable	power	system	100 V system, 200 V system	and 400 V system			
Mea	sure	ed freq	uency	50/60 Hz				
Como		Samp	ling	1.024 MHz (1.0 µs approx.) 1.024 MHz (1.0 µs approx.)				
Sampl rate	ing	Date	Instantaneous value	100 ms 100 ms				
Idic		update	Harmonics	2.25s	22.5s (2nd to 31st)			
		B L-L		0 to 500 V AC				
	Input voltage	1P3W	L-L	0 to 500 V AC				
) et	1530	L-N	0 to 250 V AC				
	f	3P3W	L-L	0 to 500 V AC				
	d L	3P4W	L-L	0 to 500 V AC				
		3P4W	L-N	0 to 289 V AC				
Ð	Im	pedan	ce	2 MΩ or more (L-N: V1/V2/V3	-Vn)			
Voltage	Re	solutio	n	0.01 V				
%	Po	wer co	nsumption	0.2 VA approx. (L-N: V1/V2/V3-Vn)				
	Accuracy*1			0.2 % *0.5 % for 2-phase voltage of 1P3W, 3-1 voltage of 3P3W and line voltage of 3P4W.				
	VT	ratio		1.00 to 600.00 (set with setting mode) *Voltage transformer (VT) is required when you measure a load with voltage over rated voltage. (Rated secondary voltage of VT is 110 V.) *When it input direct, VT ratio is set to 1.00.				
	Inp		Primary current	65,535 A or less				
		rent th CT)	Secondary current	1 A or 5 A (set with setting mode)				
ŧ	Ma	x. curr	rent	10 A (200 % of the rating)				
Current	Ove	erload ca	pacity	1,000 % of the rating for 3s				
Cu	Re	solutio	n	0.001 A				
	Po	wer co	nsumption	0.2 VA approx.				
	Accuracy*1*2			0.2 % *0.5 % for 2 (N) - phase current of 1P3W and 2 (S) - phase current of 3P3W.				
Power	Ac	curacy	*1	0.5 % Active power Class 0.5S (IEC Reactive power Class 2 (IEC	62053-22)			
Tempera- ture	Ac	curacy		±5.0 °C ±41 °F (after ambient temper Passing 2 hours or more after energi				

tire Accuracy Passing 2 hours or more after energized *1 Without error of current transformers (CT) and voltage transformers (VT) *2 As to the current under 5 % of rating, it may not satisfy the accuracy according to CT setting (max, error, 0.5 %). *1 (measures from 0.1 % of CT secondary current. * IEC62053 is the international standard for Electricity metering equipment.

OUTPUT SPECIFICATIONS Only Advanced type

Number of output point Insulation method		2 points *Insulate between output terminals			
		PhotoMOS relay			
Output type		1a			
Output capa	acity	100 mA, 30 V AC/DC			
Output mode (O	UT1/OUT2)	Pulse by integral power Output by alarm or events (set with setting mode)			
Pulse output	Pulse width	100 ms approx.			
by integral power	Pulse output unit	0.0001 kWh / 0.001 kWh / 0.01 kWh / 0.1 kWh /1 kWh / 10 kWh / 100 kWh			
Alarm output Event output	Туре	Stand-by power alarm / Under voltage alarm / Over voltage alarm / Power interruption alarm / Under current alarm / Over current alarm / Active power alarm / Reactive power alarm / Apparent power alarm / Power factor alarm / Over frequency alarm / Under frequency alarm / Voltage harmonics alarm / Current harmonics alarm / Voltage THD alarm / Current THD alarm / Unbalanced voltage alarm / Unbalanced current alarm / Power demand alarm / Current demand alarm / Counter output / Level output (external control)			
	Alarm reset	Self-reset (according to the setting) / Manual-reset			
Protection e	lement	Varistor*			
	otective device	rnal as a protection element. the place where it effects by surge.			
		where to be measured from the unit of the integral power pulse output. (Max. measurement power [kW]) / (3,600 sec \times 1 pulse/sec)			
pulse o	output is 3.6 kW ad is higher that es becomes sm	t unit is 0.001, the maximum power that can be properly measured by (3,600 sec × 1 pulse/sec × 0.001). an this value, the output pulses cannot keep up with it, and the number all. pulse output unit to the value immediately above.			
of puls	i cases, set the				
of puls In such (2) Calculate th	ne appropriate p	ulse output unit from the instantaneous power to be measured. ower [kW]/3,600 sec × 1 pulse/sec) < Unit for pulse output			
of pulse In such (2) Calculate th (Max. r When t correct	ne appropriate p neasurement p the maximum p pulse output is				

Multi-Function Power Meter KW9M SERIES

Eco-POWER METER® is a registered trademark of Panasonic Corporation. (Registered Trademark No. 5501901)

INPUT SPECIFICATIONS (Only Advanced type)

Number of inp	ut point	2 points *Not insulate between input terminals (COM is common.)			
Insulation met	hod	Designated insulation for input (insulate to the other functions)			
Input method		Contact/ non-voltage a contact or open-collector (Powered by an internal power supply)			
Input signal		Non- voltage input	 Impedance; Max. 1 kΩ (when short-circuit current: Max. 10 mA) Residual voltage when shorted: Max. 3 V Impedance when open: Min. 100 kΩ 		
In nut mode	IN1	Pulse input or synchronized with output from outer device			
Input mode	IN2	Pulse input			
Max. counting	IN1	30 Hz (when pulse input)			
speed	IN2	2000 Hz / 30 Hz			
Min. in such	IN1	16.7 ms ON:OFF ratio = 1:1			
Min. input signal width	IN2	0.25 ms (when 2000 Hz is set) / 16.7 ms (when 30 Hz is set) ON:OFF ratio = 1:1			
	Decimal point	Under 3-	digit		
Pre-scale Range		0.001 to 100.000 (set with setting mode)			
Output mode (when pulse output is selected)		HOLD			
Protective eler	ments	Zener diode			

■DEMAND MONITOR AND CONTROL SPECIFICATIONS AKW91110 supports only marked items (•)

Demano	d type		Peak demand IEC61557-12 demand (•) I. Sliding block interval demand Z. Fixed block interval demand Current demand S0-min demand (set with setting mode)								
Demano type	d monitor	input	Current transformer (CT) input (IEC demand /30-min demand)) (•) Integral pulse input (only 30-min demand) (set with setting mode)								
Demand IEC61557-12 demand (•) time span*1 30-min demand			1 to 60 min. (set with setting mode) 30 min. (fixed)								
Demand	measurer	nent item	Present demand, Estimated demand (only 30-min demand)								
Demand calculate method*2			Additional method / Average method (set with setting mode)								
Demand of	data update	e cycle (•)									
Demand sta	and-by time (mask time)*	1 to 30 min. (set with setting mode)								
	IEC61557-12	2 demand (•)	Present demand (Active/Reactive/Apparent/Active(export)/Reactive(export)/Current)								
Display 30-min demand		emand	Power demand (active power), Estimated demand, Demand target value, Ratio of estimated demand, Current present demand, Monthly max. demand, Max. demand								
Saved data			Monthly max. demand 12 records (12-month), Max.demand (•)								
Time span synchronized method			Clock synchronized (Pulse input to IN1) (set with setting mode)								
Svnchro-	Input te	rminal	IN1								
nized	Input m	ethod	Non-voltage a contact or open-collector (Powered by an internal power supply)								
signal	Pulse inpu	t condition	Pulse width 50 ms or more								
input	Operatingvo	tage/ current	5 V DC 10 mA								
<in1></in1>	Signal common		Common (IN2; common to pulse input)								
	Input te	rminal	IN2								
Pulse input <in2></in2>	Input m	ethod	Non-voltage a contact or open-collector (Powered by an internal power supply)								
	Pulse in signal	put	50,000 pulse/kWh <an detector="" external="" pulse="" required=""> 2,000 pulse/kWh <an convertor="" external="" pulse="" required=""></an></an>								
	Pul	se rate	0.001 to 100.000 kWh/pulse								
	Pulse input condition	2000 Hz 30 Hz	Pulse width 0.25 ms or more Pulse interval 0.5 ms or more (OFF: 0.25 ms or more) Pulse width 16.7 ms or more Pulse interval 33.4 ms or more (OFF: 16.7 ms or more)								
	Operating vo	Itage/ current	5 V DC 10 mA								
	Signal c	ommon	Common (IN1; common to clock synchronized input)								

*1 The time span can be arbitrarily set only for sliding block interval demand and fixed block interval demand. *2 Available when 30-min demand is selected.

COMMUNICATION SPECIFICATIONS

<rs485< th=""><th>5></th><th></th></rs485<>	5>								
Interface		Conforming to RS485							
Communication method		Half-duplex							
Synchronous system		Synchronous communication method							
Isolation status		Isolated with the internal circuits							
Protocol		MEWTOCOL, MODBUS (RTU), DL/T645-2007*1 (select with setting mode)							
Number of connected unit		99 (max.)*2							
Transmission distance		1,200 m 3,937 ft*3							
Transmiss	ion speed	38,400, 19,200, 9,600, 4,800, 2,400, 1,200 bps (select with setting mode)							
-	Data length	8bit (fixed)							
Transmission format	Parity	Not available / odd number / even number (select with setting mode)							
IUIIIal	Stop bit	1bit, 2bit (select with setting mode)							
*1 MEWTO	COL is the r	protocol for PLC from Panasonic, DL/T645 is the China power-meter							

*1 MEWTOCOL is the protocol for PLC from Panasonic. DL/T645 is the China power-meter standard. Only DL/T645-2007 is supported.
*2 For R5485 converter on the computer side, we recommend SI-35 and SI-35USB (from LINE EYE Co., Ltd.). When using SI-35, SI-35USB or PLC from our company (which can be connected up to 99 units), up to 99 can be connected.
In case using this system with the other devices, up to 31 can be connected.
*3 Please check with the actual devices when some commercial devices with R5485 interface are connected. The number of connected devices, transmission distance, and transmission speed may be different according to using transmission line.


Dimensions

Multi-Function Power Meter Eco-POWER METER® KW9M SERIES

Applicable panel thickness: 1 to 5 mm 0.039 to 0.197 in

EXTERNAL DIMENSIONS

Eco-POWER METER® is a registered trademark of Panasonic Corporation. (Registered Trademark No. 5501901) (Unit: mm in)




TERMINAL ARRANGEMENT AND WIRING DIAGRAMS

Terminal wiring

- · Be sure to wire correctly according to the terminal arrangement and wiring diagrams · Please connect a fuse or a breaker to power supply part for safety reasons, to protect the device
- and ease of maintenance. This has no built-in power switch, circuit breaker or fuse for measured voltage input parts.
- Therefore it is necessary to install them in the circuit near this unit.
- Do not turn on the power supply or input until all wiring is completed.
 Do not open the secondary side of CT while the primary side current is energized. Do not remove the terminal block while the primary side current of CT is energized. These actions may result in electric shock or CT breakdown.

Rear view



* Advanced type

After use, remove the label, take out the battery, and dispose of it according to the applicable regional (municipal) rules.

Please contact

Terminal arrangement Terminal block A (upper) 10P

icininai b	001070	(uppe	, 10											
Terminal number	1	2	3		4	5	6	7	7	8		9	10	
Functions	L+	N-	V	1	V2	V3	Vn	N	С	SG		A+	8 IN2-	
Functions	AL (Power	JX supply)	Me	easured		voltage	input	nput Va		ant		RS485		
erminal block C (middle) 8P (Only Advanced type)														
Terminal number	1		2		3	4	5	5		6		7	8	
Functions	OUT1 C		M1 C		UT2	COM2	12 IN1-		IN1-		١N	N2+	IN2-	
T unctions		tput 1			Outp	ut 2		npu	ut 1			Inpu	Input 2	
Ferminal block B (lower) 8P														
Terminal number	1	2	3		4	5	6	7	7*	8*				
Functions	CT1 K	CT1 L	CT K		CT2 L	CT3 K	CT3 L		Tn K	CTn L				
			Me	eas	* The N- availab									

Specifications of terminal block A/B

Screw size: M2.5 Tightening torque: 0.4 to 0.5 N+m Applicable wire: (Crimp-type terminal is recommended.) • Single wire 0.13 to 4 mm² (AWG26 to 12) • Stranded wire 0.2 to 4 mm² (AWG24 to 12)


for 2 pcs. Single wire / Stranded wire 2 pcs 0.5 to 2.1 mm² (AWG20 to 14)

Specifications of terminal block C Screw size: M2.0 Tightening torque: 0.2 to 0.25 N•m Applicable wire: (Crimp-type terminal is

recommended.)
 Single wire 0.08 to 1.5 mm² (AWG28 to 16)
 Stranded wire 0.2 to 1.5 mm² (AWG24 to 16)

Stripping length: 7 to 8 mm 0.276 to 0.315 in

Terminal number	1	2	3	4	5	6	7	8	9	10
Europhic and	L+	N-	V1	V2	V3	Vn	NC	SG	A+	B-
Functions	AL (Power		Mea	sured	/oltage	input	Vacant		RS48	5
Terminal b	lock C	(middl	e) 8P	(Only	Advanc	ed typ	e)			
Terminal number	1	2	2	3	4	5		6	7	8
Functions	OUT	1 CO	M1	DUT2	COM2	IN1	11 +	V1-	IN2+	IN2-
FUNCTIONS		tput 1		Outp	ut 2	1	nput 1		Inp	ut 2
Terminal b	lock B	(lower) 8P							
Terminal number	1	2	3	4	5 6 7* 8*					
Functions	CT1 K	CT1 L	CT2 K	CT2 L	CT3 K	CT3 L	CTn K	CTn L		
Functions			Mea	surad		innut			* Th	e N-pha



Connect CTn for the N-phase measurement. CTn is not necessary for normal measurement.

Panasonic Industrial Devices SUNX Co., Ltd.

2431-1 Ushiyama-cho, Kasugai-shi, Aichi, 486-0901, Japan Global Sales Department Telephone: +81-568-33-7861 Facsimile: +81-568-33-8591

panasonic.net/id/pidsx/global



All Rights Reserved © Panasonic Industrial Devices SUNX Co., Ltd. 2016