



Safety Data Sheet according to (EC) No 1907/2006 - ISO 11014-1

Page 1 of 5

96S ARAX SS 4C

SDS no. : 208471

V001.4

Revision: 13.11.2007

printing date: 14.05.2009

1. Identification of the substance/preparation and of the company/undertaking

Trade name:

96S ARAX SS 4C

Intended use:

Solder Wire

Company name:

Henkel AG & Co. KGaA
Henkelstr. 67
40191 Düsseldorf

Germany

Phone: +49 (211) 797-0

E-mail address of person responsible for Safety Data Sheet:

ua-productsafety.uk@uk.henkel.com

Emergency information:

24 Hours Emergency Tel: +44 (0)20 8312 0291

2. Hazards identification

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs.

3. Composition / information on ingredients

Declaration of ingredients according to EC/1907/2006:

Hazardous components CAS-No.	EINECS ELINCS	content	Classification
Tin 7440-31-5	231-141-8	90 - 100 %	
Silver 7440-22-4	231-131-3	1 - 5 %	
Ammonium chloride 12125-02-9	235-186-4	0,1 - 1 %	Xn - Harmful; R22 Xi - Irritant; R36
Ammonium hydrogendifluoride 1341-49-7	215-676-4	0,1 - 1 %	T - Toxic; R25 C - Corrosive; R34

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

4. First aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Obtain medical attention if irritation persists.

Eye contact:

Flush eyes with plenty of water for at least 5 minutes. If irritation persists seek medical attention.

Ingestion:

Do not induce vomiting.
Seek medical advice.

5. Fire fighting measures

Combustion behaviour:

The product itself does not burn. Any fire extinguishing action should be appropriate to the surroundings.

Suitable extinguishing media:

carbon dioxide, foam, powder
fine water spray

Extinguishing media which must not be used for safety reasons:

Do not use water on fires where molten metal is present.

Special protection equipment for firefighters:

Wear self-contained breathing apparatus.

Hazardous combustion products:

High temperatures may produce heavy metal dust, fumes or vapours., The flux medium will give rise to irritating fumes.

6. Accidental release measures

Personal precautions:

Avoid contact with skin and eyes.

Environmental precautions:

Do not empty into drains / surface water / ground water.

Clean-up methods:

Scrape up spilled material and place in a closed container for disposal.

7. Handling and storage

Handling:

Extraction is necessary to remove fumes evolved during reflow.
When using do not eat, drink or smoke.
Wash hands before breaks and immediately after handling the product.

Storage:

Store in a cool, dry place.

8. Exposure controls / personal protection**Components with specific control parameters for workplace:**

Valid for

Great Britain

Basis

UK EH40 WELs

Ingredient	ppm	mg/m ³	Type	Category	Remarks
TIN (INORGANIC COMPOUNDS AS SN) 7440-31-5		2	Time Weighted Average (TWA).		EU-2000/39/EC
SILVER, METALLIC 7440-22-4		0,1	Time Weighted Average (TWA).		EU-2000/39/EC
		0,1	Time Weighted Average (TWA).		EH40 WEL
AMMONIUM CHLORIDE, FUME 12125-02-9		10	Time Weighted Average (TWA).		EH40 WEL
		20	Short Term Exposure Limit (STEL):		EH40 WEL
FLUORIDES, INORGANIC 1341-49-7		2,5	Time Weighted Average (TWA).		EU-2000/39/EC
		2,5	Time Weighted Average (TWA).		EH40 WEL

Engineering controls:

Extraction is necessary to remove fumes evolved during reflow.

Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction.

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment.

Hand protection:

The use of chemical resistant gloves such as Nitrile are recommended

Please note that in practice the working life of chemical resistant gloves may be considerably reduced as a result of many influencing factors (e.g. temperature). Suitable risk assessment should be carried out by the end user. If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

9. Physical and chemical properties**General characteristics:**

Appearance solid material

Odor: grey
none**Phys./chem. properties:**pH-value not applicable
Boiling point Not determined
Flash point not applicable
Vapor pressure not applicable
Density 7,5 g/cm³
(25 °C (77 °F))
Solubility (qualitative) insoluble
(Solvent: Water)
Melting point 221 - 240 °C (429.8 - 464 °F)
VOC content < 5,0 %

10. Stability and reactivity

Conditions to avoid:

Stable under recommended storage conditions.

Materials to avoid:

Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

Hazardous decomposition products:

Thermal decomposition can lead to release of irritating gases and vapors.

11. Toxicological information

Oral toxicity:

This material is considered to have low toxicity if swallowed.

Inhalative toxicity:

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs.

Dermal toxicity:

This product is considered to have low dermal toxicity.

Skin irritation:

Fumes emitted during soldering may irritate the skin.

Eye irritation:

Fumes emitted during soldering may irritate the eyes.

12. Ecological information

Mobility:

The product is insoluble and sinks in water.

Persistence and Biodegradability:

The product is not biodegradable.

Bioaccumulative potential:

No data available.

General ecological information:

No data available.

13. Disposal considerations

Product disposal:

Wherever possible unwanted solder alloy should be recycled for recovery of metal.
Otherwise dispose of in accordance with local and national regulations.

Waste code(EWC):

06 04 05 - wastes containing other heavy metals

Disposal of uncleaned packages:

Dispose of as unused product.

14. Transport information

General information:

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

15. Regulations - classification and identification

Indication of danger:

none

Risk phrases:

not applicable

Safety phrases:

not applicable

Additional information:

Avoid breathing fumes given out during soldering.

Flux fumes may irritate the nose, throat and lungs.

After handling solder wash hands with soap and water before eating, drinking or smoking.

Keep out of reach of children.

National regulations/information (Great Britain):

Remarks

The Health & Safety at Work Act 1974.

The Control of Substances Hazardous to Health Regulations. L5:General Approved Code of Practice to the COSHH Regulations. HS(G)97:A Step by Step Guide to the COSHH Regulations. HS(G)193: COSHH essentials: Easy steps to control chemicals.

16. Other information

The labelling of the product is indicated in Section 15. The full text of the R-phrases indicated by codes in this safety data sheet are as follows:

R22 Harmful if swallowed.

R25 Toxic if swallowed.

R34 Causes burns.

R36 Irritating to eyes.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.