

## Han F+B 5E SMC MI SCT 0,75 - 2,5 mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 505 2601
Specification	Han F+B 5E SMC MI SCT 0,75 - 2,5 mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09155052601">https://b2b.harting.com/09155052601</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> F+B

### Version

Termination method	Screw termination
Gender	Male
With wire protection	Yes
Number of contacts	5
PE contact	Yes

### Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm <sup>2</sup>
Rated current	16 A
Rated voltage	600 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)



Pushing Performance

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0

## Commercial data

Packaging size	1
Net weight	24.7 g
Country of origin	China
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors