

OTi DALI 35/220...240/1A0 NFC I

OPTOTRONIC Intelligent - DALI NFC I (sq) | Compact constant current LED driver - Dimmable



Product family features

- Supply voltage: 220...240 V
- Line frequency: 0 Hz | 50 Hz | 60 Hz
- Lifetime: up to 100,000 hType of protection: IP20
- Integrated cable clamp for luminaire and independent installation
- Through-looping

Product family benefits

- Versatile DALI window driver due to flexible output characteristic
- DALI-2 certified incl. Parts 251, 252, 253
- Easy and fast output current setting via NFC
- Very high efficiency
- High-quality dimming of 1...100 % by amplitude dimming

Areas of application

- Suitable for downlights, spotlights and LED panels
- Suitable for use in luminaires with flexible current setting
- Installation in emergency lighting systems according to IEC 61347-2-13, appendix J
- Suitable for indoor SELV installations
- Suitable for luminaires of protection classes I and II





Technical data

Electrical data

| Nominal input voltage 220240 V Mains frequency $0/50/60 \text{ Hz}$ Input voltage AC 198264 V^{-1} Input voltage DC 176276 V Total harmonic distortion $< 10 \%^{-2}$ Power factor λ > 0.99 Efficiency in full-load $89 \%^{-3}$ Networked standby power $< 0.18 \text{ W}^{-3}$ |
|--|
| Input voltage AC 198264 V $^{1)}$ Input voltage DC 176276 V Total harmonic distortion $< 10 \% ^{2)}$ Power factor λ > 0.99 Efficiency in full-load $89 \% ^{3)}$ |
| Input voltage DC 176276 V Total harmonic distortion $< 10 \%^{2}$ Power factor λ > 0.99 Efficiency in full-load $89 \%^{-3}$ |
| Power factor λ > 0.99 Efficiency in full-load 89 % 3) |
| Efficiency in full-load 89 % ³⁾ |
| , |
| Networked standby power <0.18 W ³⁾ |
| |
| Inrush current 17 A ⁴⁾ |
| Max. ECG no. on circuit breaker 10 A (B) |
| Max. ECG no. on circuit breaker 10 A (C) |
| Max. ECG no. on circuit breaker 16 A (B) 35 |
| Max. ECG no. on circuit breaker 16 A (C) |
| Max. ECG no. on circuit breaker 25 A (B) |
| Surge capability (L/N-Ground) 2 kV |
| Surge capability (L-N) 1 kV |
| Nominal output voltage 1554 V ⁵⁾ |
| U-OUT (working voltage) 60 V |
| Nominal output current 3501050 mA ⁶⁾ |
| Default output current 700 mA |
| Output current tolerance ±5 % |
| Output ripple current (100 Hz) $< 5 \%$ ⁷⁾ |
| Output PSTLM <1 |
| Output SVM <0.4 |
| Nominal output power 5.2535 W |
| Maximum output power 35 W |
| Galvanic isolation primary/secondary SELV |
| Galvanic isolation DALI/mains Basic |
| Galvanic isolation DALI/output SELV |

¹⁾ Permitted voltage range

 $^{^{2)}}$ At full load, 220...240 V, 50 Hz / see graphs


³⁾ at 230 V, 50 Hz


⁴⁾ $_{t}$ = 220 μ s (measured at 50 % I peak) 5) Maximum 60 V

^{6) &}lt;sub>±5%</sub>

⁷⁾ Ripple average at 100 Hz

Dimensions & weight





| Mounting hole spacing, length | 163.0 mm |
|--------------------------------------|----------------------------|
| Product weight | 180.00 g |
| Cable cross-section, input side | 0.751.5 mm ² 1) |
| Cable cross-section, output side | 0.21.5 mm ² 1) |
| Wire preparation length, input side | 8.09.0 mm |
| Wire preparation length, output side | 8.09.0 mm |
| Length | 171.0 mm |
| Width | 83.0 mm |
| Height | 32.0 mm |

¹⁾ Solid or flexible leads

Colors & materials

Temperatures & operating conditions

| Ambient temperature range | -20+60 °C |
|--|---------------------|
| Maximum temperature at tc test point | 75 °C ¹⁾ |
| Max.housing temperature in case of fault | 110 °C |
| Temperature range at storage | -40+85 °C |
| Permitted rel. humidity during operation | 585 % ²⁾ |

¹⁾ Maximum at the Tc-point

Lifespan

 $^{^{1)}}$ T $_{\rm C}$ = 75 °C, 0.2% / 1,000 h failure rate / T $_{\rm C}$ = 65 °C, 0.1% / 1,000 h failure rate

Additional product data

 $^{^{2)}\,\}mathrm{Maximum}$ 56 days/year at 85 %

| Encapsulated | No |
|--------------|----|
| · | |

Capabilities

| Dimmable | Yes |
|--|-------------------------------------|
| Dimming interface | DALI / Touch DIM / Touch DIM Sensor |
| Dimming range | 1100 % 1) |
| Dimming method | Amplitude Modulation |
| Overheating protection | Automatic reversible |
| Overload protection | Automatic reversible |
| Short-circuit protection | Automatic reversible |
| No-load proof | Yes |
| Intended for no-load operation | No |
| Max. cable length to lamp/LED module | 2.0 m ²⁾ |
| Suitable for fixtures with prot. class | 1/11 |
| Type of connection, input side | Push terminal |
| Type of connection, output side | Push terminal |
| Suitable for through-wiring | Yes |
| Suitable for emergency lighting | Yes |
| Constant lumen function | Programmable |
| Programming interface | DALI, NFC |
| Control interface | DALI |
| Number of channels | 1 |
| DALI-2 Energy Data | Yes ³⁾ |
| DALI-2 Diagnostic Data | Yes ⁴⁾ |

 $^{^{1)}\, {\}hbox{For maximum nominal output current}}\\$

Programming

| Box programming | Yes |
|------------------------|------------|
| Tuner4TRONIC | Yes |
| Tuner4TRONIC Field App | No |
| Programming device | DALI / NFC |

Programmable features

| Constant Lumen | Yes |
|---------------------|-----|
| Lamp Operating Time | Yes |
| Driver Guard | Yes |
| DALI Settings | Yes |

 $^{^{\}mbox{\scriptsize 2)}}$ Output wires must be routed as close as possible to each other

³⁾ Acc. DALI part 252

⁴⁾ Acc. DALI part 253

| Emergency Mode | Yes |
|------------------------|-------------------|
| DALI-2 Luminaire Data | Yes ¹⁾ |
| Configuration Lock | Yes |
| Soft Switch Off | Yes |
| Dim to Dark | Yes |
| TouchDIM + Sensor | Yes |
| Corridor Functionality | Yes |
| OEM Key | No |

¹⁾ Acc. DALI part 251

Certificates & standards

| Approval marks – approval | CE / UKCA / EL / DALI-2 / EAC |
|---------------------------|---|
| Standards | Acc. to EN 61347-1/Acc. to EN 61347-2-13/Acc. to EN 55015/Acc. to EN 61547/Acc. to EN 61000-3-2/Acc. to EN 62384/Acc. to EN 62386-Acc. to IEC 62386-101:Ed2/Acc. to IEC 62386-102:Ed2/Acc. to IEC 62386-207:Ed1 |
| Protection class | Ш |
| Type of protection | IP20 |

Logistical data

| Commodity code | 850440829000 |
|----------------|--------------|

Environmental information

| Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACh) | | | | |
|---|--|--|--|--|
| Date of Declaration | 02-03-2022 | | | |
| Primary Article Identifier | 4062172201810 | | | |
| Candidate List Substance 1 | Lead | | | |
| CAS No. of substance 1 | 7439-92-1 | | | |
| Safe Use Instruction | The identification of the Candidate List substance is sufficient to allow safe use of the article. | | | |
| Declaration No. in SCIP database | 81e9413c-fffc-4068-a61a-9d625dda4f56 | | | |

Download Data

| | File |
|---|--|
| Z | User instruction OPTOTRONIC LED Power Supply |
| 乙 | Certificates OT ENEC 40038447 010322 |

| = | CAD data OTI DALI NFC I IGS 140721 |
|----------|---|
| <u> </u> | CAD data OTI DALI NFC I STEP 140721 |
| <u> </u> | CAD Data 2-dim OTI DALI NFC I CAD2PDF 140721 |
| <u> </u> | CAD data 3-dim OTI DALI NFC I CAD3PDF 140721 |

Ecodesign regulation information:

Intended for use with LED modules.

The forward voltage of the LED light source shall be within the defined operating window of the control gear in all operating conditions including dimming if applicable.

Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Logistical Data

| Product code | Product description | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Volume | Gross weight |
|---------------|---------------------------------|------------------------------|--------------------------------------|----------|--------------|
| 4062172201810 | OTi DALI 35/220240/1A0 NFC I | Shipping carton box 16 | 366 mm x 268 mm x 100 mm | 9.81 dm³ | 3196.00 g |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Data privacy

This OSRAM driver can be configured using the Tuner4TRONIC software. This requires registering on www.myosram.com and downloading theTuner4TRONIC software from the Internet. The Tuner4TRONIC software enables users to access and view the operational data of a luminaire or driver via the corresponding programming interfaces. A password key (Config Lock) must be set up in the driver via the Tuner4TRONIC software in order to control which users can access and view operational data. Follow the instructions for password setup. To grant an external person or company rights to access or view operational data, you can assign password keys. In this case, however, you are responsible for ensuring that the third party concerned takes notice of the information described here. However, OSRAM can read out operating data from devices for maintenance and service purposes even when a password key has been assigned. In individual cases, OSRAM will also use its access rights in order to optimize or improve driver hardware and driver functions. In accordance with data privacy principles, any user of operating data (luminaire manufacturers, third parties with access rights) must ensure that personal data (e.g. name, address, location IDs) are only merged with the prior written consent of the person (end user) concerned. The respective user of the operating data is responsible for providing evidence of consent.

| 11 | 150 | ıa | ım | ρг |
|----|-----|----|----|----|

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.