



Ordering Information

IP67 SMA Front Mount Bulkhead Jacks

Part Number	Description
132397	IP67 SMA Straight Crimp Front Mount Jack Bulkhead, 1.13 mm
901-10797	IP67 SMA Straight Crimp Front Mount Jack Bulkhead, 1.32 mm
901-10798	IP67 SMA Straight Crimp Front Mount Jack Bulkhead, 1.37 mm
901-10812	IP67 SMA Straight Crimp Front Mount Jack Bulkhead, RG-178
901-10813	IP67 SMA Straight Crimp Front Mount Jack Bulkhead, RG-316DB
901-10814	IP67 SMA Straight Crimp Front Mount Jack Bulkhead, RG-402
901-10816	IP67 SMA Straight Crimp Front Mount Jack Bulkhead, RG-58

Overview

Amphenol RF offers a number of 50 ohm front mount SMA bulkhead jacks fully tested to IP67 specifications in the mated and unmated condition. These connectors are designed on a variety of industry-standard flexible and semi-rigid cable types and available in the straight crimp configuration. They feature a threaded coupling mechanism for secure mating.

The front mount bulkhead SMA jack can be fastened inside of a panel or enclosure to provide additional security for sensitive systems and feature a threaded coupling mechanism for secure mating. This is aided by a tamper resistant design and the flexibility of the micro-coax cables.

Features and Benefits

- Waterproof IP67 rated
- Reliable electrical performance up to 6 GHz
- Threaded coupling mechanism for secure mating
- Vibration and tamper resistant design
- Ideal for applications with space constraints

Applications

- Antennas
- Base Stations
- Drones
- Test and Measurement Equipment
- Industrial Automation and Inspection
- Bluetooth and Cellular technology
- WLAN

Amphenol RF

Four Old Newtown Road
Danbury, CT 06810

For more information visit www.amphenolrf.com
or call 800.627.7100

Technical Specifications

Electrical

Impedance	50Ω
Frequency Range	DC - 6 GHz
Voltage Rating	333 V RMS Max Continuous
Dielectric Withstanding Voltage	1000 VRMS Min
VSWR (Return Loss)	Varies
Insulation Resistance	5000 MΩ Min
Center Contact Resistance	3.0 mΩ Min
Outer Contact Resistance	2.0 mΩ Min

Environmental

Temperature Range	-65°C to +165°C
RoHS Compliance	Compliant with Exemption 6C

Mechanical

Mating Cycles	500 Min
Coupling Mechanism	Threaded

Materials

Body	Brass, Nickel Plating
Contact	Beryllium Copper, Gold Plating
Hex Nut	Brass, Nickel Plating
Lock Washer	Brass, Nickel Plating
Insulator	PTFE, Natural
Ferrule	Copper, Nickel Plating
Gasket	Silicone Rubber, Red
O-Ring	Silicone Rubber, Blue

Note: Technical specifications are typical and may vary by specific part number. Please see component drawing.

Amphenol RF

Four Old Newtown Road
Danbury, CT 06810

For more information visit www.amphenolrf.com
or call 800.627.7100