Specifications

multicomp PRO

RoHS

Compliant




Operation Voltage Current Rating Contact Resistance Insulation Resistance Dielectric Withstanding Voltage Operating Temperature **Material** Insulator Contacts Contact Plating

: 250V AC Max. : 3 Amps Max. : 30mΩ Max. : 1000MΩ Min : 500V AC / Minute : -40°C to +105°C

: PBT, Rated UL94V-0

- : Brass
- : Underplate: 50m" Nickel
- Solder Tails Area: 80m" ~ 120m" Tin/Lead Free (Matte Tin)

Diagram



Dimensions : Millimetres

Part Number Table

Description	Number	Α	В	С	D	E	F	
	of pins	(mm)	(mm)	(mm)	(mm)	(mm)	(mm)	Part Number
Thru Hole Chip Carrier, Plastic Leaded	28	18.3	18.3	7.62	7.62	7.62	7.62	SPC15567
	32	18	20.8	7.62	10.16	7.62	5.08	SPC15568
	44	23.5	23.5	12.7	12.7	12.7	12.7	SPC15569
	68	31.56	31.56	20.32	20.32	20.32	20.32	SPC15570
	84	36.66	36.66	25.4	25.4	25.4	25.4	SPC15571

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

