Pin Headers

multicomp PRO


RoHS Compliant



Specifications

Current Rating Voltage Rating Temperature Range Contact Resistance Insulation Resistance Withstanding Voltage Material Colour

- : 3A AC/DC
- : 250V AC/DC
- : -25°C to +85°C : 20mΩ Max.
- . 201102 1018X.
- : 1000MΩ Min.
- : 1500V AC/minute
- : PBT30%GF, UL94V-0
- : Black



Part Number Table

Description	No. of Position	Pin Material	Part Number
Pin Header, Board-to-Board, 2.54mm, Through Hole	2	Brass, Flash Gold Plated	SPC20481
	3		SPC20482
	4		SPC20483
	40		SPC20484
	2	Brass, Tin Plating	SPC20485
	3		SPC20486
	4		SPC20487
	5		SPC20488
	10		SPC20489
	40		SPC20490

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for white any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farrell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

