

HDC HQP TSLU 1PG16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

Version	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 16
Order No.	1003090000
Type	HDC HQP TSLU 1PG16
GTIN (EAN)	4032248698028
Qty.	1 pc(s).

HDC HQP TSLU 1PG16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	48 mm	Depth (inches)	1.89 inch
Height	54 mm	Height (inches)	2.126 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	26.6 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3		
Chemical resistance	Substance	Acetone	
	Chemical resistance	Conditionally resistant	
	Substance	Drilling oil	
	Chemical resistance	Resistant	
	Substance	Diesel	
	Chemical resistance	Resistant	
	Substance	Ethyl alcohol	
	Chemical resistance	Resistant	
	Substance	Transmission oil	
	Chemical resistance	Resistant	
	Substance	Hydraulic oil	
	Chemical resistance	Resistant	
	Substance	Coolant	
	Chemical resistance	Resistant	
	Substance	Petroleum benzine	
	Chemical resistance	Resistant	
	Substance	Sweat	
	Chemical resistance	Resistant	
	Substance	Premium gasoline	
	Chemical resistance	Conditionally resistant	
Substance	Water		
Chemical resistance	Resistant		
Substance	UV		
Chemical resistance	Unstable		
Substance	Ozone		
Chemical resistance	Unstable		

Dimensions

Cable entry	w. threading	Height of housing B	54 mm
Total length housing	48 mm	Width housing C	28.8 mm

General data

EMC housings	No	Housing main material	Plastic
Protection degree	IP65 (in plugged condition)	Series	HQ
UL 94 flammability rating	V-0		

HDC HQP TSLU 1PG16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Version

BG	HQ	Cable entry	w. threading
Clamp version	Side-locking clamp	Colour (RAL)	RAL 1001
Design	Standard	Design of housing	Cable entry from side, Plug housing
Design of locking system	Side-locking clamp on lower side	External thread	PG 16
Number of cable entry on top	0	Number of cable entry sideways	1
Size	HQ	Size of cable entries	PG 16
Suitable for ModuPlug®	No	Top part/bottom part/lid	upper part
Type	Plug		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E92202

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN