TE Internal #: TB1147D4722-004


M8/M12 Cable Assemblies, Sensor/Actuator, 4 Position, M8 Plug,

M8 Pigtail, Straight Connector Orientation (End A)

View on TE.com >



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies



M8/M12 Application Type: Sensor/Actuator

Number of Positions: 4

Connector Type (End A): M8 Plug Cable Assembly Type: M8 Pigtail

Connector Orientation (End A): Straight

### **Features**

#### **Product Type Features**

| Troduct Type realures         |                |
|-------------------------------|----------------|
| LED                           | Without        |
| Product Type                  | Cable Assembly |
| Assembly Type                 | Overmolded     |
| Connector Type (End A)        | M8 Plug        |
| Cable Assembly Type           | M8 Pigtail     |
| Configuration Features        |                |
| Number of Positions           | 4              |
| Mechanical Attachment         |                |
| Screw & Hole Thread Size      | M8             |
| Connector Orientation (End A) | Straight       |
| Connector Orientation (End B) | Straight       |
| Housing Features              |                |
| Housing Material              | Nylon          |
| Operation/Application         |                |

Sensor/Actuator

M8/M12 Application Type



| Shielded                     | Yes          |
|------------------------------|--------------|
| Other                        |              |
| Cable Assembly Length        | 3 m          |
| Cable Assembly Configuration | Double Ended |

# **Product Compliance**

For compliance documentation, visit the product page on TE.com>

| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions  |
|---|--|
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (1.2% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per<br>homogenous material. Also BFR/CFR/PVC<br>Free  |
| Solder Process Capability                     | Not reviewed for solder process capability   |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# **Compatible Parts**



TE Part # T4040110044-000 RPC-SPE-M8-FF-4CON-LBUS

#### **Documents**

#### **Product Drawings**

RPC-M8-MS-MS-4CON-P-3.0SH

English

#### **CAD Files**

3D PDF

3D

**Customer View Model** 

ENG\_CVM\_CVM\_TB1147D4722-004\_A.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_TB1147D4722-004\_A.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_TB1147D4722-004\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

# Datasheets & Catalog Pages

Catalog-Single Pair Ethernet M8 Hybrid Board Receptacle IP67 and Single Pair Ethernet M8 Hybrid Cordset

English

# **Product Specifications**

**Application Specification** 

English