

SAFETY DATA SHEET

THE DOW CHEMICAL COMPANY

Product name: DOWSIL[™] 7091 Adhesive Sealant Grey

Issue Date: 04/29/2022 Print Date: 04/30/2022

THE DOW CHEMICAL COMPANY encourages and expects you to read and understand the entire (M)SDS, as there is important information throughout the document. We expect you to follow the precautions identified in this document unless your use conditions would necessitate other appropriate methods or actions.

1. IDENTIFICATION

Product name: DOWSIL[™] 7091 Adhesive Sealant Grey

Recommended use of the chemical and restrictions on use Identified uses: Adhesive, binding agents

COMPANY IDENTIFICATION

THE DOW CHEMICAL COMPANY 2211 H.H. DOW WAY MIDLAND MI 48674 UNITED STATES

Customer Information Number:

800-258-2436 SDSQuestion@dow.com

EMERGENCY TELEPHONE NUMBER

24-Hour Emergency Contact: CHEMTREC +1 800-424-9300 Local Emergency Contact: 800-424-9300

2. HAZARDS IDENTIFICATION

Hazard classification

GHS classification in accordance with the OSHA Hazard Communication Standard (29 CFR 1910.1200) Not a hazardous substance or mixture.

Label elements

Precautionary statements Prevention Use only outdoors or in a well-ventilated area.

Other hazards

No data available

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical nature: Silicone elastomer This product is a mixture. Contains no hazardous ingredients according to GHS

4. FIRST AID MEASURES

Description of first aid measures General advice:

First Aid responders should pay attention to self-protection and use the recommended protective clothing (chemical resistant gloves, splash protection). If potential for exposure exists refer to Section 8 for specific personal protective equipment.

Inhalation: Move person to fresh air and keep comfortable for breathing; consult a physician.

Skin contact: Wash off with plenty of water.

Eye contact: Flush eyes thoroughly with water for several minutes. Remove contact lenses after the initial 1-2 minutes and continue flushing for several additional minutes. If effects occur, consult a physician, preferably an ophthalmologist.

Ingestion: If swallowed, seek medical attention. Do not induce vomiting unless directed to do so by medical personnel.

Most important symptoms and effects, both acute and delayed:

Aside from the information found under Description of first aid measures (above) and Indication of immediate medical attention and special treatment needed (below), any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Notes to physician: No specific antidote. Treatment of exposure should be directed at the control of symptoms and the clinical condition of the patient.

5. FIREFIGHTING MEASURES

Extinguishing media

Suitable extinguishing media: Alcohol-resistant foam. Carbon dioxide (CO2). Dry chemical. Water spray.

Unsuitable extinguishing media: None known...

Special hazards arising from the substance or mixture

Hazardous combustion products: Metal oxides. Carbon oxides. Silicon oxides.

Unusual Fire and Explosion Hazards: Exposure to combustion products may be a hazard to health..

Advice for firefighters

Fire Fighting Procedures: Use water spray to cool unopened containers.. Evacuate area.. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations..

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Remove undamaged containers from fire area if it is safe to do so.

Special protective equipment for firefighters: Wear self-contained breathing apparatus for firefighting if necessary.. Use personal protective equipment..

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures: Use personal protective equipment. Follow safe handling advice and personal protective equipment recommendations.

Environmental precautions: Discharge into the environment must be avoided. Prevent further leakage or spillage if safe to do so. Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.

Methods and materials for containment and cleaning up: Wipe up or scrape up and contain for salvage or disposal. Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable. For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.

See sections: 7, 8, 11, 12 and 13.

7. HANDLING AND STORAGE

Precautions for safe handling: Do not get on skin or clothing. Avoid contact with eyes. Do not swallow. Take care to prevent spills, waste and minimize release to the environment. Handle in accordance with good industrial hygiene and safety practice. CONTAINERS MAY BE HAZARDOUS WHEN EMPTY. Since emptied containers retain product residue follow all (M)SDS and label warnings even after container is emptied.

Use only with adequate ventilation. See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Conditions for safe storage: Keep in properly labelled containers. Store in accordance with the particular national regulations.

Do not store with the following product types: Strong oxidizing agents. Unsuitable materials for containers: None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

If exposure limits exist, they are listed below. If no exposure limits are displayed, then no values are applicable.

Exposure controls

Engineering controls: Use local exhaust ventilation, or other engineering controls to maintain airborne levels below exposure limit requirements or guidelines. If there are no applicable exposure limit requirements or guidelines, general ventilation should be sufficient for most operations. Local exhaust ventilation may be necessary for some operations.

Individual protection measures

Eye/face protection: Use safety glasses (with side shields).

Skin protection

Hand protection: Use gloves chemically resistant to this material. Examples of preferred glove barrier materials include: Butyl rubber. Natural rubber ("latex"). Neoprene. Nitrile/butadiene rubber ("nitrile" or "NBR"). Ethyl vinyl alcohol laminate ("EVAL"). Polyvinyl chloride ("PVC" or "vinyl"). NOTICE: The selection of a specific glove for a particular application and duration of use in a workplace should also take into account all relevant workplace factors such as, but not limited to: Other chemicals which may be handled, physical requirements (cut/puncture protection, dexterity, thermal protection), potential body reactions to glove materials, as well as the instructions/specifications provided by the glove supplier.

Other protection: Use protective clothing chemically resistant to this material. Selection of specific items such as face shield, boots, apron, or full body suit will depend on the task.

Respiratory protection: Respiratory protection should be worn when there is a potential to exceed the exposure limit requirements or guidelines. If there are no applicable exposure limit requirements or guidelines, wear respiratory protection when adverse effects, such as respiratory irritation or discomfort have been experienced, or where indicated by your risk assessment process. For most conditions, no respiratory protection should be needed; however, if handling at elevated temperatures without sufficient ventilation, use an approved air-purifying respirator.

The following should be effective types of air-purifying respirators: Organic vapor cartridge.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical state	paste
Color	grey
Odor	alcohol-like
Odor Threshold	No data available
рН	Not applicable
Melting point/range	No data available
Freezing point	No data available
Boiling point (760 mmHg)	Not applicable
Flash point	Seta closed cup >100 °C (212 °F)
Evaporation Rate (Butyl Acetate	Not applicable
= 1)	
Flammability (solid, gas)	Not classified as a flammability hazard
Lower explosion limit	No data available
Upper explosion limit	No data available
Vapor Pressure	Not applicable

Relative Vapor Density (air = 1)	No data available
Relative Density (water = 1)	1.39
Water solubility	No data available
Partition coefficient: n- octanol/water	No data available
Auto-ignition temperature	No data available
Decomposition temperature	No data available
Dynamic Viscosity	Not applicable
Kinematic Viscosity	Not applicable
Explosive properties	Not explosive
Oxidizing properties	The substance or mixture is not classified as oxidizing.
Molecular weight	No data available
Particle size	No data available

NOTE: The physical data presented above are typical values and should not be construed as a specification.

10. STABILITY AND REACTIVITY

Reactivity: Not classified as a reactivity hazard.

Chemical stability: Stable under normal conditions.

Possibility of hazardous reactions: Can react with strong oxidizing agents.

Conditions to avoid: None known.

Incompatible materials: Avoid contact with oxidizing materials.

Hazardous decomposition products:

Decomposition products can include and are not limited to: Formaldehyde.

11. TOXICOLOGICAL INFORMATION

Toxicological information appears in this section when such data is available.

Information on likely routes of exposure Eye contact, Skin contact, Ingestion.

Acute toxicity (represents short term exposures with immediate effects - no chronic/delayed effects known unless otherwise noted)

Acute Toxicity Endpoints: Not classified based on available information.

Acute oral toxicity

Information for the Product:

Low toxicity if swallowed. Small amounts swallowed incidentally as a result of normal handling operations are not likely to cause injury; however, swallowing larger amounts may cause injury.

As product: Single dose oral LD50 has not been determined.

Based on information for component(s): LD50, Rat, male, > 2,000 mg/kg Estimated.

Acute dermal toxicity

Information for the Product:

Prolonged skin contact is unlikely to result in absorption of harmful amounts.

As product: The dermal LD50 has not been determined.

Based on information for component(s): LD50, Rabbit, male, > 2,000 mg/kg Estimated.

Acute inhalation toxicity

Information for the Product:

Brief exposure (minutes) is not likely to cause adverse effects. Vapor from heated material may cause respiratory irritation.

As product: The LC50 has not been determined.

Skin corrosion/irritation

Not classified based on available information.

Information for the Product:

Based on information for component(s): Brief contact is essentially nonirritating to skin. May cause drying and flaking of the skin.

Serious eye damage/eye irritation

Not classified based on available information.

Information for the Product:

Based on information for component(s): May cause slight temporary eye irritation. May cause mild eye discomfort.

Sensitization

For skin sensitization:

Not classified based on available information.

For respiratory sensitization:

Not classified based on available information.

Information for the Product:

For skin sensitization: Contains component(s) which did not cause allergic skin sensitization in guinea pigs. Contains component(s) which have not demonstrated the potential for contact allergy in mice.

For respiratory sensitization: No relevant data found.

Specific Target Organ Systemic Toxicity (Single Exposure)

Not classified based on available information.

Information for the Product:

Product test data not available.

Aspiration Hazard

Not classified based on available information.

Information for the Product:

Based on physical properties, not likely to be an aspiration hazard.

Chronic toxicity (represents longer term exposures with repeated dose resulting in chronic/delayed effects - no immediate effects known unless otherwise noted)

Specific Target Organ Systemic Toxicity (Repeated Exposure)

Not classified based on available information.

Information for the Product:

Product test data not available.

Carcinogenicity

Not classified based on available information.

Information for the Product:

Product test data not available.

Teratogenicity

Not classified based on available information.

Information for the Product:

Product test data not available.

Reproductive toxicity

Not classified based on available information.

Information for the Product:

Product test data not available.

Mutagenicity

Not classified based on available information.

Information for the Product:

Product test data not available.

12. ECOLOGICAL INFORMATION

Ecotoxicological information appears in this section when such data is available.

Toxicity No data available.

Persistence and degradability No data available.

Bioaccumulative potential No data available.

Mobility in soil No data available.

13. DISPOSAL CONSIDERATIONS

Disposal methods: DO NOT DUMP INTO ANY SEWERS, ON THE GROUND, OR INTO ANY BODY OF WATER. All disposal practices must be in compliance with all Federal, State/Provincial and local laws and regulations. Regulations may vary in different locations. Waste characterizations and compliance with applicable laws are the responsibility solely of the waste generator. AS YOUR SUPPLIER, WE HAVE NO CONTROL OVER THE MANAGEMENT PRACTICES OR MANUFACTURING PROCESSES OF PARTIES HANDLING OR USING THIS MATERIAL. THE INFORMATION PRESENTED HERE PERTAINS ONLY TO THE PRODUCT AS SHIPPED IN ITS INTENDED CONDITION AS DESCRIBED IN MSDS SECTION: Composition Information. FOR UNUSED & UNCONTAMINATED PRODUCT, the preferred options include sending to a licensed, permitted: Incinerator or other thermal destruction device. For additional information, refer to: Handling & Storage Information, MSDS Section 7 Stability & Reactivity Information, MSDS Section10 Regulatory Information, MSDS Section 15

Treatment and disposal methods of used packaging: Empty containers should be recycled or otherwise disposed of by an approved waste management facility. Waste characterizations and

compliance with applicable laws are the responsibility solely of the waste generator. Do not re-use containers for any purpose.

14. TRANSPORT INFORMATION

DOT

Not regulated for transport

Classification for SEA transport (IMO-IMDG):

Transport in bulk according to Annex I or II of MARPOL 73/78 and the IBC or IGC Code Not regulated for transport Consult IMO regulations before transporting ocean bulk

Classification for AIR transport (IATA/ICAO):

Not regulated for transport

This information is not intended to convey all specific regulatory or operational requirements/information relating to this product. Transportation classifications may vary by container volume and may be influenced by regional or country variations in regulations. Additional transportation system information can be obtained through an authorized sales or customer service representative. It is the responsibility of the transporting organization to follow all applicable laws, regulations and rules relating to the transportation of the material.

15. REGULATORY INFORMATION

Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Sections 311 and 312 No SARA Hazards

Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and
Community Right-to-Know Act of 1986) Section 313The following components are subject to reporting levels established by SARA Title III, Section 313:
ComponentsComponentsCobalt aluminate blue spinel1345-16-0

Pennsylvania Right To Know

The following chemicals are listed because of the additional requirements of Pennsylvania law:

Components	CASRN
Calcium carbonate (synthetic) treated with synthetic fatty	Not available
acids, C14-18 and C16-18 unsatd.	
Polydimethylsiloxane hydroxy-terminated	70131-67-8

Siloxanes and silicones, dimethyl Titanium dioxide

63148-62-9 13463-67-7

California Prop. 65

WARNING: This product can expose you to chemicals including Methanol, which is/are known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

United States TSCA Inventory (TSCA)

All components of this product are in compliance with the inventory listing requirements of the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.

16. OTHER INFORMATION

Hazard Rating System

NFPA

	Health	Flammability	Instability		
	0	1	0		
H	HMIS				
	Health	Flammability	Physical Hazard		
	0/	1	0		

Revision

Identification Number: 4046862 / A001 / Issue Date: 04/29/2022 / Version: 10.2 Most recent revision(s) are noted by the bold, double bars in left-hand margin throughout this document.

Full text of other abbreviations

AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act: CMR - Carcinogen, Mutagen or Reproductive Toxicant: DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance: ELx - Loading rate associated with x% response: EmS - Emergency Schedule: ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China: IMDG - International Maritime Dangerous Goods: IMO -International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO -International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 -Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for

Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA -Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA -Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Information Source and References

This SDS is prepared by Product Regulatory Services and Hazard Communications Groups from information supplied by internal references within our company.

THE DOW CHEMICAL COMPANY urges each customer or recipient of this (M)SDS to study it carefully and consult appropriate expertise, as necessary or appropriate, to become aware of and understand the data contained in this (M)SDS and any hazards associated with the product. The information herein is provided in good faith and believed to be accurate as of the effective date shown above. However, no warranty, express or implied, is given. Regulatory requirements are subject to change and may differ between various locations. It is the buyer's/user's responsibility to ensure that his activities comply with all federal, state, provincial or local laws. The information presented here pertains only to the product as shipped. Since conditions for use of the product are not under the control of the manufacturer, it is the buyer's/user's duty to determine the conditions necessary for the safe use of this product. Due to the proliferation of sources for information such as manufacturer-specific (M)SDSs, we are not and cannot be responsible for (M)SDSs obtained from any source other than ourselves. If you have obtained an (M)SDS from another source or if you are not sure that the (M)SDS you have is current, please contact us for the most current version.